



M5E.CX.0

Mini biology tweezers - Superalloy Anti-Acid/Anti-Mag - tips: straight, extra fine, superior finish. OAL: 80mm



3" 80 mm
Extra fine tips

Mini tweezers leaflet

Documents

 Body material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Category	High precision tweezers
Kit	no
Tip style	M5E
Tip type characteristic	extra fine
Bent / angled / curved tip (y/n)	no
Reverse action	

	no
Handle serration(y/n)	no
Tip serration (y/n)	no
Locking system	no
ESD safe	no
Body material	CX
Product OAL (mm - in)	80.00 - 3.15
Product width (mm - in)	7.00 - 0.276
Product height (mm - in)	9.00 - 0.354
Tip thickness A (mm - in)	0.02 - 0.001
Tip width B (mm - in)	0.07 - 0.003
Tip opening gap (mm - in)	7.00 - 0.276
Net weight (g-lb)	6 - 0.013



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com