




246SVR.SA.1

Plastic replaceable tip tweezers - PVDF - tips: thin, angled head. OAL: 125mm. ESD safe



Fine bent tips

OAL 5" 125 mm
 B 0.020" 0.5 mm
 A 0.020" 0.5 mm
 D 0.350" 9.0 mm
 E 45°

Documents

 Tip material TDS

 Body material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Plastic Replaceable Tip Tweezers
Kit	no

Tip style	246
Tip type characteristic	thin
Bent / angled / curved tip	angled
Reverse action	no
Handle serration(y/n)	no
Tip serration (y/n)	no
Locking system	no
ESD safe	yes
Body material	SA
Tip material	SV
Product OAL (mm - in)	125.00 - 4.921
Product width (mm - in)	10.00 - 0.394
Product height (mm - in)	15.00 - 0.591
Tip length (mm - in)	23.00 - 0.906
Tip thickness A (mm - in)	0.50 - 0.02
Tip width B (mm - in)	0.50 - 0.02
Tip opening gap (mm - in)	10.00 - 0.394
Degree of bending	45
Net weight (g-lb)	18 - 0.04
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com