




# A246SV

Kit of 2 PVDF tips and 3 screws - tips: thin, angled head. OAL: 36mm. ESD safe



Fine bent tips

OAL 1.417" 36 mm

B 0.020" 0.5 mm

A 0.020" 0.5 mm

D 0.350" 9.0 mm

E 45°

## Documents

Tip material TDS

## Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Plastic Tweezer Tips
Kit	no
Tip style	246

<b>Tip type characteristic</b>	thin
<b>Bent / angled / curved tip</b>	angled
<b>Tip serration (y/n)</b>	no
<b>ESD safe</b>	yes
<b>Tip material</b>	SV
<b>Product OAL (mm - in)</b>	36.00 - 1.417
<b>Product width (mm - in)</b>	9.00 - 0.354
<b>Product height (mm - in)</b>	3.50 - 0.138
<b>Tip thickness A (mm - in)</b>	0.50 - 0.02
<b>Tip width B (mm - in)</b>	0.50 - 0.02
<b>Degree of bending</b>	45
<b>Net weight (g-lb)</b>	1,5 - 0.002
<b>RoHS compliant</b>	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com