




A249SV

Kit of 2 PVDF tips and 3 screws - tips: straight, strong, thick. OAL: 40mm. ESD safe



Strong tips

OAL 1.575" 40 mm

B 0.079" 2 mm

A 0.040" 1 mm

Documents

 Tip material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Plastic Tweezer Tips
Kit	no
Tip style	249
Tip type characteristic	thick, strong

Bent / angled / curved tip (y/n)	no
Tip serration (y/n)	no
ESD safe	yes
Tip material	SV
Product OAL (mm - in)	40.00 - 1.575
Product width (mm - in)	8.00 - 0.315
Product height (mm - in)	4.00 - 0.157
Tip thickness A (mm - in)	1.00 - 0.039
Tip width B (mm - in)	2.00 - 0.079
Net weight (g-lb)	1,5 - 0.002
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com