



VT-5412 SMART VIDEO DOORBELL-2 WAY AUDIO-BLACK BODY

Dimensions
75x40x143mm

SKU:8355

2 YEARS
WARRANTY



Technical Information

Battery Type: 18650 Battery 3350mAh

Unit Color: Black+Silver

Body Type: ABS + PC

Sensor Type: PIR

Dimmable: No

Warranty (Years): 2

Operation Temperature: -10°C ~+50°C

Input Power: AC:8-24V

Features

- ✓ Two-way audio
- ✓ IR Distance: dual IR cut filter with auto switch, max 5 meters
- ✓ Motion detection: alerts users with a push notification
- ✓ Remote operation-system settings, account management, stream code setting
- ✓ Video Compression:H.264, 720P
- ✓ Storage:Max 64GB TF Card
- ✓ Consumption:0.25mA (standby mode), 150mA (working mode)
- ✓ Resolution:1280x720
- ✓ Field Of View:166 Degree
- ✓ Video Quality:HD720P@25FPS
- ✓ D/N Mode:Auto Switch by a light sensor
- ✓ Network :Wi-Fi 2.4 GHz, IEEE 802.11b/g/n

Packaging

Unit Details

Gross Weight(GW) Kgs	0.48012
Unit CBM	0.001646

Listing Details

EAN Code	3800157634960
----------	---------------

Master Box Packaging

Master Box Qty (Pcs Per Carton)	50
---------------------------------	----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES