

SPECIFICATIONS

Signal Inputs/Output	
Input DDC Signal	5 volts p-p (TTL)
Maximum Single Link Range	3840x2160p
Output Video	HDMI
Operating Frequency	
Vertical Frequency Range	50/60Hz
Video Amplifier Bandwidth	Up to 10.2Gbps/340MHz
Resolutions (HDTV)	
Interlaced (50&60Hz)	480i, 576i, 720i, 1080i
Progressive (50&60Hz)	480p, 576p, 720p, 1080p
Power and Environment	
Dimensions	100x48x25mm
Weight	126g
External Power Requirements	5V DC @ 1A
Operating Temperature	0°C to +70°C
Operating Humidity	10% to 85% RH (no condensation)