

**SPECIFICATIONS**

Power requirement	5V DC @ 1A
Output DDC signal	5 volts p-p (TTL)
Max baud rate	10.2Gbps
Max bandwidth	340MHz
Deep Colour	36 bit
Max Single Link Range	3840x2160
Dimensions	150 x 64 x 25mm
Weight (not inc PSU)	0.3kg
Operating Temperature	0 to +7C
Operating Humidity	10% to 85% RH (no condensation)