

**SPECIFICATIONS**

Operating environment	-15 to 55°C, Humidity 5 to 90%
Power requirement	220-240V~50Hz
Power supply	5V DC 1A
Power consumption	800mA
HDMI Input	24/50/60fs/1080p/1080i/720p/576p/576i/480p/480i
Audio formats output	LPCM7.1/DTS/Dolby-AC3/DSD
Audio formats input	DTS-HD/Dolby-trueHD/LPCM7.1/ DTS/Dolby-AC3/DSD
Input video signal	0.5~1.5Volts p-p
Output DDC signal	5 Volts p-p (TT1L)
Max baud rate	4.95Gbps
Max bandwidth	165MHz
Dimensions (each)	83 x 43 x 23mm
Weight (not inc PSU)	104g (each approx)