


ELECTRICAL TEST:
 1.100% OPEN SHORT MIS WIRE TEST
 2.CONTACT RESISTANCE:5 OHM MAX
 3.INSULATION RESISTANCE:5M OHM MIN
 4.HI-POT TEST:DC 300V/10ms
 5.0.2-3.0M PASS 4K@60HZ TEST


CONSUMER ITEM	LENGTH (mm)	ERP	Packing
HDMI A-D/0.2M	200 ± 20	/	
HDMI A-D/0.5M	500 ± 20		
HDMI A-D/1.0M	1000 ± 30		
HDMI A-D/2.0M	2000 ± 30		
HDMI A-D/3.0M	3000 ± 30		



Cable Marking:
 HIGH SPEED HDMI® CABLE WITH ETHERNET

PIN Assignment

P1 A TYPE	P2 D TYPE
1	3
2	5
3	4
4	6
5	8
6	7
7	9
8	11
9	10
10	12
11	14
12	13
13	2
14	1
15	16
16	15
17	17
18	18
19	19
SHELL	SHELL



⑤	CABLE	2.0V HDMI 19+1 32AWG BC [(1/0.20BC*1P+D1/0.20BC+AL/MY)*5P+1/0.20BC*4C]+AL +D1/0.20BC+16/3/0.12AM Black PVC Jacket OD:4.5±0.15mm	m
④	MODEL	Black 45P PVC	g
③	MODEL	PE,Nature color	g
②	plug	HDMI DM 19P Gold plated,Insulation:BLACK	1pcs
①	plug	HDMI AM 19P Gold plated,Insulation:BLACK	1pcs
NO.	PART NAME	DESCRIPTION	UNIT

PRO-SIGNAL				DESCRIPTION	FINISHED PRODUCT'S FIGURE	SCALE	FIT	UNITS: MM	1RD ANGLE
APPROVED	CHECKED	DRAWING	DESIGNED	MODEL NO.	PSG91701	△			
				DRAWING NO.		△			
				FINISHING		△	2019/05/08		A1
				MATERIAL		SYM	DATE		REVISION