

Motion detector

## IS 360-1 DE

white

EAN 4007841032845



### Function description

Intelligent technology for installation. Infrared wall sensor IS 360-1 DE, for indoors and out, ideal for installing in projecting roofs and suspended ceilings, 360° angle of coverage, reach can be set up to 4 m, selectable time and twilight threshold, detection zone can be customised with shrouds.

### Technical specifications

Type	Motion detectors
Dimensions (Ø x H)	78 x 89 mm
Mains power supply	230 – 240 V , 50 / 60 Hz
Sensor Technology	passive infrared
Application, place	Indoors, outdoors
Type of installation	Other
Switching zones	306 switching zones
Electronic scalability	No
Mechanical scalability	No
Optimum mounting height	2,5 m
Detection angle	360 °
Angle of aperture	90 °
Sneak-by guard	Yes
Capability of masking out individual segments	Yes
Reach, tangential	Ø 8 m (50 m <sup>2</sup> )
Twilight setting TEACH	No
Twilight setting	2 – 2000 lx
Time setting	8 sec – 35 min

# Data sheet



Motion detector

## IS 360-1 DE

white

EAN 4007841032845

### Technical specifications

Switching output 1, resistive	1000 W
Switching output 1, number of LEDs / fluorescent lamps	6 pcs.
Constant-lighting control	No
Basic light level function	No
With remote control	No
Interconnection	Yes
IP rating	IP54
Material	Plastic
Ambient temperature	-20 – 40 °C
Colour	white
Colour, RAL	9010
Manufacturer's Warranty	3 years
Version	white
PU1, EAN	4007841032845

# Data sheet



Motion detector

## IS 360-1 DE

white

EAN 4007841032845

Mood image

