

WE 1010

1-Channel Power Unit, digital, 70 W
Product no.: T0053298699



Benefits

- › Power unit, 1 channel with soldering iron WEP 70 and safety rest PH 70
- › 70 W solder iron with ergonomic handle and providing toolless tip change
- › ESD safe station, iron and heat-resistant silicon cable for safe handling
- › Using ET soldering tips
- › Standby mode and auto setback conserves energy, protects equipment
- › Password-protected to preserve settings
- › Change hot tips out by hand by twisting the plastic knurled nut on the soldering pencil without an additional tool.



Technical Data

Dimensions L x W x H (mm)	150 x 120 x 98
Dimensions L x W x H (inches)	5.91 x 4.72 x 3.86
Weight (approx.) in kg	1.4
Voltage	230 V
Power	85 W
Channels	1
Temperature range (depends on tool) °C	100 - 450
Temperature range (depends on tool) °F	200 - 850
Temperature accuracy °C	± 5
Temperature accuracy °F	± 9
Temperature stability °C	± 6
Temperature stability °F	± 10
Equipotential bonding socket	---
Display	Digital LC Display
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---