

TM
TM 201/15 V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation. There are five different lengths (12, 15, 18, 20 and 30 mm) and eleven sizes - a marker type for all sleeves.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

General ordering data

Type	TM 201/15 V0
Order No.	1798620000
Version	TM, Socket x 5 mm, PVC, Colour: Transparent, Conductor O.D.: 1.5 - 2.5 mm
GTIN (EAN)	4032248243358
Qty.	1,000 pc(s).

TM
TM 201/15 V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	5 mm	Width (inches)	0.197 inch
Height	15 mm	Height (inches)	0.591 inch
Depth	5 mm	Depth (inches)	0.197 inch
Net weight	0.265 g		

General data

Colour	Transparent	Material	PVC
Operating temperature range	-40...80 °C	Recommended industries	Transportation, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Width	5 mm		

Conductor and cable markers

Conductor O.D.	1.5 - 2.5 mm	Conductor O.D., max.	2.5 mm
Conductor O.D., min.	1.5 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.25 mm ²		

Classifications

ETIM 3.0	EC001530	ETIM 4.0	EC001530
ETIM 5.0	EC001530	ETIM 6.0	EC001530
UNSPSC	44-12-17-08	eClass 5.1	27-14-91-03
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP
Product Change Notification	PCN Transparent Sleeves_DE PCN Transparent Sleeves_EN

TM
TM 201/15 V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Accessories
Blank


TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are five different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the SMark laser printer, PrintJet ADVANCED, plotter, MC-Mobilo or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.
TM-I 15 MC NE RT	1609981686	TM-I, Insert markers, mm, red	15 x 4 4008190367824	400 pc(s).
TM-I 15 MC NE VI	1427870000	TM-I, Insert markers, mm, violet	15 x 4 4050118231847	400 pc(s).
TM-I 15 MC NE SI	1609981697	TM-I, Insert markers, mm, silver	15 x 4 4008190137410	400 pc(s).
TM-I 15 MC NE GE	1609981687	TM-I, Insert markers, mm, yellow	15 x 4 4008190914776	400 pc(s).
TM-I 15 MC NE GN	1609981688	TM-I, Insert markers, mm, green	15 x 4 4008190398705	400 pc(s).
TM-I 15 MC NE WS	1609981044	TM-I, Insert markers, mm, white	15 x 4 4008190914783	400 pc(s).
TM-I 15 MC NE BL	1609981693	TM-I, Insert markers, mm, blue	15 x 4 4008190367831	400 pc(s).