

**TM-I**  
**TM-I 15 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**Process reliability: TM-I**

TM-I inlay tags have a guide tab which allows them to slide easily into the transparent sleeves from the type TM. The MultiMark TM-I markers should not be used together with the CLI T sleeves. We currently optimize the usability of the transparent sleeves from the type CLI T. Once the tag is in place, the tab is snapped off at the predetermined break point. The ready-assembled sleeves can then be simply pushed over the conductors. Your benefits: large quantities can be efficiently pre-assembled in a single step.

**Your benefits with MultiMark**

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

**General ordering data**

Type	TM-I 15 MM WS
Order No.	<a href="#">2005450000</a>
Version	TM-I, Insert markers, 15 x 4 mm, white
GTIN (EAN)	4050118390346
Qty.	2,000 pc(s).
compatible printer	<a href="#">2430920000</a> <a href="#">2448870000</a> <a href="#">1140490000</a>

## Data sheet

### TM-I TM-I 15 MM WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	4 mm	Width (inches)	0.157 inch
Height	15 mm	Height (inches)	0.591 inch
Net weight	0.156 g		

### General data

Colour	white	Halogen	No
Material	Polyester	Number per roll	2,000
Operating temperature range	-40...150 °C	UL 94 flammability rating	HB
Width	4 mm		

### Conductor and cable markers

Halogen	No
---------	----

### Classifications

ETIM 5.0	EC001530	ETIM 6.0	EC001530
eClass 6.2	27-40-04-01	eClass 9.0	27-40-04-01
eClass 9.1	27-40-04-01		

### Approvals

ROHS	Conform
------	---------

### Downloads


Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**TM-I**  
**TM-I 15 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**TM-I  
TM-I 15 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Accessories**

**Ink ribbons THM MMP**



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
RIBBON MM 76/360 SW	<a href="#">2005080000</a>	Ink ribbon	4050118389951	1 pc(s).

**Accessories / replacement parts**



Our marking systems can be used to quickly and reliably label connector markers, conductor and cable markers, device markers and labels. The M-Print® PRO software enables rapid and easy identification of your electrical equipment. You can design, label and order your marking materials professionally and quickly. Frames, barcodes, graphics or photos are easily incorporated. The versatile data conversion routines enable quick and flexible data integration. The Weidmüller PrintJet ADVANCED, MCP Plus and MCP Basic printers and the THM series printers are available for printing.

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
THM MMP ROLLER 115	<a href="#">1357420000</a>		4050118160314	1 pc(s).