

2019




wiha 

Tools that work for you

# PROFESSIONAL QUALITY BITS




## COMPLETE BITS PROGRAM










Slotted • Phillips • TORX® • Security TORX® • Hex Inch/Metric • Ball End Hex  
MagicRing Hex • Security Hex • Nut Driver • Pozidriv® • Square • Tri-Wing  
Spanner • Torq Set • TORXPlus® • Security TORXPlus® • Xeno Phillips























## Terminator Impact Insert & Power Bits

DESCRIPTION	Page
 Terminator Impact Bits	4-7



## Standard Bits

DESCRIPTION	Page
 Torx® Insert/Power Bits	8-9
 Phillips Insert/Power Bits	16-17
 Hex Metric & Inch Insert/Power Bits	19-20
 Square Insert/Power Bits	24
 Slotted Insert/Power Bits	24-25
 Pozidriv® Insert/Power Bits	26
 Nut Setters	50




## Specialty Bits

DESCRIPTION	Page
  Xeno Phillips Terminal Block	18
  Torx® Align Bits	11
  Security Torx® Insert/Power Bits	12-13
  TorxPlus® Insert/Power Bits	14
  Ball End Torx®	15
  Security Pentalobe	15
  Security Hex Triple Square Insert Bits	21
  XZN Insert	28
  Tri-Wing Insert/Power Bits	27
  Torq Set Insert/Power Bits	27
  Spanner	28










## Cutting Tools

DESCRIPTION	Page
 Counter Sink	28
 Drill Bit	28



## High Performance Bits

DESCRIPTION	Page
 Dura Bits	29
Slotted, Phillips, Pozidriv®, Torx® Insert/Power Bits - Tungsten Carbide Coated	
 Diamond Bits	29
Slotted, Phillips, Pozidriv®, Torx® Insert/Power Bits	
 TiN Coated Bits	30
Phillips & Torx® - Titanium Insert/Power Bits	

## Insert & Power Bit Sets

DESCRIPTION	Page
 Security Bits Collector	36
 26inOne Ultra Drivers	33
 Insert Bit Selectors	10,13,22,37
 XSelector/XLSelectors	10,22,37
 6-in-1 Multi-Bit Sets	13,22,38
 Stubby Bit Holder Sets	13,22,32
 Pop-Up Bit Holder Sets	32
 Power Bit Belt Packs	10-11, 39
 PokitPak Sets	10-11,17,22


## Power Blades & Sets

DESCRIPTION	Page
 Power Blades	13,18,23,31
Slotted/Phillips/Security Torx® & Hex TriWing/Square/Spanner/Pozidriv®	
 Power Blade Sets	13,18,23,31


**ESD 1/4" Quick Release Bit Holder Blade Set**

	DESCRIPTION	Page
	1/4" Quick Release	42











**TorqueControl Insert & Micro Bit Sets**

	DESCRIPTION	Page
	TorqueControl Bit Sets	39








**ESD Safe Micro Bit Handles/Bits & Sets**

	DESCRIPTION	Page
	Micro Bits	43-46
	ESD Safe Micro Bit Sets	47-19

**Bit Holders**

	DESCRIPTION	Page
	ESD Safe Bit Holders	42
	SoftFinish® Cushion Grip	40
	MicroFinish Non-Slip Grip	40
	3K Ergo Bit Holder	40
	T-handle	40
	SoftGrip Stubby Bit Holder	40
	Flexible Shaft Bit Holder	40
	Drive-Loc VI Bit Holder	40
	Protturn Precision	40
	Multi-Bit Holders	41

**Bit Holders**

	DESCRIPTION	Page
	Micro Bit Power Tool Adapter	45
	ClicFix Quick Release Insert Bits	42
	CentroFix Quick Release All 1/4" Drive Tools	42
	Protturn Quick Release 1/4" Drive	41
	Stainless Steel Bit Holder	41
	Magnetic Bit Holders & Retaining Ring Bit Holder	41
	"SlimFix" Impact Bit Holder Quick Release	41

**Bit Sockets**

	DESCRIPTION	Page
	Torx® 1/4" Drive	51
	Torx® 3/8" Drive	51
	Torx® 3/8" - 5/16" Bits	51
	Security Torx® 3/8"	51
	Slotted Bit Sockets 1/2" Drive	51
	Phillips Bit Socket 1/2" Drive	51
	Hex Bit Sockets 1/4" Drive	52
	Hex Bit Sockets 3/8" Drive	52
	Ball End Hex Sockets	52
	Socket Adapters	52
	Impact Bit Holding Sockets	53
	6" Bit Sockets 1/4" & 3/8" Drive	53
	Socket Sets	54-55

## Wiha Terminator Impact Bits

# Impact Bits

Ready For Sudden Impact!



### 765 Phillips Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	+	—	■
No.	Size	mm	pkg.
76501	1	29	10
76502	2	29	10
76503	3	29	10

### 768 Phillips Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	+	—	■
No.	Size	mm	pkg.
76801	1	29	2
76802	2	29	2
76803	3	29	2



### 765 Pozidriv Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	+	—	■
No.	Size	mm	pkg.
76506	1	29	10
76507	2	29	10
76508	3	29	10

### 768 Pozidriv Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	+	—	■
No.	Size	mm	pkg.
76806	1	29	2
76807	2	29	2
76808	3	29	2



### 765 TORX Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	*	—	■
No.	Size	mm	pkg.
76510	T10	29	10
76511	T15	29	10
76512	T20	29	10
76513	T25	29	10
76514	T27	29	10
76516	T30	29	10
76517	T40	29	10

### 768 TORX Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	*	—	■
No.	Size	mm	pkg.
76810	T10	29	2
76811	T15	29	2
76812	T20	29	2
76813	T25	29	2
76814	T27	29	2
76816	T30	29	2
76817	T40	29	2

Impact rated bits for long life in impact applications  
 Standard 1/4" drive - No special adaptor required  
 Wiha enhanced bi-material torsion zone  
 Precision machined exact fit tips  
 Wiha exclusive CVM tool steel  
 Guaranteed to out perform impact imposters



Dual material impact absorbing torsion zone

## 1/4" Drive Insert & Power Bits



### 765 Square Terminator Impact Bits, 1/4" Insert - 10 Bit Pack

Item	□	—	■
No.	Size	mm	pkg.
76538	1	29	10
76539	2	29	10
76540	3	29	10

### 768 Square Terminator Impact Bits, 1/4" Insert - 2 Bit Pack

Item	□	—	■
No.	Size	mm	pkg.
76838	1	29	2
76839	2	29	2
76840	3	29	2



Ultra Drivers on page 33-35



Includes 1/4" SlimFix Bit Holder

### 76898 42 Pc. Combo Bit Set With Terminator Impact Bits & Ultra Driver Bit Set

Item No. 76898 1.5 lbs. .92

#### Terminator Impact Bits:

Phillips: #1, 2 (2), 3

Square: #1, 2 (2), 3

Torx®: T10, T15, T20 (2), T25 (2), T30 (2), T40

Hex Metric: 3.0, 4.0, 5.0, 6.0mm

Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

#### Double End Ultra Driver Bits:

Slotted: 3.0+4.5, 5.5+6.5mm

Phillips: #1+2, #0+3

Pozidriv®: #1+2

Square: #1+2, #0+3

Torx®: T10+T15, T20+T25





Hex Inch: 1/8+9/64, 5/32+3/16"

Hex Metric: 3.0+4.0, 5.0+6.0mm









**765 Hex Inch Terminator Impact Bits, 1/4" Insert - 10 Bit Pack**





Item				
No.	Inch	mm	pkg.	
76530	1/8	29	10	
76531	9/64	29	10	
76532	5/32	29	10	
76533	3/16	29	10	
76534	7/32	29	10	
76535	1/4	29	10	

**768 Hex Inch Terminator Impact Bits, 1/4" Insert - 2 Bit Pack**





Item				
No.	Inch	mm	pkg.	
76830	1/8	29	2	
76831	9/64	29	2	
76832	5/32	29	2	
76833	3/16	29	2	
76834	7/32	29	2	
76835	1/4	29	2	




**765 Hex Metric Terminator Impact Bits, 1/4" Insert - 10 Bit Pack**

Item				
No.	mm	mm	pkg.	
76523	3.0	29	10	
76524	4.0	29	10	
76525	5.0	29	10	
76526	6.0	29	10	


**768 Hex Metric Terminator Impact Bits, 1/4" Insert - 2 Bit Pack**

Item				
No.	mm	mm	pkg.	
76823	3.0	29	2	
76824	4.0	29	2	
76825	5.0	29	2	
76826	6.0	29	2	



**76897 28 Pc. Terminator Impact Insert Bit Set With SlimFix 1/4" Locking Bit Holder**

**Item No. Set includes the following bits:**



76897	Phillips: #1, 2 (2), 3
	Sq: #1, 2, 3 & Pozidriv®: #1, 2, 3
lbs. .47	Hex Metric: 3.0, 4.0, 5.0, 6.0mm
	Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
	Torx®: T10, T15, T20, T25(2), T30, T40

**Wiha Insert Terminator Impact Bit Sets**



**76876 10 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm**


**76876 Set includes the following bits:**

-  Hex In: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
-  Hex Metric: 3.0, 4.0, 5.0, 6.0mm



**76877 10 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm**




**76877 Set includes the following bits:**

-  Torx®: T10, T15, T20 (2), T25 (2), T27, T30 (2), T40



**76881 10 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm**


**76881 Set includes the following bits:**

-  Phillips: #1, 2, 3
-  Square: #1, 2, 3
-  Torx®: T20, T25, T30, T40



**76899 34 Pc. Terminator Impact Insert Bit Set With 3K Bit Holder Handle & SlimFix 1/4" Locking Bit Holder**

**Item No. Set includes the following bits:**




76899	2 Phillips: #1, 2, 3
	Square: #1, 2 (2), 3
lbs.	Pozidriv®: #1, 2, 3
1.12	Torx®: T10, T15, T20 (2), T25 (2), T30 (2), T40
	Hex Metric: 3.0, 4.0, 5.0, 6.0mm
	Hex Inch: 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



Includes magnetic bit holder

**76890 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm**

**76890 Set includes the following bits:**




-  3 Phillips: #2
-  Square: #2
-  Torx®: T15, T20, T25

Includes magnetic bit holder



**76891 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm**

**76891 Set includes the following bits:**



-  Phillips: #2, 3
-  Square: #2, 3
-  Torx®: T20, T25, T30

Includes magnetic bit holder



**76893 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm**

**76893 Set includes the following bits:**


-  Hex Inch: 5/32, 3/16, 7/32, 1/4"
-  Hex Metric: 4, 5, 6mm

Includes magnetic bit holder



**76895 8 Pc. Bit Buddy Set With Terminator Impact Insert Bits - 29mm**

**76895 Set includes the following bits:**

-  Torx®: T10, T15, T20, T25, T27, T30, T40

Includes magnetic bit holder

## Wiha Power Terminator Impact Bits & Power Terminator Impact Bit Sets



### 765 Phillips Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76543	1	49	10
76544	2	49	10
76545	3	49	10

### 768 Phillips Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76843	1	49	2
76844	2	49	2
76845	3	49	2



### 765 Pozidriv® Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76548	1	49	10
76549	2	49	10
76550	3	49	10

### 768 Pozidriv® Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	+	—	—
No.	Size	mm	pkg.
76848	1	49	2
76849	2	49	2
76850	3	49	2



### 765 Square Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	□	—	—
No.	Size	mm	pkg.
76578	1	49	10
76579	2	49	10
76580	3	49	10

### 768 Square Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	□	—	—
No.	Size	mm	pkg.
76878	1	49	2
76879	2	49	2
76880	3	49	2



### 765 TORX® Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	T	—	—
No.	Size	mm	pkg.
76553	T10	49	10
76554	T15	49	10
76555	T20	49	10
76556	T25	49	10
76557	T27	49	10
76558	T30	49	10
76559	T40	49	10

### 768 TORX® Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	T	—	—
No.	Size	mm	pkg.
76853	T10	49	2
76854	T15	49	2
76855	T20	49	2
76856	T25	49	2
76857	T27	49	2
76858	T30	49	2
76859	T40	49	2



### 765 Hex Inch Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	⬡	—	—
No.	Inch	mm	pkg.
76570	1/8	49	10
76571	9/64	49	10
76572	5/32	49	10
76573	3/16	49	10
76574	7/32	49	10
76575	1/4	49	10

### 768 Hex Inch Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	⬡	—	—
No.	Inch	mm	pkg.
76870	1/8	49	2
76871	9/64	49	2
76872	5/32	49	2
76873	3/16	49	2
76874	7/32	49	2
76875	1/4	49	2



### 765 Hex Metric Terminator Impact Bits, 1/4" Power - 10 Bit Pack

Item	⬡	—	—
No.	mm	mm	pkg.
76563	3.0	49	10
76564	4.0	49	10
76565	5.0	49	10
76566	6.0	49	10

### 768 Hex Metric Terminator Impact Bits, 1/4" Power - 2 Bit Pack

Item	⬡	—	—
No.	mm	mm	pkg.
76863	3.0	49	2
76864	4.0	49	2
76865	5.0	49	2
76866	6.0	49	2



### 76892 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76892 Set includes the following bits:

- ⊕ Phillips: #2, 3
- Square: #2, 3
- ⊛ Torx®: T20, T25, T30



### 76896 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76896 Set includes the following bits:

- ⊛ Torx®: T10, T15, T20, T25, T27, T30, T40



### 76894 7 Pc. Bit Buddy Set With Terminator Impact Power Bits - 49mm

76894 Set includes the following bits:

- ⬡ Hex Inch: 5/32, 3/16, 7/32, 1/4"
- ⬡ Hex Metric: 4, 5, 6mm

**Wiha Terminator Impact Bit Box Packs**



**766 Phillips Terminator Impact Bits, 1/4" Insert - 25 Bit Box Pack**

Item			
No.	Size	mm	pkg.
76601	1	29	25
76602	2	29	25
76603	3	29	25



**766 Square Terminator Impact Bits, 1/4" Power - 15 Bit Pack**

Item			
No.	Size	mm	pkg.
76645	2	49	15



**766 TORX® Terminator Impact Bits, 1/4" Power - 15 Bit Pack**

Item			
No.	Size	mm	pkg.
76650	T10	49	15
76651	T15	49	15
76652	T20	49	15
76653	T25	49	15
76654	T27	49	15
76655	T30	49	15
76656	T40	49	15



**766 Square Terminator Impact Bits, 1/4" Insert - 25 Bit Pack**

Item			
No.	Size	mm	pkg.
76605	2	29	25



Identification on bits allows quick bit selection

**Wiha Power Terminator Impact Bits 250 Bit Packs**



**766 TORX® Terminator Impact Bits, 1/4" Insert - 25 Bit Pack**

Item			
No.	Size	mm	pkg.
76610	T10	29	25
76611	T15	29	25
76612	T20	29	25
76613	T25	29	25
76614	T27	29	25
76615	T30	29	25
76616	T40	29	25



**765 Phillips Terminator Impact Bits, 1/4" Insert - 250 Bit Pack**

Item			
No.	Size	mm	pkg.
76581	1	29	250
76582	2	29	250



**765 Phillips Terminator Impact Bits, 1/4" Power - 250 Bit Pack**

Item			
No.	Size	mm	pkg.
76590	1	49	250
76591	2	49	250



**765 Square Terminator Impact Bits, 1/4" Insert - 250 Bit Pack**

Item			
No.	Size	mm	pkg.
76583	1	29	250
76584	2	29	250



**765 Square Terminator Impact Bits, 1/4" Power - 250 Bit Pack**

Item			
No.	Size	mm	pkg.
76592	1	49	250
76593	2	49	250



**766 Phillips Terminator Impact Bits, 1/4" Power - 15 Bit Pack**

Item			
No.	Size	mm	pkg.
76641	1	49	15
76642	2	49	15
76643	2	49	15



**765 TORX® Terminator Impact Bits, 1/4" Insert - 250 Bit Pack**

Item			
No.	Size	mm	pkg.
76585	T15	29	250
76586	T20	29	250
76587	T25	29	250
76588	T27	29	250
76589	T30	29	250



**765 TORX® Terminator Impact Bits, 1/4" Power - 250 Bit Pack**

Item			
No.	Size	mm	pkg.
76594	T15	49	250
76595	T20	49	250
76596	T25	49	250
76597	T27	49	250
76598	T30	49	250



## TORX® Bits

The ideal multi-purpose bits for all around quality and performance

Made by Wiha - Production Quality

Suitable for all applications for both manual and machine  
Hardness HRC 59-61

Highly resistant to wear and tear for a long tool life

Impact resistant modified CVM, tool steel, hardened



### Wiha TORX® Bit Packs



**71571 TORX® Insert Bit Packs, 1" CVM S2** modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

**71571 Set includes the following bits:**

**Torx®:**  
T15, T20, T25, T27,  
wt. .08 T30, T40 x 1" (25mm)



**71570 TORX® Insert Bit Packs, 1" CVM S2** modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc bit pack.

**71570 Set includes the following bits:**

**Torx®:**  
T5, T6, T7, T8, T9,  
wt. .07 T10 x 1" (25mm)

### Wiha TORX® Insert Bit



10 bit pack

#### 715 TORX® Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
71523	T3	25	10	.12
71524	T4	25	10	.12
71505	T5	25	10	.12
71506	T6	25	10	.12
71507	T7	25	10	.12
71508	T8	25	10	.12
71509	T9	25	10	.12
71510	T10	25	10	.12
71515	T15	25	10	.12
71520	T20	25	10	.12
71525	T25	25	10	.12
71527	T27	25	10	.13
71530	T30	25	10	.14
71540	T40	25	10	.15

#### 30 Piece Contractor Grade Bits

#### 725 TORX® Insert Bit Packs, 30 Pcs., 1/4"

Item No.	Size	mm	lbs.
72572	T7	25	.36
72573	T8	25	.36
72574	T9	25	.36
72575	T10	25	.36
72576	T15	25	.36
72577	T20	25	.36
72578	T25	25	.36
72579	T27	25	.36
72580	T30	25	.36
72581	T40	25	.36

### Wiha TORX® Bit Packs

2 bit pack



#### 715 TORX® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
71548	T3	25	.03
71549	T4	25	.03
71550	T5	25	.03
71551	T6	25	.03
71552	T7	25	.03
71553	T8	25	.03
71554	T9	25	.03
71555	T10	25	.03
71556	T15	25	.03
71557	T20	25	.03
71558	T25	25	.03
71559	T27	25	.04
71560	T30	25	.04
71561	T40	25	.04

2 bit pack



#### 777 TORX® Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item No.	Size	mm
77701	T6+T7	30
77702	T8+T9	30
77703	T10+T15	30
77704	T20+T25	30
77705	T27+T30	30

### Wiha TORX® 5/16" Bits



10 bit pack

#### 725 TORX® Bits, 5/16"

Item No.	Size	mm	pkg.	lbs.
72525	T25	35	10	.27
72527	T27	35	10	.27
72530	T30	35	10	.27
72540	T40	35	10	.28
72545	T45	35	10	.31
72550	T50	35	10	.32
72555	T55	35	10	.52
72570	T60	35	10	.52

5/16" Insert Bits

2 bit pack



#### 725 TORX® Insert Bit Packs, 5/16"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
72528	T25	35	.28
72529	T27	35	.28
72531	T30	35	.28
72541	T40	35	.28
72546	T45	35	.31
72551	T50	35	.32
72556	T55	35	.52
72569	T60	35	.52




### Wiha TORX® Power Bits



#### 745 TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.	lbs.
74511	T6	50	10	.18	
74512	T7	50	10	.18	
74513	T8	50	10	.18	
74517	T9	50	10	.19	
74519	T10	50	10	.20	
74521	T15	50	10	.20	
74523	T20	50	10	.20	
74529	T25	50	10	.20	
74531	T27	50	10	.20	
74533	T30	50	10	.20	
74535	T40	50	10	.25	



#### 745 TORX® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Size	mm	pkg.	lbs.
74536	T6	70	10	.02	
74538	T7	70	10	.02	
74542	T8	70	10	.02	
74544	T9	70	10	.02	
74546	T10	70	10	.02	
74548	T15	70	10	.02	
74551	T20	70	10	.03	
74553	T25	70	10	.03	
74556	T27	70	10	.04	
74558	T30	70	10	.04	
74561	T40	70	10	.04	



#### 745 TORX® Power Bits 1/4" Hex Drive, Length 3.5"/90mm

Item	No.	Size	mm	pkg.	lbs.
74563	T6	90	1	.03	
74565	T7	90	1	.03	
74567	T8	90	1	.03	
74569	T9	90	1	.03	
74571	T10	90	1	.03	
74573	T15	90	1	.03	
74575	T20	90	1	.04	
74577	T25	90	1	.04	
74579	T27	90	1	.04	
74581	T30	90	1	.04	
74583	T40	90	1	.04	



#### 745 TORX® Power Bit Packs, 2"

CVM S2 modified tool steel.

Item	No.	Size	mm	lbs.
74525	T1	50	.05	
74527	T2	50	.05	
74530	T3	50	.05	
74540	T4	50	.05	
74559	T5	50	.05	
74501	T6	50	.05	
74502	T7	50	.05	
74503	T8	50	.05	
74504	T9	50	.05	
74506	T10	50	.05	
74508	T15	50	.05	
74510	T20	50	.05	
74514	T25	50	.06	
74515	T27	50	.06	
74516	T30	50	.06	
74518	T40	50	.08	



#### 739 TORX® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm 2 bit pack


Item	No.	Size	mm	pkg.	lbs.
73936	T6	70	1	.02	
73937	T7	70	1	.02	
73938	T8	70	1	.02	
73939	T9	70	1	.02	
73940	T10	70	1	.02	
73941	T15	70	1	.02	
73942	T20	70	1	.03	
73943	T25	70	1	.03	
73944	T27	70	1	.04	
73945	T30	70	1	.04	
73946	T40	70	1	.04	



#### 745 TORX® Power Bits 1/4" Hex Drive, Length 6.0"/150mm


Item	No.	Size	mm	pkg.	lbs.
74580	T6	150	1	.04	
74582	T7	150	1	.04	
74584	T8	150	1	.04	
74585	T9	150	1	.04	
74586	T10	150	1	.04	
74587	T15	150	1	.04	
74588	T20	150	1	.04	
74589	T25	150	1	.04	
74590	T27	150	1	.04	
74591	T30	150	1	.04	

### Wiha TORX® Double End Bits



#### 744 TORX® Double End Bits 1/4" Hex Drive, Length 2.56"/65mm

Item	No.	Size	Size	mm	pkg.	lbs.
74413	T7	T7	65	10	.32	
74415	T8	T8	65	10	.32	
74417	T9	T9	65	10	.32	
74419	T10	T10	65	10	.32	
74431	T27	T27	65	10	.34	
74433	T30	T30	65	10	.35	
74435	T40	T40	65	10	.38	



#### 744 TORX® Double End Bit Pack 1/4" Hex Drive, Length 2.56"/65mm

Item	No.	Size	Size	mm	lbs.
74461	T7	T7	65	.05	
74462	T8	T8	65	.05	
74463	T9	T9	65	.05	
74464	T10	T10	65	.05	
74465	T15	T15	65	.05	
74468	T27	T27	65	.06	
74469	T30	T30	65	.07	
74470	T40	T40	65	.07	

## Wiha Stainless Steel Insert Bits & Power Bits



### 715 Stainless Steel TORX® Bits, 1/4"

Item	No.	Size	mm	pkg.
	71500	T8	25	1
	71502	T10	25	1
	71513	T40	25	1



### 704 Stainless Steel TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.
	70411	T15	50	1
	70414	T25	50	1
	70416	T30	50	1
	70417	T40	50	1

## Wiha TORX® Insert Bit Sets

Bit holder stainless steel, magnetic



### 38044 TORX® Pop-Up Bit Screwdriver Set

Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle.

Set includes the following 1/4" bits:  
lbs. TORX®: T5, T6, T7, T8, T9, T10, .42 T15, T20, T25, T27, T30, T40



### 38003 TORX® Multi-Bit Screwdriver with Wiha Powerhandle.

Includes the following 1/4" bits:

TORX® : T5, T6, T7, T8, T9, T10



### 79242 Bit-Selector With TORX® Bits Includes Universal Magnetic 1/4" Bit Holder & The Following 10 Insert Bits:

lbs. TORX®: T5, T6, T7, T8, T9, .32 T10, T15, T20, T25, T30



### 38045 TORX® SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:  
lbs. TORX®: T8, T10, T15, .20 T20, T25, T30

### 79245 Bit-Selector With TORX® Bits Includes Auto Lock Magnetic 1/4" Bit Holder & The Following 10 Insert Bits:

lbs. TORX®: T7, T8, T9, T10, .34 T15, T20, T25, T27, T30, T40

## Wiha TORX® Insert Bit & Power Bit Sets



### 79445 XSelector Bit Set With TORX® Bits Set Includes 1/4" Magnetic Bit Holder & the following 10 bits:

lbs. TORX®: T7, T8, T9, T10, T15, .29 T20, T25, T27, T30, T40



### 71195 PokitPak - TORX® Insert Bits In Molded Case - Includes 6 - 1/4" Insert Bits & Magnetic Bit Holder

lbs. TORX® : T8, T10, T15, T20, T25, T30



### 74985 Power Bit Belt Pack With TORX® Bits Includes the following 10 bits:

lbs. TORX®: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

## Wiha Insert Bit Blister Pack



### 72595 10 Pack TORX® Insert Bit Pack CVM S2 modified tool steel.

lbs. TORX® : T7, T8, T9, T10, T15, .16 T20, T25, T27, T30, T40

## Wiha Insert Bit & Socket Set



### 72590 11 Piece TORX® Insert Bit Pack & Socket Set CVM S2 modified tool steel.

1/4" to 3/8" Drive Socket  
TORX® 1/4" Bits: T10, T15, T20, T25, T27, T30  
5/16" to 3/8" Drive Socket  
lbs. TORX® 5/16" Bits: T40, T45, T50 .36

**Wiha TORX® Align Insert Bits and Power Bits**

**Wiha TORX® Align Coated Insert Bits PokitPak**

**Torx® Align Tapered For Snug Fit In Screw**

Highly resistant to wear and tear for a long tool life



Impact resistant modified chrome-vanadium-molybdenum, tool steel, hardened

**Made by Wiha - Production Quality**

Suitable for all applications for both manual and machine  
Hardness HRC 59-61



**79283 PokitPak - TORX® Align Insert Bits In Molded Case -**

**Set Includes 6 - 1/4" Insert Bits**

**TORX® Align:**

T10, T15, T20, T25, T30, T40

lbs. .12



10 bit pack

**715 TORX® Align Bits, 1/4"**

Item No.	Size	mm	pkg.	lbs.
71536	T6	25	10	.12
71537	T7	25	10	.12
71538	T8	25	10	.12
71541	T10	25	10	.12
71542	T15	25	10	.12
71543	T20	25	10	.12
71544	T25	25	10	.13
71545	T27	25	10	.13
71546	T30	25	10	.14
71547	T40	25	10	.15

(Also Known As Torx Wedge Fit)



10 bit pack

**747 TORX® Align Bits 1/4" Hex Drive, Length 2.0"/50mm**

Item No.	Size	mm	pkg.	lbs.
74711	T6	50	10	.18
74714	T7	50	10	.18
74717	T8	50	10	.18
74721	T9	50	10	.18
74724	T10	50	10	.18
74728	T15	50	10	.20
74732	T20	50	10	.22
74736	T25	50	10	.22
74739	T27	50	10	.22
74742	T30	50	10	.22

(Also Known As Torx Wedge Fit)

2 bit pack



**733 TORX® Align Insert Bit Packs, 1"**

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
73310	T6	25	.03
73311	T7	25	.03
73312	T8	25	.03
73313	T9	25	.03
73314	T10	25	.03
73315	T15	25	.03
73316	T20	25	.03
73317	T25	25	.03
73318	T27	25	.03
73319	T30	25	.03
73320	T40	25	.04

2 bit pack



**747 TORX® Align Power Bit Packs, 2"**

Item No.	Size	mm	lbs.
74760	T6	50	.05
74761	T7	50	.05
74762	T8	50	.05
74763	T9	50	.05
74764	T10	50	.05
74765	T15	50	.05
74766	T20	50	.06
74767	T25	50	.06
74768	T27	50	.06
74769	T30	50	.06



**74981 Power Bit Belt Pack With TORX® Align Bits**

Set includes the following 10 bits:

**TORX® Align:** T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

lbs. .28



## Wiha Security TORX® Insert Bits and Power Bits

### Security Torx®

Made by Wiha -  
Production  
Quality



Impact resistant modified  
CVM tool steel, hardened

Highly resistant  
to wear and  
tear for a  
long tool life

Suitable for all applications  
for both manual and machine  
Hardness HRC 59-61

10 bit pack



#### 701 Security TORX® Bits, 1/4"

Item	⚙	—	—	↩
No.	Size	mm	pkg.	lbs.
70127	T7s	25	10	.12
70128	T8s	25	10	.12
70129	T9s	25	10	.12
70135	T10s	25	10	.12
70139	T15s	25	10	.12
70142	T20s	25	10	.12
70148	T25s	25	10	.12
70160	T27s	25	10	.13
70163	T30s	25	10	.13
70168	T40s	25	10	.14



#### 701 Security TORX® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	⚙	—	↩
No.	Size	mm	lbs.
70150	T7s	25	.03
70151	T8s	25	.03
70152	T9s	25	.03
70153	T10s	25	.03
70154	T15s	25	.03
70155	T20s	25	.03
70156	T25s	25	.03
70157	T27s	25	.03
70158	T30s	25	.03
70159	T40s	25	.03



#### 725 Security TORX® Bits, 5/16"

Item	⚙	—	—	↩
No.	Size	mm	pkg.	lbs.
72514	T25s	35	10	.26
72515	T27s	35	10	.27
72516	T30s	35	10	.28
72542	T40s	35	10	.28
72547	T45s	35	10	.32
72552	T50s	35	10	.34
72557	T55s	35	10	.52
72558	T60s	35	10	.65



#### 725 Security TORX® Bits, 5/16" 2 Bit Pk.

Item	⚙	—	↩
No.	Size	mm	lbs.
72559	T25s	35	.26
72560	T27s	35	.27
72561	T30s	35	.28
72562	T40s	35	.28
72563	T45s	35	.29
72564	T50s	35	.30
72567	T55s	35	.32
72568	T60s	35	.35



#### 745 Protturn Security TORX® Power Bits 1/4" Hex Drive, Length 3.0"/75mm

Item	⚙	—	—	↩
No.	Size	mm	pkg.	lbs.
74566	T10s	75	5	.01
74568	T15s	75	5	.01
74570	T20s	75	5	.01
74572	T25s	75	5	.02
74574	T27s	75	5	.02
74576	T30s	75	5	.03




#### 705 Security TORX® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	⚙	—	—	↩
No.	Size	mm	pkg.	lbs.
70507	T7s	50	10	.18
70508	T8s	50	10	.18
70509	T9s	50	10	.18
70510	T10s	50	10	.19
70515	T15s	50	10	.19
70520	T20s	50	10	.21
70525	T25s	50	10	.23
70527	T27s	50	10	.23
70530	T30s	50	10	.23
70540	T40s	50	10	.23
70545	T45s	50	10	.33
70550	T50s	50	10	.37



#### 705 Security TORX® Power Bit Packs, 2"

Item	⚙	—	↩
No.	Size	mm	lbs.
70556	T7s	50	.07
70557	T8s	50	.07
70558	T9s	50	.07
70559	T10s	50	.07
70560	T15s	50	.07
70561	T20s	50	.07
70562	T25s	50	.07
70563	T27s	50	.07
70564	T30s	50	.07
70565	T40s	50	.07
70566	T45s	50	.08
70567	T50s	50	.08
70568	T55s	50	.09



#### 705 Security TORX® Power Bits 1/4" Hex Drive, Length 3.5"/90mm

Item	⚙	—	—	↩
No.	Size	mm	pkg.	lbs.
70533	T10s	90	5	.02
70534	T15s	90	5	.02
70535	T20s	90	5	.02
70536	T25s	90	5	.02
70537	T27s	90	5	.03
70538	T30s	90	5	.03
70539	T40s	90	5	.03



### Wiha Security TORX® Insert Bit & Power Bit Sets



**79247 Bit-Selector With Security TORX® Bits, Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:** lbs. .32

**Security TORX®:**  
T7s, T8s, T9s, T10s, T15s,  
T20s, T25s, T27s, T30s, T40s



**70190 Bit-Selector With Security TORX® Bits, Includes The Following 7 Insert Bits:**

<b>Security TORX®:</b>	
T7s, T8s, T9s,	lbs.
T10s, T15s, T20s, T25s	.21



**38009 Security TORX® Screwdriver with Wiha Powerhandle** lbs. .36

**Includes The Following 1/4" Bits:**

**Security TORX®:**  
T7s, T8s, T9s, T10s, T15s, T20s



**38010 Security TORX® Screwdriver with Wiha Powerhandle** lbs. .41

**Includes The Following 1/4" Bits:**

**Security TORX®:** T10s, T15s,  
T20s, T25s, T30s, T40s



**38047 Security TORX® SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.**

**Includes The Following 1/4" Bits:** lbs. .20

**Security TORX®:** T8s, T10s,  
T15s, T20s, T25s, T30s

Bit holder stainless steel, magnetic



**38046 Security TORX® Pop-Up Bit Screwdriver Set** Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle. lbs. .42

**Includes The Following 1/4" Bits:**

**TORX®:** T5, T6  
**Security TORX®:** T7s, T8s, T9s, T10s,  
T15s, T20s, T25s, T27s, T30s, T40s

Bit holder stainless steel, magnetic

75mm Bits



**38042 Security TORX® Pop-Up Bit Screwdriver Set** Wiha Cushion Grip handle, multi-component. Compact storage for 6 bits in the handle. lbs. .44

**Includes The Following 75mm 1/4" Bits:**

**Security TORX®:**  
T10s, T15s, T20s, T25s, T27s, T30s



**79447 XSelector Bit Set With Security TORX® Bits, Includes 1/4" Magnetic Bit Holder & The Following Bits:** lbs. .27

**Security TORX®:** T7s, T8s,  
T9s, T10s, T15s, T20s, T25s,  
T27s, T30s, T40s



**74987 Power Bit Belt Pack With Security TORX® Bits, Includes the following 10 bits:**

	T7s, T8s, T9s,
lbs.	T10s, T15s, T20s,
.29	T25s, T27s, T30s, T40s

### Wiha Security TORX® Power Blades & Holder



**760 Security TORX® Power Blades** S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.	Size	lbs.	pkg.
76008	T8s	.02	1
76009	T9s	.02	1
76010	T10s	.02	1
76015	T15s	.02	1
76020	T20s	.02	1
76025	T25s	.03	1
76027	T27s	.03	1
76030	T30s	.04	1
76040	T40s	.04	1



**76092 9 Piece Security TORX® Blade Set**

Item No.	lbs.	Set includes:
76092	.30	T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s



**76000 CentroFix Cushion Grip Blade Holder** Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26

## Wiha TORXPlus® Insert Bits and Power Bits

# TORXPlus®

Made by Wiha -  
Production Quality

Highly resistant  
to wear and  
tear for a  
long tool life

Impact resistant modified  
chrome-vanadium-molybdenum,  
tool steel, hardened

Suitable for all applications  
for both manual and  
machine Hardness  
HRC 59-61

 **TORXPlus®**  
 **Security Pentalobe**



10 bit  
pack

### 716 TORXPlus® Insert Bits, 1/4" Hex, 1" OAL

Item No.	Size	mm	pkg.	lbs.
71603	IP3	25	10	.12
71604	IP4	25	10	.12
71605	IP5	25	10	.12
71606	IP6	25	10	.12
71607	IP7	25	10	.12
71608	IP8	25	10	.12
71609	IP9	25	10	.12
71610	IP10	25	10	.12
71615	IP15	25	10	.12
71620	IP20	25	10	.12
71625	IP25	25	10	.12
71627	IP27	25	10	.13
71630	IP30	25	10	.13
71640	IP40	25	10	.15



2 bit  
pack

### 716 TORXPlus® Insert Bit Packs, 1"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
71631	IP3	25	.03
71632	IP4	25	.03
71633	IP5	25	.03
71634	IP6	25	.03
71635	IP7	25	.03
71636	IP8	25	.03
71637	IP9	25	.03
71638	IP10	25	.03
71639	IP15	25	.03
71641	IP20	25	.03
71642	IP25	25	.03
71643	IP27	25	.03
71644	IP30	25	.03
71645	IP40	25	.04



10 bit pack

### 746 TORXPlus® Power Bits, 1/4" Hex, 2" OAL

Item No.	Size	mm	pkg.	lbs.
74601	IP5	50	10	.18
74602	IP6	50	10	.18
74603	IP7	50	10	.18
74604	IP8	50	10	.18
74608	IP9	50	10	.18
74612	IP10	50	10	.20
74616	IP15	50	10	.20
74620	IP20	50	10	.20
74624	IP25	50	10	.20
74628	IP27	50	10	.25
74632	IP30	50	10	.25
74636	IP40	50	10	.25



### 74982 Power Bit Belt Pack With TORXPlus®

Bits Includes The Following 10 Bits:

lbs.	TORXPlus®: IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30
.28	

2 bit  
pack



### 746 TORXPlus® Power Bit Packs, 2"

Item No.	Size	mm	lbs.
74611	IP1	50	.05
74613	IP2	50	.05
74614	IP3	50	.05
74617	IP4	50	.05
74659	IP5	50	.05
74660	IP6	50	.05
74661	IP7	50	.05
74662	IP8	50	.05
74663	IP9	50	.05
74664	IP10	50	.05
74665	IP15	50	.05
74666	IP20	50	.06
74667	IP25	50	.06
74668	IP27	50	.06
74669	IP30	50	.06
74670	IP40	50	.06

## Wiha TORXPlus® Insert Bit Selectors



### 71690 Bit-Selector With TORXPlus® Bits Set Includes Magnetic 1/4" Bit Holder

& The Following 10 Bits:

lbs.	TORXPlus®: IP7, IP8, IP9, IP10, IP15, IP20, IP25
.31	IP27, IP30, IP40

### 71692 Bit-Selector With TORXPlus® Bits Set Includes Magnetic 1/4" Bit Holder

& The Following 10 Bits:

lbs.	TORXPlus®: IP3, IP4, IP5, IP6, IP7, IP8, IP9, IP10, IP15, IP20
.31	

### Wiha Security Pentalobe 5 Point Insert Bit



**716 Security Pentalobe 5 Point Insert Bits, 1/4" Hex, 1" OAL**

Item				
No.	Size	mm	pkg.	lbs.
71648	PLS8	25	1	.11
71650	PLS10	25	1	.11
71652	PLS15	25	1	.11
71654	PLS20	25	1	.12
71656	PLS25	25	1	.13
71657	PLS27	25	1	.13
71658	PLS30	25	1	.14
71660	PLS40	35	1	.14

### Wiha Ball End TORX® Bits



10 bit pack



**745 Ball End TORX® Bits. 1/4" Hex Drive, Length 2.0"/50mm**

Item				
No.	Size	mm	pkg.	lbs.
74524	T9	50	10	.18
74526	T10	50	10	.18
74528	T15	50	10	.18
74532	T20	50	10	.18
74534	T25	50	10	.18
74537	T27	50	10	.18
74539	T30	50	10	.18
74541	T40	50	10	.18

### Wiha TORX® MagicSpring Screw Holding Power Bits

Screw Holding TORX Bits

2 bit pack



Stainless rotary spring

**745 TORX® MagicSpring Screw Holding Power Bits, 1/4" Hex Drive, Length 2.0"/50mm**

Item				
No.	Size	mm	pkg.	lbs.
74552	T10	50	2	.05
74554	T15	50	2	.05
74555	T20	50	2	.05
74557	T25	50	2	.05
74562	T30	50	2	.05
74564	T40	50	2	.05

NOTES:

### Wiha Insert Security Pentalobe 5 Point XSelector



**79450 XSelector Bit Set With Security Pentalobe 5 Point Bits Includes Magnetic Bit Holder & The Following 7 Bits:**

	Security Pentalobe: PLS8,
lbs.	PLS10, PLS15, PLS20,
.24	PLS25, PLS27, PLS30

2 bit pack



**745 Ball End TORX® Power Bit Packs, 1"**

Item			
No.	Size	mm	lbs.
74505	T9	50	.05
74520	T10	50	.05
74522	T15	50	.05
74543	T20	50	.05
74545	T25	50	.06
74547	T27	50	.06
74549	T30	50	.08
74550	T40	50	.08

## Torx® Profiles



Torx®



Ball End Torx®



Security Torx®



TorxPlus®



Security Pentalobe 5 Point



## Wiha Phillips Insert Bits



### 711 Phillips Insert Bits, 1/4" - 10 Bit Packs

Item	+	—	↔	↔
No.	Size	mm	pkg.	lbs.
71100	0	25	10	.10
71101	1	25	10	.11
71102	2	25	10	.11
71103	3	25	10	.11

### 711 Phillips Insert Bit Bulk Packs, 1/4"

No.	Size	mm	pkg.	lbs.
71125	2	25	25 pc	.30
71150	2	25	50 pc	.62
71199	2	25	100 pc	1.20

### 725 Phillips Insert Contractor Grade, 1/4"

No.	Size	mm	pkg.	lbs.
72519	0	25	30 pc	.85
72521	1	25	30 pc	.85
72522	2	25	30 pc	.85
72523	3	25	30 pc	.85

# Phillips Bits

*The ideal multi-purpose bits for all around quality & performance*

**Made by Wiha - Production Quality**

Suitable for all applications for both manual and machine  
Hardness HRC 59-61



Impact resistant modified CVM, tool steel, hardened

Highly resistant to wear and tear for a long tool life



High grade CVM steel, hardened torsion zone to prevent uneven torque distribution DIN 3126 ISO 1173 with anti-camout ribs

## Wiha Phillips Insert Bit Packs

2 bit pack



### 711 Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel

Item	+	—	↔	↔
No.	Size	mm	lbs.	
71149	0	25	.03	
71151	1	25	.03	
71152	2	25	.03	
71153	3	25	.04	



### 71155 Phillips Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71155 Set includes the following bits:

↔ + Phillips:  
wt. .08 6 pieces 2 x 1" (25mm)

2 bit pack



### 777 Phillips Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item	+	—
No.	Size	mm
77707	#1 + #2	30
77708	#0 + #3	30



### 71154 Phillips Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

71154 Set includes the following bits:

↔ + Phillips:  
wt. .04 1, 2, 3 x 1" (25mm)




### 71056 Slotted/Phillips Insert Bit Packs, 1"

CVM S2 modified tool steel. Extra hard with natural finish, exact fit machined tips. 6 pc. bit pk.

71056 Set includes the following bits:

● Slotted:  
4.5, 5.5, 6.5 x 1" (25mm)

⊕ Phillips:  
1, 2, 3 x 1" (25mm) .08



10 bit pack



### 71132 Phillips Drywall Stop Bit

High grade Chrome-vanadium steel, through hardened. Ideal bit for drywall constructors. Blue ring prevents the screw from being recessed too deeply into the plasterboard.

Item	+	—	↔	↔
No.	Size	mm	lbs.	Pkg.
71132	2	25	.20	10





**Wiha Phillips 5/16" Insert Bits**

2 bit pack



**721 Phillips Insert Bit Packs, 1"**

CVM S2 modified tool steel. 5/16" Hex Drive.

Item				
No.	Size	mm	lbs.	
72102	2	32	.05	
72103	3	32	.06	
72104	4	32	.07	

**Wiha Phillips ACR Insert Bits**



**711 Phillips ACR Insert Bits, 1/4"**

Item				
No.	Size	mm	pkg.	lbs.
71126	1	25	10	.11

**Wiha Phillips Long Insert Bits**



**711 Phillips Long Insert Bits. 1/4" Hex Drive, Length 2.0"/50mm**

Item				
No.	Size	mm	pkg.	lbs.
71106	2	50	10	.25
71107	3	50	10	.27

2 bit pack



**711 Phillips Long Insert Bit Packs, 2"**

CVM S2 modified tool steel

Item				
No.	Size	mm	lbs.	
71166	2	50	.06	

**Wiha Phillips Power Bits**



10 bit pack

**741 Phillips Power Bits 1/4" Hex Drive, Length 2.0"/50mm**

Item				
No.	Size	mm	pkg.	lbs.
74100	00	50	10	.22
74102	0	50	10	.23
74103	1	50	10	.24
74112	2	50	10	.25
74124	3	50	10	.26



2 bit pack

**741 Phillips Power Bit Packs, 2"**

CVM S2 modified tool steel.

Item				
No.	Size	mm	lbs.	
74157	00	50	.06	
74158	0	50	.06	
74164	1	50	.06	
74165	2	50	.06	
74166	3	50	.06	



**74150 Phillips Power Bit Packs, 2" CVM**

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.

74150 Set includes the following bits:

			Phillips Sizes:
wt.	.09	1, 2, 3	x 2" (50mm)

10 bit pack



**741 Phillips Power Bits. 1/4" Hex Drive, Length 2.75"/70mm**

Item				
No.	Size	mm	pkg.	lbs.
74167	00	70	10	.29
74168	0	70	10	.29
74106	1	70	10	.29
74115	2	70	10	.37
74127	3	70	10	.41



2 bit pack

**739 Phillips Power Bits. 1/4" Hex Drive, Length 2.75"/70mm**

Item				
No.	Size	mm	pkg.	lbs.
73912	00	70	1	.29
73913	0	70	1	.29
73914	1	70	1	.29
73915	2	70	1	.37
73916	3	70	1	.41



**741 Phillips Power Bits 1/4" Hex Drive, Length 3.5"/90mm**

Item				
No.	Size	mm	pkg.	lbs.
74104	00	90	1	.32
74107	0	90	1	.32
74109	1	90	1	.34
74118	2	90	1	.47
74130	3	90	1	.53



**741 Phillips Power Bits 1/4" Hex Drive, Length 4.33"/110mm**

Item				
No.	Size	mm	pkg.	lbs.
74111	1	110	1	.40
74121	2	110	1	.56
74131	3	110	1	.65



**741 Phillips Power Bits 1/4" Hex Drive, Length 127mm/5"**

Item				
No.	Size	mm	pkg.	lbs.
74113	1	127	1	.04
74123	2	127	1	.06
74133	3	127	1	.07



**741 Phillips Power Bits 1/4" Hex Drive, Length 150mm/5.9"**

Item				
No.	Size	mm	pkg.	lbs.
74116	1	150	1	.05
74126	2	150	1	.07
74136	3	150	1	.09

**Wiha PokitPak Bit Set**



**71198 PokitPak - Slotted & Phillips Insert Bits In Molded Case -**

Set Includes 6 - 1/4" Insert Bits & lbs. Magnetic Bit Holder

.16 Slotted: 4.5, 6.0mm

Phillips: 0, 1, 2, 3

## Wiha Phillips Power Bit Packs



**714 Phillips Double End Bits**  
1/4" Hex Drive, Length 2.36"/60mm

Item	+	+	—	—	↵	↵
No.	Size	Size	mm	mm	pkg.	lbs.
71404	1	x 1	60	10	.31	
71424	3	x 3	60	10	.32	



2 bit pack



**714 Phillips Double End Power Bit Packs**, 60mm OAL

Item	+	+	—	—	↵	↵
No.	Size	Size	mm	lbs.		
71464	1	+ 1	60	.07		
71465	2	+ 2	60	.07		
71466	3	+ 3	60	.07		



**743 Slotted & Phillips Double End Bits**, 1/4" Hex Drive, Length 2.36"/60mm

Item	↑	⊕	—	—	↵	↵
No.	mm	Size	mm	pkg.	lbs.	
74303	4.5	x 1	60	10	.22	
74306	5.5	x 2	60	10	.30	
74309	7.0	x 3	60	10	.32	



2 bit pack



**743 Slotted/Phillips Double End Power Bit Packs**, 60mm OAL

Item	⊕	⊕	—	—	↵	↵
No.	mm	Size	mm	lbs.		
74304	4.5	+ 1	60	.07		
74308	5.5	+ 2	60	.07		
74310	7.0	+ 3	60	.07		

## Wiha Stainless Steel Phillips Insert Bits & Power Bits



**711 Stainless Steel Phillips Insert Bits**, 1/4"

Item	+	—	—
No.	Size	mm	pkg.
71133	1	25	1
71135	3	25	1



**704 Stainless Steel Phillips Power Bits**, 1/4"

Item	+	—	—
No.	Size	mm	pkg.
70401	1	50	1
70405	3	50	1

## Terminal Block Xeno Bits



10 bit pack



**714 Xeno Combination Terminal Block Power Bits**, 1/4" Hex Drive, OAL 2.0"/50mm

Item	⊕	—	—	↵	↵
No.	Size	mm	pkg.	lbs.	
71452	1	50	10	.24	
71453	2	50	10	.25	

2 bit pack



**714 Xeno Combination Terminal Block Power Bit Packs**, 2" CVM S2 modified tool steel

Item	⊕	—	↵
No.	Size	mm	lbs.
71455	1	50	.06
71456	2	50	.06

## Wiha Phillips Power Blades & Power Blade Holder



**760 Phillips Power Blades**

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item	⊕	↵	—
No.	Size	lbs.	pkg.
76041	0	.01	1
76042	1	.02	1
76043	2	.03	1
76044	3	.04	1



**76094 4 Piece Phillips Blade Set**

Item	↵	Set includes:
No.	lbs.	Phillips: #0, 1, 2,
76094	.17	3 x 90mm



**76000 CentroFix Cushion Grip Blade Holder**

Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item	⊕	—	—	↵	↵	↵
No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26


# Hex Bits

*The ideal multi-purpose bits for all around quality & performance*


Made by Wiha - Production Quality

Impact resistant modified CVM, tool steel, hardened

Suitable for all applications for both manual and machine  
Hardness HRC 59-61



Highly resistant to wear and tear for a long tool life



## Hex Inch & Metric Insert Bits

2 bit pack



### 713 Hex Inch Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item				
No.	Inch	mm	lbs.	
71359	.050	25	.03	
71360	1/16	25	.03	
71361	5/64	25	.03	
71362	3/32	25	.03	
71363	7/64	25	.03	
71364	1/8	25	.03	
71365	9/64	25	.03	
71366	5/32	25	.04	
71367	3/16	25	.04	
71368	7/32	25	.04	
71369	1/4	25	.04	
71373	5/16	25	.05	
71387	3/8	25	.06	

### 733 Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item				
No.	mm	mm	lbs.	
73301	1.5	25	.03	
73302	2.0	25	.03	
73303	2.5	25	.03	
73304	3.0	25	.03	
73305	4.0	25	.03	
73306	5.0	25	.03	
73307	6.0	25	.04	
73308	8.0	25	.05	
73309	10.0	25	.06	

2 bit pack



### 777 Hex Inch Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item				
No.	Inch	mm		
77723	3/32 + 7/64"	30		
77724	1/8 + 9/64"	30		
77725	5/32 + 3/16"	30		
77726	7/32 + 1/4"	30		

### 777 Hex Metric Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item				
No.	Metric	mm		
77719	2.0 + 2.5mm	30		
77720	3.0 + 4.0mm	30		
77721	5.0 + 6.0mm	30		

## Wiha Hex Inch & Metric Insert Bits



10 bit pack

### 713 Hex Inch Insert Bits, 1/4"

Item				
No.	Inch	mm	pkg.	lbs.
71329	.050	25	10	.12
71326	1/16	25	10	.12
71328	5/64	25	10	.12
71330	3/32	25	10	.12
71333	7/64	25	10	.12
71336	1/8	25	10	.12
71339	9/64	25	10	.12
71342	5/32	25	10	.12
71345	3/16	25	10	.13
71348	7/32	25	10	.13
71351	1/4	25	10	.13
71353	5/16	25	10	.20
71356	3/8	25	10	.25

### 725 Hex Inch Insert Contractor Grade, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
72502	1/16	25	30 pc	.85
72503	5/64	25	30 pc	.85
72504	3/32	25	30 pc	.85
72506	7/64	25	30 pc	.85
72507	1/8	25	30 pc	.85
72508	9/64	25	30 pc	.85
72509	5/32	25	30 pc	.85
72511	3/16	25	30 pc	.85
72512	7/32	25	30 pc	.85
72513	1/4	25	30 pc	.85



### 713 Hex Metric Insert Bits, 1/4"

Item				
No.	mm	mm	pkg.	lbs.
71303	1.5	25	10	.12
71306	2.0	25	10	.12
71308	2.5	25	10	.12
71309	3.0	25	10	.12
71312	4.0	25	10	.12
71315	5.0	25	10	.14
71318	6.0	25	10	.14
71321	8.0	25	10	.20
71324	10.0	25	10	.27

### 725 Hex Metric Insert Contractor Grade, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
72582	2.0	25	30 pc	.85
72583	2.5	25	30 pc	.85
72584	3.0	25	30 pc	.85
72585	4.0	25	30 pc	.85
72586	5.0	25	30 pc	.85
72587	6.0	25	30 pc	.85



### 71397 Hex Metric Insert Bit Packs, 1" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71397 Set includes the following bits:

wt. .21	2.0, 2.5, 3.0, 4.0, 5.0, 6.0		

### Hex Metric Long Insert Bit On 5/16"



### 72388 Hex Metric Bit On 5/16" Stock

Item				
No.	mm	mm	pkg.	lbs.
72388	12.0	75	10	.14



### 71396 Hex Inch Insert Bit Packs, 1"

6 pc. bit pack.





71396 Set includes the following bits:

wt. .13	1/16, 3/32, 1/8, 5/32	3/16, 1/4" x 1" (25mm)	

## Wiha Hex Inch & Metric Power Bits







**743 Hex Inch Power Bits. 1/4" Hex Drive, Length 2.0"/50mm**

Item				
No.	Inch	mm	pkg.	lbs.
74311	3/32	50	10	.30
74312	7/64	50	10	.30
74313	1/8	50	10	.30
74314	9/64	50	10	.30
74315	5/32	50	10	.30
74316	3/16	50	10	.30
74317	7/32	50	10	.30
74318	1/4	50	10	.30







**743 Hex Metric Power Bits. 1/4" Hex Drive, Length 2.0"/50mm**

Item				
No.	mm	mm	pkg.	lbs.
74325	2.5	50	10	.25
74330	3.0	50	10	.25
74340	4.0	50	10	.25
74350	5.0	50	10	.25
74360	6.0	50	10	.25
74380	8.0	50	10	.38








**743 Hex Inch Power Bits 1/4" Hex Drive, Length 2.75"/70mm**

Item				
No.	Inch	mm	pkg.	lbs.
74342	3/32	70	10	.36
74343	7/64	70	10	.36
74344	1/8	70	10	.36
74345	9/64	70	10	.36
74346	5/32	70	10	.36
74348	7/32	70	10	.36
74349	1/4	70	10	.36







**743 Hex Metric Power Bits 1/4" Hex Drive, Length 2.75"/70mm**

Item				
No.	mm	mm	pkg.	lbs.
74351	2.0	70	10	.36
74352	2.5	70	10	.36
74353	3.0	70	10	.36
74354	4.0	70	10	.36
74355	5.0	70	10	.36
74356	6.0	70	10	.36
74357	8.0	70	10	.36






**743 Hex Inch Power Bit Packs, 2"**

Item			
No.	Inch	mm	lbs.
74381	3/32	50	.07
74382	7/64	50	.07
74383	1/8	50	.07
74384	9/64	50	.07
74385	5/32	50	.07
74386	3/16	50	.07
74387	7/32	50	.07
74388	1/4	50	.07








**743 Hex Metric Power Bit Packs, 2"**

Item			
No.	mm	mm	lbs.
74361	2.5	50	.07
74362	3.0	50	.07
74363	4.0	50	.07
74364	5.0	50	.07
74365	6.0	50	.07
74366	8.0	50	.09







**739 Hex Inch Power Bits 1/4" Hex Drive, Length 2.75"/70mm**

Item				
No.	Inch	mm	pkg.	lbs.
73919	3/32	70	1	.36
73920	7/64	70	1	.36
73921	1/8	70	1	.36
73922	9/64	70	1	.36
73923	5/32	70	1	.36
73924	3/16	70	1	.36
73925	7/32	70	1	.36
73926	1/4	70	1	.36







**739 Hex Metric Power Bits 1/4" Hex Drive, Length 2.75"/70mm**

Item				
No.	mm	mm	pkg.	lbs.
73928	2.0	70	1	.36
73929	2.5	70	1	.36
73930	3.0	70	1	.36
73931	4.0	70	1	.36
73932	5.0	70	1	.36
73933	6.0	70	1	.36
73934	8.0	70	1	.36







**743 Hex Metric Power Bits 1/4" Hex Drive, Length 3.5"/90mm**

Item				
No.	mm	mm	pkg.	lbs.
74332	2.0	90	1	.40
74333	2.5	90	1	.40
74334	3.0	90	1	.40
74335	4.0	90	1	.40
74336	5.0	90	1	.40
74337	6.0	90	1	.40

## Wiha Ball End Hex Inch Insert Bits






**717 Ball End Hex Inch Insert Bits, 1/4"**

Item				
No.	Inch	mm	pkg.	lbs.
71701	3/32	25	10	.12
71702	7/64	25	10	.12
71703	1/8	25	10	.12
71704	9/64	25	10	.12
71705	5/32	25	10	.12
71706	3/16	25	10	.13
71707	7/32	25	10	.14
71708	1/4	25	10	.15






**717 Ball End Hex Inch Insert Bit Packs, 1"**

Item			
No.	Inch	mm	lbs.
71711	3/32	25	.03
71712	7/64	25	.03
71713	1/8	25	.03
71714	9/64	25	.03
71715	5/32	25	.04
71716	3/16	25	.04
71717	7/32	25	.04
71718	1/4	25	.04



**717 Ball End Hex Metric Insert Bits 1/4" Hex Drive, Length 1.5"/38mm**

Item			
No.	mm	mm	pkg.
71719	1.5	38	2
71720	2.0	38	2
71721	2.5	38	2
71722	3.0	38	2
71723	4.0	38	2
71724	5.0	38	2
71725	6.0	38	2



### Wiha Security Hex Insert Bits



#### 719 Security Hex Inch Insert Bits, 1/4"

Item					
No.	Inch	mm	pkg.	lbs.	
71930	5/64	25	10	.12	
71932	3/32	25	10	.12	
71934	7/64	25	10	.12	
71936	1/8	25	10	.12	
71938	9/64	25	10	.12	
71940	5/32	25	10	.12	
71955	3/16	25	10	.13	
71956	7/32	25	10	.14	
71960	1/4	25	10	.15	



#### 719 Security Hex Inch Insert Bit Packs, 1"


CVM S2 modified tool steel.

Item				
No.	Inch	mm	lbs.	
71970	5/64	25	.03	
71971	3/32	25	.03	
71972	7/64	25	.03	
71973	1/8	25	.03	
71974	9/64	25	.03	
71975	5/32	25	.03	
71976	3/16	25	.04	
71977	7/32	25	.04	
71978	1/4	25	.04	



#### 719 Security Hex Metric Insert Bits, 1/4"

Item					
No.	mm	mm	pkg.	lbs.	
71939	2.0	25	10	.12	
71941	2.5	25	10	.12	
71942	3.0	25	10	.12	
71943	4.0	25	10	.12	
71944	5.0	25	10	.15	
71945	6.0	25	10	.15	
71946	8.0	25	10	.20	




#### 719 Security Hex Metric Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item				
No.	mm	mm	lbs.	
71979	2.0	25	.03	
71980	2.5	25	.03	
71981	3.0	25	.03	
71982	4.0	25	.03	
71983	5.0	25	.04	
71984	6.0	25	.04	
71985	8.0	25	.05	

### MagicRing Insert & Power Bits



#### 713 MagicRing Metric Insert Bits, 1/4"

Item					
No.	mm	mm	pkg.	lbs.	
71304	3.0	25	1	.01	
71307	4.0	25	1	.01	
71310	5.0	25	1	.01	
71311	6.0	25	1	.01	



#### 743 MagicRing Metric Power Bits, 1/4"

Item					
No.	mm	mm	pkg.	lbs.	
74301	3.0	50	1	.02	
74305	4.0	50	1	.02	
74307	5.0	50	1	.03	
74319	6.0	50	1	.03	



#### 713 MagicRing Inch Insert Bits, 1/4"

Item					
No.	Inch	mm	pkg.	lbs.	
71343	1/8	25	1	.01	
71346	9/64	25	1	.01	
71349	5/32	25	1	.01	
71352	3/16	25	1	.01	
71354	7/32	25	1	.01	



#### 743 MagicRing Inch Power Bits, 1/4"

Item					
No.	Inch	mm	pkg.	lbs.	
74369	1/8	50	1	.02	
74371	9/64	50	1	.02	
74373	5/32	50	1	.02	
74375	3/16	50	1	.03	
74379	1/4	50	1	.03	

### Wiha Stainless Steel Hex Metric Insert Bits



#### 701 Stainless Steel Hex MM Insert Bits, 1/4"


Item				
No.	mm	mm	pkg.	
70175	5.0	25	1	
70176	6.0	25	1	

### 1/4" Ball End MagicRing Bits



#### 717 MagicRing Metric Power Ball End Bits

Item					
No.	mm	mm	pkg.	lbs.	
71730	3.0	50	1	.02	
71740	4.0	50	1	.02	
71750	5.0	50	1	.03	
71760	6.0	50	1	.03	



#### 717 MagicRing Inch Power Ball End Bits

Item					
No.	Inch	mm	pkg.	lbs.	
71726	1/8	50	1	.02	
71728	9/64	50	1	.02	
71732	5/32	50	1	.02	
71734	3/16	50	1	.03	
71736	7/32	50	1	.03	
71738	1/4	50	1	.03	

### Screw Holding Hex Bits



## Wiha Hex Inch & Metric Bit Sets



**79246 Bit-Selector With Hex Inch Bits Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:** lbs. .32

**Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

**79256 Bit-Selector With Hex Metric Bits Set Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:** lbs. .30

**Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm



**38058 Hex Inch SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.** lbs. .22

**Includes the following 1/4" bits:**

**Hex Inch:** 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"



**38057 Hex Metric SoftFinish® CushionGrip Stubby Bit Holder with Wiha cushion grip handle and CVM tool steel shaft.** lbs. .21

**Includes The Following 1/4" Bits:**

**Hex Metric:** 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm



**79446 XSelector Bit Set With Hex Inch Bits Set Includes Magnetic Bit Holder & The Following 10 Bits:** lbs. .27

**Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

Bit holder stainless steel, magnetic



**38049 Hex Inch & Metric Pop-Up Bit Screwdriver Set** Cushion Grip handle, multi-component. Compact storage holds 12 bits.

**Includes The Following 1/4" Bits:**

**Hex Inch:** 5/64, 3/32, 1/8, 5/32, 3/16, 1/4"

**lbs. Hex Metric:** 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm



**74986 Power Bit Belt Pack With Inch & Metric Hex Bits Set Includes The Following 10 Bits:** lbs. .34

**Inch:** 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

**Metric:** 3.0, 4.0, 5.0, 6.0mm

## Wiha Security Hex Inch & Metric Bit Sets



**79266 Bit-Selector With Security Hex Inch Bits Set Includes Magnetic 1/4" ClicFix Bit Holder & The Following 9 Bits:**

**Security Hex Inch:** lbs. 5/64, 3/32, 7/64, 1/8, 9/64, .32 5/32, 3/16, 7/32, 1/4"



**38014 Security Hex Inch Multi-Bit Screwdriver, 6 Pc. Set With Wiha Powerhandle & CVM steel, hardened shaft.** lbs. .40

**Set includes the following 1/4" bits:**

**Security Hex:**

3/32, 1/8, 5/32, 3/16, 7/32"



**71998 PokitPak - Security Hex Inch Insert Bits In Molded Case - Set Includes 6 - 1/4" Insert Bits** lbs. .12

**Inch Security Hex:**

3/32, 7/64, 1/8, 9/64, 5/32, 3/16"



**71995 PokitPak - Security Hex Metric Insert Bits In Molded Case - Set Includes 6 - 1/4" Insert Bits** lbs. .21

**Metric Security Hex:**

2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

## Wiha Insert Bit Blister Pack



**72596 10 Pack Hex Inch Insert Bit Pack**

CVM S2 modified tool steel.

**Hex Inch:** lbs.

1/16, 5/64, 3/32, 7/64, 1/8, .16

9/64, 5/32, 3/16, 7/32, 1/4"

**Wiha Security Hex Inch & Metric Power Blades** 




**760 Hex Inch Power Blades**

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.	Inch	lbs.	pkg.
76045	1/16	.01	1
76005	5/64	.01	1
76006	3/32	.02	1
76007	7/64	.02	1
76014	1/8	.03	1
76016	9/64	.03	1
76017	5/32	.04	1
76018	3/16	.04	1
76019	7/32	.05	1
76021	1/4	.06	1

**Wiha Ball End Hex Inch & Metric Bit Sets**



**79276 Bit-Selector With Ball End Hex Inch Bits Includes Magnetic 1/4" Bit Holder & The Following 8 Bits:**  lbs. .30

**Ball End Hex Inch:** 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



**38056 Ball End Hex SoftFinish® CushionGrip Stubby Bit Holder** with Wiha cushion grip handle and CVM tool steel shaft.

**Set Includes The Following 1/4" Bits:**  lbs. **Ball End Hex Inch:** 1/8, 9/64, 5/32, .21 3/16, 7/32, 1/4"

**Wiha MagicRing Hex Inch & Metric Bit Sets**



**74999 Power Bit Belt Pack With Ball End Screw Holding Hex Bits**  lbs. .37

**Inch:** 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"  
**Metric:** 3.0, 4.0, 5.0, 6.0mm

**Wiha Security Hex Inch & Metric Power Blades**



**760 Security Hex Metric Power Blades**

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item No.	mm	lbs.	pkg.
76001	2.5	.02	1
76002	3.0	.02	1
76003	4.0	.03	1
76004	5.0	.04	1



**760 Security Hex Inch Power Blades**  
OAL 90mm/3.5".


Item No.	Inch	lbs.	pkg.
76046	5/64	.01	1
76047	3/32	.02	1
76048	7/64	.02	1
76049	1/8	.03	1
76050	9/64	.03	1
76051	5/32	.04	1
76052	3/16	.04	1
76053	7/32	.05	1
76054	1/4	.06	1

**Wiha Power Blade Holder**



**76000 CentroFix Cushion Grip Blade Holder** Wiha-SoftFinish® impact resistant, with roll off protection. Quick release bit holder with magnet.

Item No.	mm	mm	Inch	mm	Inch	lbs.
76000	6.0	149	5.9	34.6	1.36	.26



**76090 4 Piece Security Hex Blade Set**

Item No.	lbs.	Metric:
76090	.12	4.0, 5.0 x 90mm



**76096 10 Piece Security Hex Blade Set**

Item No.	lbs.	Inch:
76096	.32	1/16*, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 90mm

\*1/16" Standard Inch Hex Only

**Wiha Square Power Blades**



**760 Square Power Blades**  
OAL 90mm/3.5".

Item No.	Size	lbs.	pkg.
76056	1	.02	1
76057	2	.03	1
76058	3	.04	1



**76095 3 Piece Square Blade Set**


Item No.	lbs.	Square:
76095	.11	#1, 2, 3 x 90mm

## Square Insert & Power Bits

### Square Bits



CVM, tool steel, hardened





 Square

Suitable for all applications for both manual & machine hardness HRC 59-61







10 bit pack

#### 718 Square Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71801	1	25	10	.11
71802	2	25	10	.11
71803	3	25	10	.11

#### 30 Piece Contractor Grade Bits

#### 725 Square Insert Contractor Grade, 1/4"




Item				
No.	mm	mm	pkg.	lbs.
72537	1	25	30 pc	.85
72538	2	25	30 pc	.85
72539	3	25	30 pc	.85

2 bit pack



#### 718 Square Insert Bit Packs, 1"

CVM S2 modified tool steel.


Item			
No.	Size	mm	lbs.
71851	1	25	.03
71852	2	25	.03
71853	3	25	.03



#### 71854 Square Insert Bit Packs, 1"

CVM S2 modified tool steel. 3 pc. bit pack



71854 Set includes the following bits:

 Square: wt. .04 1, 2, 3 x 1" (25mm)

2 bit pack







#### 777 Square Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item		
No.	Size	mm
77712	#1 + #2	30
77713	#0 + #3	30



10 bit pack

#### 748 Square Power Bits, 1/4" Hex Drive, Length 2.0"/50mm




Item				
No.	Size	mm	pkg.	lbs.
74813	1	50	10	.20
74816	2	50	10	.20
74819	3	50	10	.20

2 bit pack



#### 748 Square Power Bit Packs, 2"


CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
74860	1	50	.05
74861	2	50	.05
74862	3	50	.05



#### 74890 Square Power Bit Packs, 2" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.


74890 Set includes the following bits:

 Square: wt. .08 1, 2, 3 x 2.0" (50mm)






#### 74895 Square Power Bit Packs, 2.0" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

74895 Set includes the following bits:

 Square: 2 of each sizes wt. 1.2 1, 2, 3 x 2.0" (50mm)



#### 748 Square Power Bit, 1/4" Hex Drive, Length 3.5"/90mm CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
74811	1	90	.08
74812	2	90	.08
74814	3	90	.08

## Slotted Bits

The ideal multi-purpose bits for all around quality & performance

Made by Wiha - Production Quality

Highly resistant to wear and tear for a long tool life






Impact resistant modified CVM, tool steel, hardened

 Slotted







10 bit pack

#### 710 Slotted Insert Bits, 1/4" Hex Drive, Length 25mm/.984"

Item					
No.	mm	Inch	mm	Inch	pkg.
71001	4.5	.177	0.6	.024	10
71004	5.5	.216	0.8	.030	10
71002	6.5	.255	1.2	.039	10
71003	8.0	.315	1.6	.063	10

#### 30 Piece Contractor Grade Bits





#### 725 Slotted Insert Contractor Grade, 1/4"

Item				
No.	mm	mm	pkg.	lbs.
72534	4.5	25	30 pc	.85
72535	5.5	25	30 pc	.85
72536	6.0	25	30 pc	.85

2 pc. bit pack!



#### 710 Slotted Insert Bits, 1/4" Hex Drive, Length 1.54"/39mm 2 pc. Bit pack.

Item					
No.	mm	Inch	mm	Inch	pkg.
71030	3.0	.118	0.5	.020	2
71031	3.5	.139	0.6	.024	2
71032	4.0	.157	0.8	.031	2
71034	5.5	.216	1.0	.039	2
71035	6.5	.255	1.2	.047	2
71036	8.0	.315	1.6	.063	2

2 bit pack



#### 777 Slotted Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item		
No.	Size	mm
77715	3.0 + 4.5mm	30
77716	4.0 + 6.0mm	30
77717	5.5 + 6.5mm	30



**Wiha Slotted Insert & Power Bits**



**720 Slotted Insert Bits. 5/16" Hex Drive, Length 41mm**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	Inch	mm	pkg.	lbs.
72049	8.0	.315	1.6	10	.31
72050	10.0	.393	1.6	10	.46
72051	12.0	.472	2.0	10	.56



**720 Slotted Insert Bit Packs, 1" CVM S2 modified tool steel. 5/16" Hex Drive.**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	mm	Inch	mm	lbs.
72031	1.6	8.0	.315	41	.08
72039	1.6	10.0	.393	41	.10
72047	2.0	12.0	.472	41	.12



**740 Slotted Power Bits, 1/4" Hex Drive, Length 2.75"/70mm**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	Inch	mm	Inch	pkg.
74033	2.5	.098	0.4	.015	10
74034	3.0	.118	0.5	.020	10
74035	3.5	.139	0.6	.024	10
74036	4.0	.157	0.8	.020	10
74039	5.5	.216	1.0	.032	10
74041	6.5	.255	1.2	.039	10



**739 Slotted Power Bits, 1/4" Hex Drive, Length 2.75"/70mm 2 bit pack**

Item	⌚	⌚	⌚	⌚
No.	mm	Inch	mm	Inch
73905	2.5	.098	0.4	.015
73906	3.0	.118	0.5	.020
73907	3.5	.139	0.6	.024
73908	4.0	.157	0.8	.020
73909	5.5	.216	1.0	.032
73910	6.5	.255	1.2	.039



**710 Slotted Insert Bit Packs, 1" CVM S2 modified tool steel.**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	mm	Inch	mm	lbs.
71051	0.6	4.5	.177	25	.03
71052	0.8	5.5	.216	25	.03
71053	1.2	6.0	.255	25	.03
71054	1.6	8.0	.315	25	.03



**71055 Slotted Insert Bit Packs, 1" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	mm	Inch	mm	lbs.
71055	4.5	5.5	6.0	1"	(25mm)



**740 Slotted Power Bits, 1/4" Hex Drive, Length 2.0"/50mm 10pk. weight .20 lbs.**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	Inch	mm	Inch	pkg.
74003	3.0	.118	0.5	.020	10
74006	3.5	.139	0.6	.024	10
74009	4.0	.157	0.5	.020	10
74010	4.0	.157	0.8	.030	10
74012	4.5	.177	0.6	.024	10
74015	5.5	.216	0.8	.032	10
74018	6.5	.255	1.2	.039	10
74021	8.0	.315	1.2	.039	10
74023	8.0	.315	1.6	.063	10




**740 Slotted Power Bit Packs, 2" CVM S2 modified tool steel.**

Item	⌚	⌚	⌚
No.	mm	mm	lbs.
74061	3.0	50	.05
74062	3.5	50	.05
74063	4.0	50	.05
74064	4.0	50	.05
74065	4.5	50	.05
74066	5.5	50	.05
74067	6.5	50	.06
74068	8.0	50	.08
74069	8.0	50	.08



**74050 Slotted Power Bit Packs, 2" CVM S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	mm	Inch	mm	lbs.
74050	4.5	5.5	6.5	2"	(50mm)



**743 Slotted and Phillips Double End Bits, 1/4" Hex Drive, Length 2.36"/60mm**

Item	⌚	⌚	⌚	⌚	⌚
No.	mm	Size	mm	pkg.	lbs.
74303	4.5	x 1	60	10	.22
74306	5.5	x 2	60	10	.30
74309	7.0	x 3	60	10	.32

**Wiha Slotted Power Blades**



**760 Slotted Power Blades**  
S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item	⌚	⌚	⌚
No.	mm	lbs.	pkg.
76035	2.5	.02	1
76036	3.0	.02	1
76037	4.5	.03	1
76038	5.5	.03	1
76039	6.0	.04	1



**76093 5 Piece Slotted Blade Set**

Item	⌚	⌚	⌚
No.	lbs.	Slotted:	Set includes:
76093	.16	2.5, 3.0, 4.5, 5.5, 6.0mm x 90mm	

## Pozidriv® Bits

The ideal multi-purpose tools to meet production requirements for both quality and performance

Impact resistant modified CVM, tool steel, hardened



Suitable for all applications for both manual and machine  
Hardness HRC 59-61

### PoziDriv® Insert & Power Bits



#### 712 Pozidriv® Insert Bits, 1/4"

Item	No.	Size	mm	pkg.	lbs.
	71200	0	25	10	.10
	71201	1	25	10	.10
	71202	2	25	10	.10
	71203	3	25	10	.10



#### 742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.	lbs.
	74203	1	50	10	.24
	74212	2	50	10	.25
	74221	3	50	10	.26



#### 712 Pozidriv® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item	No.	Size	mm	lbs.
	71250	0	25	.03
	71251	1	25	.03
	71252	2	25	.03
	71253	3	25	.04



#### 742 Pozidriv® Power Bit Packs, 2"

CVM S2 modified tool steel.

Item	No.	Size	mm	lbs.
	74261	1	50	.06
	74262	2	50	.06
	74263	3	50	.07



#### 71254 Pozidriv® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 3 pc. bit pack.


71254 Set includes the following bits:

Pozidriv®:  
wt. .04 1, 2, 3 x 1" (25mm)



#### 777 Pozidriv® Double End Insert Bit Packs, 1/4" CVM S2 modified tool steel

Item	No.	Size	mm
	77710	#1 + #2	30



#### 742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Size	mm	pkg.
	74201	0	70	10
	74205	1	70	10
	74214	2	70	10



#### 739 Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.75"/70mm 2 bit pack

Item	No.	Size	mm	pkg.
	73901	0	70	1
	73902	1	70	1
	73903	2	70	1



#### 742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 3.5"/90mm Single Pack

Item	No.	Size	mm	pkg.	lbs.
	74231	1	90	1	.03
	74232	2	90	1	.04
	74233	3	90	1	.05



#### 742 Pozidriv® Power Bits. 1/4" Hex Drive, Length 3.5"/90mm 10 Bit Pack

Item	No.	Size	mm	pkg.	lbs.
	74236	1	90	10	.34
	74237	2	90	10	.46
	74238	3	90	10	.53

### Wiha Stainless Steel Pozidriv® Insert & Power Bits



#### 712 Stainless Steel Pozidriv® Insert Bits, 1/4"

Item	No.	Size	mm	pkg.
	71243	3	25	1



#### 704 Stainless Steel Pozidriv® Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.
	70410	3	50	1


### Wiha Pozidriv® Power Blades



#### 760 Pozidriv® Power Blades

S2 modified tool steel. Hardened & tempered to HRC 60. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item	No.	Size	lbs.	pkg.
	76011	1	.03	1
	76012	2	.04	1
	76013	3	.04	1




#### 76091 3 Piece Pozidriv® Blade Set

Item	No.	lbs.	Pozidriv®: #1, 2,
	76091	.12	3 x 90mm

# Specialty

Highly resistant to wear and tear for a long tool life







 Tri-Wing

## Tri-Wing Bits



10 bit pack




### 719 Triwing Insert Bits, 1/4"/25mm

Item				
No.	Size	mm	pkg.	lbs.
71900	0	25	10	.10
71901	1	25	10	.10
71902	2	25	10	.10
71903	3	25	10	.10
71904	4	25	10	.13
71905	5	25	10	.13



2 bit pack

### 719 Tri-Wing Insert Bit Packs, 1"


Item			
No.	Size	mm	lbs.
71949	0	25	.03
71950	1	25	.03
71951	2	25	.03
71952	3	25	.03
71953	4	25	.03
71913	5	25	.04



### 71954 Tri-Wing Insert Bit Packs, 1"

6 pc. bit pack.

**71954 Set includes the following bits:**

 Triwing: 0, 1, 2, wt. .07 3, 4, 5 x 1" (25mm)

# Bits







 Torq Set

Suitable for all applications for both manual & machine Hardness HRC 59-61

10 bit pack






### 749 Tri-Wing Power Bits, 1/4"/50mm

Item				
No.	Size	mm	pkg.	lbs.
74901	3	50	10	.24
74903	5	50	10	.24
74904	6	50	10	.46

2 bit pack



### 749 Tri-Wing Power Bit Packs, 2"




Item			
No.	Size	mm	lbs.
74961	4	50	.06
74962	5	50	.06
74963	6	50	.10

## Wiha Tri-Wing Power Blades




### 760 Tri-Wing Power Blades

S2 modified tool steel. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	Size	lbs.	pkg.
76031	1	.02	1
76032	2	.02	1
76033	3	.03	1
76034	4	.04	1



### 76088 4 Piece Tri-Wing Blade Set





Item		Set includes:
No.	lbs.	Tri-Wing: #1, 2,
76088	.16	3, 4 x 90mm

## Torq Set Bits



10 bit pack





### 719 Torq Set Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71921	0	25	10	.10
71922	1	25	10	.10
71923	2	25	10	.10
71924	3	25	10	.10
71907	4	25	10	.10
71909	5	25	10	.10
71906	6	25	10	.10
71908	8	25	10	.13
71910	10	25	10	.13



10 bit pack

### 749 Torq Set Power Bits, 1/4"/50mm




Item				
No.	Size	mm	pkg.	lbs.
74911	4	50	10	.03
74912	5	50	10	.03
74913	6	50	10	.03
74914	8	50	10	.04
74915	10	50	10	.04



2 bit pack

### 719 Torq Set Insert Bit Packs, 1"

CVM S2 modified tool steel.




Item			
No.	Size	mm	lbs.
71911	4	25	.03
71912	5	25	.03
71957	6	25	.03
71958	8	25	.04
71959	10	25	.04



2 bit pack

### 749 Torq Set Power Bit Packs, 2"

CVM S2 modified tool steel.

Item			
No.	Size	mm	lbs.
74964	4	50	.06
74965	5	50	.06
74966	6	50	.06
74967	8	50	.07
74968	10	50	.07



## Specialty Bits

Highly resistant to wear & tear for a long tool life

Spanner

Suitable for all applications for both manual and machine  
Hardness HRC 59-61



### Spanner Bits

10 bit pack

#### 719 Spanner Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71914	4	25	10	.11
71916	6	25	10	.12
71918	8	25	10	.12
71920	10	25	10	.12



2 bit pack

#### 719 Spanner Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item				
No.	Size	mm	lbs.	
71963	4	25	.03	
71964	6	25	.03	
71965	8	25	.04	
71966	10	25	.04	

### Wiha Spanner Power Blades



#### 760 Spanner Power Blades

S2 modified tool steel. Blades fit CentroFix power blade handle. OAL 90mm/3.5".

Item			
No.	Size	lbs.	pkg.
76022	6	.03	1
76023	8	.04	1
76024	10	.04	1



#### 76089 3 Piece Spanner Blade Set

Item		Set includes:
No.	lbs.	Spanner: #6, 8,
76089	.12	10 x 90mm

### XZN Insert Bits

## Specialty Bits

Suitable for all applications for both manual and machine Hardness HRC 59-61

Highly resistant to wear and tear for a long tool life



Impact resistant modified CVM, tool steel, hardened

Triple Square

2 bit pack

#### 701 XZN Insert Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
70143	M3	25	2	.04
70144	M4	25	2	.04
70145	M5	25	2	.04
70146	M6	25	2	.04
70147	M8	25	2	.04



#### 355 XZN Triple Square L-key

Item				
No.	Size	mm	pkg.	lbs.
35512	M12	124	1	.02
35514	M14	138	1	.04
35516	M16	156	1	.07

### Countersink & Drill Bits

High quality HSS steel, ground with radial relief. Universal application in metal, plastic and wood. Guarantees outstanding chip removal, chatter free operation & smooth surface finish.

### 90° Countersink Bit - 1/4" Shank



#### 786 HSS 1/4" Drive Countersinks

High quality HSS steel, ground with radial relief. 1/4" Hex shank according to DIN 3126 C 6.3.

Item						
No.	Size	Inch	mm	Inch	size	pkg
78615	6.3	.26	35	1.38	M3	1
78617	8.3	.33	35	1.38	M4	1
78619	10.4	.41	35	1.38	M5	1
78621	12.4	.49	35	1.38	M6	1
78622	16.5	.65	35	1.38	M8	1
78624	20.5	.81	35	1.38	M10	1

### 1/4" Shank High Speed Drill Bits



#### 780 1/4" Shank Stubby High Speed Drill Bits

DIN 3126 C 6.3.

Item				
No.	Size	Inch	pkg	lbs.
78002	1/16	1.26	1	.02
78005	3/32	1.41	1	.02
78008	1/8	1.57	1	.02
78011	5/32	1.73	1	.03
78015	3/16	1.97	1	.03
78018	1/4	1.97	1	.03

### High Precision Tool Holder For Countersinks & Drill Bits



Quick release tool holder for Drills, Countersinks & Power bits

#### 71480 CentroFix Bit Holder

Item					
No.	Size	Size	mm	Inch	lbs.
71480	1/4"	1/4"	60	2.3	.09




### Dura Torsion Insert and Power Bits

#### Carbide Coated

*Positive location in the screw head with decrease of:*

- necessary pressure forces
- working time
- costs
- wear & tear of bits & screw heads
- anti-cam-out effect

With the Dura bit Wiha has again proved it's power of innovation. The extra hard, elastic Quattro Torsion bit is equipped with an extremely wear resistant tungsten carbide coating that grips the screw head.



#### 710 Dura Bits, Slotted, 1/4"

Item	+	≡	↶	↷	≡
No.	mm	Inch	mm	Inch	mm
71010	0.6	.024	4.5	.177	25
71011	0.8	.030	5.5	.216	25
71012	1.0	.039	5.5	.216	25
71013	1.2	.039	6.5	.255	25



#### 715 Dura Bits, TORX®, 1/4"

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
71576	T15	25	.02	
71578	T20	25	.02	
71582	T30	25	.02	



#### 711 Dura Bits, Phillips, 1/4"

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
71111	1	25	.02	
71112	2	25	.02	
71113	3	25	.02	



#### 712 Dura Bits, Pozidriv, 1/4"

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
71211	1	25	.02	
71212	2	25	.02	
71213	3	25	.02	



#### 741 Dura Phillips Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
74141	1	50	.04	
74142	2	50	.04	
74143	3	50	.04	



#### 742 Dura Pozidriv® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
74241	1	50	.04	
74242	2	50	.04	
74243	3	50	.04	



Bits Tungsten Carbide Coated

#### 71094 Bit-Selector With Dura Insert 1/4"

Bits. Set Includes Magnetic 1/4" Bit Holder & The Following 10 Bits:

- Slotted: 4.5, 5.5, 6.5mm
- Phillips: 1, 2, 3
- TORX®: T10, T15, T20, T25
- .29 lbs.

### Diamond Torsion Insert and Power Bits

Diamond bits supplement Wiha's range of high-quality special bits. When used with machines, the increased tool life of the Wiha Diamond bit reduces cost.

- High wear resistance
- Micro particle coating with sapphire and diamond contents
- Optimized torsion zone

#### Reduction of:

- pressure forces to be applied
- wear and tear of bit and screw head
- working time & costs
- Cam-out effect



The ideal bit even for the most difficult of applications



#### 710 Diamond Bits, Slotted, 1/4"

Item	+	≡	↶	↷	≡
No.	mm	Inch	mm	Inch	mm
71020	4.5	.177	0.6	.024	25
71021	5.5	.216	0.8	.030	25
71022	5.5	.216	1.0	.039	25
71023	6.5	.255	1.2	.039	25



#### 711 Diamond Bits, Phillips, 1/4"

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
71182	2	25	.02	
71183	3	25	.02	



#### 712 Diamond Bits, Pozidriv®, 1/4"

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
71221	1	25	.02	
71223	3	25	.02	



#### 715 Diamond Bits, TORX®, 1/4"

Item	+	≡	↶	↷
No.	Size	mm	lbs.	
71516	T10	25	.02	
71517	T15	25	.02	
71518	T20	25	.02	
71521	T30	25	.02	
71522	T40	25	.03	




#### 741 Diamond Phillips Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item	+	≡	
No.	Size	mm	lbs.
74161	1	50	.03
74163	3	50	.04

**Wiha TiN Coated Insert/Power Bits**

The abbreviation TiN stands for Titanium-Nitride, which has a hardness up to 85 HRC. This coating guarantees a high wear and tear resistance.



- Tough, hard torsion quality with very hard TiN coating
- Optimized torsion zone
- High wear resistance



715 TORX® TiN Coated Insert Bits, 1/4"				
Item				
No.	Size	mm	lbs.	
71585	T5	25	.02	
71587	T7	25	.02	
71563	T10	25	.02	
71564	T15	25	.02	
71565	T20	25	.02	
71566	T25	25	.02	
71569	T27	25	.02	
71567	T30	25	.02	
71568	T40	25	.02	

TiN - Titanium Nitride



711 Phillips TiN Coated Insert Bits 1/4" Hex Drive, Length 2.0"/50mm				
Item				
No.	Size	mm	lbs.	
71142	2	50	.04	
71143	3	50	.04	

TiN - Titanium Nitride



711 Phillips TiN Coated Power Bits 1/4" Hex Drive, Length 2.0"/50mm				
Item				
No.	Size	mm	lbs.	
71122	2	25	.02	
71123	3	25	.02	

TiN - Titanium Nitride




741 Phillips TiN Coated Power Bits 1/4" Hex Drive, Length 2.0"/50mm				
Item				
No.	Size	mm	lbs.	
74101	1	50	.04	
74105	2	50	.04	
74108	3	50	.04	

TiN - Titanium Nitride

**NOTES:**

[Blank area for notes]

**Wear Characteristics**









**Wiha Power Blade Sets**

Blade Holder For Power Blades






**76000 CentroFix Cushion Grip Blade Holder**  
Wiha-SoftFinish® impact resistant, with roll off protection. Ergonomic cushion grip handle. Quick release bit holder with magnet.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
<b>76000</b>	6.0	149	5.9	34.6	1.36	.26




**76079 Canvas Folding Wallet**

Holds 38 90mm power blades.

Item			
No.	Size	lbs.	pkg.
<b>76079</b>	7-1/8" x 6" x 2"	.42	1





**76099 37 Pc. Power Blade Set, In Durable Belt Pack** Set includes cushion grip CentroFix Blade Holder & 36 interchangeable blades.

<b>Item No. 76099</b>	 lbs. 2.06
<b>Slotted:</b>	2.5, 3.0, 4.5, 5.5, 6.0mm
<b>Phillips:</b>	#0, 1, 2, 3
<b>Security TORX®:</b>	T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s
<b>Security Hex Inch:</b>	1/16*, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
<b>Pozidriv®:</b>	#1, 2, 3 & <b>Square:</b> #1, 2, 3
<b>4" Nut Setters:</b>	1/4, 5/16, 3/8"
Cushion Grip CentroFix Blade Holder	
* 1/16" Standard Inch Hex Only	




**76085 9 Pc. Power Blade Nut Driver Set** 30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

<b>Item No. 76085</b>	 lbs. .96
<b>Inch:</b>	3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"




**76086 12 Pc. Power Blade Nut Driver Set** 30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

<b>Item No. 76086</b>	 lbs. 1.22
<b>Metric:</b>	4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 12.0, 13.0mm




**76087 61 Pc. Power Blade Service Kit, In Durable Zipper Case** Set includes Bit Holding Handle, MicroBit Storage Handle, 4mm to 1/4" Magnetic Adapter, 9 power blades, 46 bits & 3 nut setters.

<b>Item No. 76087</b>	 lbs. 1.34
<b>90mm Power Blades:</b>	<b>Slotted:</b> 4.5, 5.5, 6.0mm
<b>Phillips:</b>	#1, 2, 3 & <b>Square:</b> #1, 2, 3
<b>75mm Security TORX® Bits:</b>	T10s, T15s, T20s, T25s, T27s, T30s
<b>MicroBits:</b>	<b>Phillips:</b> #000, 00, 0, 1, 2, <b>Slotted:</b> .8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
<b>Hex Inch:</b>	.028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
<b>Hex Metric:</b>	1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
<b>TORX®:</b>	T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
<b>Magnetic Nut Setters:</b>	1/4, 5/16, 3/8"




**76098 36 Pc. Power Blade Set, In Durable Belt Pack** Set includes cushion grip CentroFix Blade Holder & 35 interchangeable blades.

<b>Item No. 76098</b>	 lbs. 1.86
<b>Slotted:</b>	2.5, 3.0, 4.5, 5.5, 6.0mm
<b>Phillips:</b>	#0, 1, 2, 3
<b>Security TORX®:</b>	T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
<b>Security Hex Metric:</b>	2.5, 3.0, 4.0, 5.0mm
<b>Pozidriv®:</b>	#1, 2, 3 & <b>Square:</b> #1, 2, 3
<b>Spanner:</b>	#6, 8, 10 & <b>Tri-Wing:</b> #1, 2, 3, 4
Cushion Grip CentroFix Blade Holder	



**76084 12 Pc. Power Blade Inch & Metric Nut Driver Set** 30mm deep drilled Nut drivers. Use with #76000 CentroFix Blade Holder. 100mm OAL

<b>Item No. 76084</b>	 lbs. 2.97
<b>Inch:</b>	3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2"
<b>Metric:</b>	4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 12.0, 13.0mm
Cushion Grip CentroFix Blade Holder	

## CushionGrip Stubby Bit Sets



**38043** SoftFinish® Cushion Grip Stubby Bit Holder with Wiha cushion grip handle & CVM tool steel shaft.

Set includes the following 1/4" bits:

- Slotted:** 4.5, 6.0mm
- Phillips:** #1, #2 lbs.
- Pozidriv®:** #1, #2 .20



**38048** SoftFinish® Cushion Grip Stubby Bit Holder with Wiha cushion grip handle & CVM tool steel shaft.

Set includes the following 1/4" bits:

- Slotted:** 4.5, 6.0mm
- Phillips:** #1, #2 lbs.
- Square:** #1, #2 .20

### NOTES:

## Wiha Cushion Grip Pop-Up Screwdriver Bit Sets



**38032** Pop-Up Bit Screwdriver Set

Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle. Bit holder stainless steel, magnetic. 8.25" OAL

- Slotted:** 4.5, 5.5, 6.0mm
- Phillips:** 1, 2, 3 .42
- TORX®:** T10, T15, T20, T25, T27, T30



**38041** Pop-Up Bit Screwdriver Set

Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle. Bit holder stainless steel, magnetic. 8.25" OAL

- Slotted:** 4.5, 6.0mm
- Square:** 1, 2 lbs.
- Phillips:** 1, 2 .42
- Hex:** 4.0, 5.0, 6.0mm
- TORX®:** T20, T25, T30



**38035** Pop-Up Bit Screwdriver Set


Wiha Cushion Grip handle, multi-component. Compact storage for 12 bits in the handle. Bit holder stainless steel, magnetic. 8.25" OAL

- Slotted:** 4.5, 5.5, 6.5mm lbs.
- Phillips:** 0, 1, 2 .42
- TORX®:** T6, T15, T20, T25
- Security TORX®:** T8s, T10s

## Wiha Insulated Pop-Up Insert Bit Sets



Convenient rotating cap




**38050** Insulated Pop-Up Bit Holder Set With 1/4" Insert Bits

Insulated cushion grip multi-component handle. Bit holder holds 1/4" Insert bits. Convenient rotating cap.

**Item** Set includes the following bits:

- |              |                                 |
|--------------|---------------------------------|
| <b>No.</b>   | <b>Slotted:</b> 4.5, 5.5, 6.0mm |
| <b>38050</b> | <b>Phillips:</b> #0, 1, 2, 3    |
|              | <b>Square:</b> #1, 2, 3         |
|              | <b>Pozidriv®:</b> #1, 2, 3      |
|              | lbs. .46                        |



**38051** Insulated Pop-Up Bit Holder Set With 1/4" Insert Bits

Insulated cushion grip multi-component handle. Bit holder holds 1/4" Insert bits. Convenient rotating cap.


**Item** Set includes the following bits:

- |              |                                 |
|--------------|---------------------------------|
| <b>No.</b>   | <b>Slotted:</b> 4.5, 5.5, 6.0mm |
| <b>38051</b> | <b>Phillips:</b> #0, 1, 2, 3    |
|              | <b>Square:</b> #1, 2, 3         |
|              | <b>TORX®:</b> T15, T20, T25     |
|              | lbs. .46                        |



# 26inOne!

- Includes:
- 13 double end bits
- Locking bit holder
- Pop-up bit access
- Rugged Industrial Design
- Cushion grip handle
- Professional quality
- Made in Germany



“Grab & Go Tool Box”



**Twenty-Six  
Screwdrivers  
in One**

**Ultra Lite!  
Ultra Compact!  
Ultra Fast Access!  
Ultra Quality!**



Tradesman



Technician's



Industrial

### 77790 Cushion Grip Ultra Driver 26inOne

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Includes the following 1/4" double end bits:

- Slotted: 3.0+4.5, 5.5+6.5mm
- Phillips: #1+2, #0+3 lbs.
- Pozidriv®: #1+2 .45
- Square: #1+2, #0+3
- TORX®: T10+T15, T20+T25
- Hex Inch: 1/8+9/64, 5/32+3/16"
- Hex Metric: 3.0+4.0, 5.0+6.0mm

### 77791 Cushion Grip Ultra Driver 26inOne

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Includes the following 1/4" double end bits:

- Slotted: 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- Phillips: #1+2, #0+3 lbs.
- Pozidriv®: #1+2 .45
- Square: #1+2, #0+3
- TORX®: T6+T7, T8+T9, T10+T15, T20+T25, T27+T30


### 77792 Cushion Grip Ultra Driver 26inOne

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.


Includes the following 1/4" double end bits:

- Slotted: 4.0+6.0mm
- Phillips: #1+2 lbs.
- TORX®: T8+T9, T10+T15, T20+T25, T27+T30 .45
- Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm

#### Tradesman Bit Reload



#### Technician's Bit Reload



#### Industrial Bit Reload



### 77780 13 Pc. Double End Insert Bit Reload

For the 26inOne (For #77790)

Includes the following 1/4" double end bits:

- Slotted: 3.0+4.5, 5.5+6.5mm
- Phillips: #1+2, #0+3 lbs.
- Pozidriv®: #1+2 .14
- Square: #1+2, #0+3
- TORX®: T10+T15, T20+T25
- Hex Inch: 1/8+9/64, 5/32+3/16"
- Hex Metric: 3.0+4.0, 5.0+6.0mm

### 77781 13 Pc. Double End Insert Bit Reload

For the 26inOne (For #77791)

Includes the following 1/4" double end bits:

- Slotted: 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- Phillips: #1+2, #0+3 lbs.
- Pozidriv®: #1+2 .14
- Square: #1+2, #0+3
- TORX®: T6+T7, T8+T9, T10+T15, T20+T25, T27+T30

### 77782 13 Pc. Double End Insert Bit Reload

For the 26inOne (For #77792)

Includes the following 1/4" double end bits:

- Slotted: 4.0+6.0mm
- Phillips: #1+2 lbs.
- TORX®: T8+T9, T10+T15, T20+T25, T27+T30 .14
- Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm

## Ultra Driver Accessories



Fits 26inOne  
Ultra Driver



Fits 26inOne  
Ultra Driver

### 77740 Valve Stem Double End Tool,

2 Pack CVM steel, hardened.

Item	mm	Inch	lbs.
77740	30	1.18	.02

### 77741 1/4" Socket Adapter 1/4" Hex to 1/4"

Square Drive. CVM steel, hardened.

Item	mm	Inch	lbs.
77741	30	1.18	.01

## 26inOne! Ultra Driver Displays



### 30 Piece Display "Tradesman"

**97790 30 Ultra Drivers Display**

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97790

Tradesman 1/4" Double End Bits:

- Slotted: 3.0+4.5, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⊗ TORX®: T10+T15, T20+T25
- Hex Inch: 1/8+9/64, 5/32+3/16"
- Hex Metric: 3.0+4.0, 5.0+6.0mm



### 30 Piece Display "Technician's"

**97791 30 Ultra Drivers Display**

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97791

Technician's 1/4" Double End Bits:

- Slotted: 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⊗ TORX®: T6+T7, T8+T9, T10+T15, T20+T25, T27+T30



### 30 Piece Display "Industrial"

**97792 30 Ultra Drivers Display**

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97792

Industrial 1/4" Double End Bits:

- Slotted: 4.0+6.0mm
- ⊕ Phillips: #1+2
- ⊗ TORX®: T8+T9, T10+T15, T20+T25, T27+T30
- Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm



### 6 Pack "Tradesman"

**97780 6 Pack Ultra Drivers Display Reorder**

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97780

Tradesman 1/4" Double End Bits:

- Slotted: 3.0+4.5, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⊗ TORX®: T10+T15, T20+T25
- Hex Inch: 1/8+9/64, 5/32+3/16"
- Hex Metric: 3.0+4.0, 5.0+6.0mm



### 6 Pack "Technician's"

**97781 6 Pack Ultra Drivers Display Reorder**

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97781

Technician's 1/4" Double End Bits:

- Slotted: 3.0+4.5, 4.0+6.0, 5.5+6.5mm
- ⊕ Phillips: #1+2, #0+3
- ⊕ Pozidriv®: #1+2
- Square: #1+2, #0+3
- ⊗ TORX®: T6+T7, T8+T9, T10+T15, T20+T25, T27+T30



### 6 Pack "Industrial"

**97782 6 Pack Ultra Drivers Display Reorder**

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

Item No. 97782

Industrial 1/4" Double End Bits:

- Slotted: 4.0+6.0mm
- ⊕ Phillips: #1+2
- ⊗ TORX®: T8+T9, T10+T15, T20+T25, T27+T30
- Hex Inch: 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
- Hex Metric: 2.0+2.5, 3.0+4.0, 5.0+6.0mm








**Ultra Driver Bonus Pack**



**77795 24 Piece Cushion Grip Ultra Driver 26inOne Bonus Pack**

Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.

**Includes:**

-  **Slotted:** 3.0+4.5, 4.0+6.0, 5.5+6.5mm lbs.
-  **Phillips:** #1+2, #0+3
-  **Pozidriv®:** #1+2
-  **Square:** #1+2, #0+3
-  **TORX®:** T6+T7, T8+T9, T10+T15, T20+T25, T27+T30
-  **Hex Inch:** 3/32+7/64, 1/8+9/64, 5/32+3/16, 7/32+1/4"
-  **Hex Metric:** 2.0+2.5, 3.0+4.0, 5.0+6.0mm
- 1/4" Hex to 1/4" Square Socket Adapter**
- Double End Valve Stem Tool**

**Combo Terminator & Bit Set**

**Terminator Impact Bits & Ultra Driver**



26inOne!

Tradesman

**76898 42 Pc. Ultra Driver & Terminator Impact Bit Set**

Item No. 76898 lbs. .92

**Terminator Impact Bits**

- Phillips:** #1, 2 (2), 3
- Square:** #1, 2 (2), 3
- Hex Inch:** 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
- Hex Metric:** 3.0, 4.0, 5.0, 6.0mm
- TORX®:** T10, T15, T20 (2), T25 (2), T30 (2), T40

**SlimFix 1/4" Bit Holder**

**Ultra Driver Double End Bits:**

- Slotted:** 3.0+4.5, 5.5+6.5mm
- Phillips:** #1+2, #0+3
- Pozidriv®:** #1+2
- Square:** #1+2, #0+3
- Torx®:** T10+T15, T20+T25
- Hex Inch:** 1/8+9/64, 5/32+3/16"
- Hex MM:** 3.0+4.0, 5.0+6.0mm

**Combo Pliers & Bit Set**

**BiCut SuperCut & Ultra Driver**

26inOne!



Tradesman

**77786 15 Pc. Ultra Driver & Pliers Set With BiCut SuperCut & Ultra Driver Bit Set**

Item No. 77786 lbs. 1.17

**8.0" Soft Grip Vinyl BiCut SuperCut**

For cutting various materials from soft to extremely hard. Double the power at the press of a button.

**Ultra Driver Double End Bits:**

- Slotted:** 3.0+4.5, 5.5+6.5mm
- Phillips:** #1+2, #0+3
- Pozidriv®:** #1+2
- Square:** #1+2, #0+3
- TORX®:** T10+T15, T20+T25
- Hex Inch:** 1/8+9/64, 5/32+3/16"
- Hex MM:** 3.0+4.0, 5.0+6.0mm

**1/4" Sockets & Bit Set**

**Tradesman Ultra Driver & 1/4" To 1/4" Sq. Drive Sockets**

26inOne!



Tradesman

**77793 29 Pc. Ultra Driver & Socket Set**

1/4" Sockets, Adapter & Ultra Driver Bit Set

Item No. 77793 lbs. .92

**1/4" Square Drive Sockets**

Inch: 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"  
Metric: 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm

**1/4" x 1/4" Socket Adapter**

**Ultra Driver Double End Bits:**







- Slotted:** 3.0+4.5, 5.5+6.5mm
- Phillips:** #1+2, #0+3
- Pozidriv®:** #1+2
- Square:** #1+2, #0+3
- TORX®:** T10+T15, T20+T25
- Hex Inch:** 1/8+9/64, 5/32+3/16"
- Hex MM:** 3.0+4.0, 5.0+6.0mm

**Security Ultra Driver**



**77789 Security Cushion Grip Ultra Driver 26inOne** Wiha cushion grip handle & CVM tool steel shaft. Locking bit holder.







**Includes 1/4" double end Security bits:**

-  **Slotted/Phillips:** 5.5mm+#2 lbs.
-  **Square:** #1+#2 lbs.
-  **TORX®:** T8s+T9s, T10s+T15s, T20s+T25s, T27s+T30s .45
-  **Hex Inch:** 1/8+9/64, 5/32+3/16, 7/32+1/4"
-  **Hex Metric:** 3.0+4.0, 5.0+6.0mm
-  **Spanner:** #4+#6, #8+#10

**Security Bit Reload**

**77783 13 Pc. Double End Insert Bit Reload For the 26inOne (For #77789)**

**Includes the following 1/4" double end bits:**

-  **Slotted/Phillips:** 5.5mm+#2 lbs.
-  **Square:** #1+#2 lbs.
-  **TORX®:** T8s+T9s, T10s+T15s, T20s+T25s, T27s+T30s .14
-  **Hex Inch:** 1/8+9/64, 5/32+3/16, 7/32+1/4"
-  **Hex Metric:** 3.0+4.0, 5.0+6.0mm
-  **Spanner:** #4+#6, #8+#10





## Wiha Security Bits Collectors



**71990** Bits Collector with Security **TORX**, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits. 39 Pc. Set includes: Handle, 1/4" bit holder, 1/4" Bit holding socket adapter, storage box & the following 1/4" bits:

- ⊕ Security **TORX**: T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- ⊖ Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⚙ Tri-Wing: 1, 2, 3, 4
- ⊕ Torq Set: 6, 8, 10
- ⊖ Spanner: 4, 6, 8, 10
- ⦿ Slotted: 6.0, 8.0mm
- ⚙ ⊕ Phillips: 1, 2
- lbs. ⊕ Pozidriv®: 0, 1, 2, 3
- 1.03 ⊖ Square: 1, 2, 3



**71991** Bits Collector with Security **TORX**, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits. 39 Pc. Set includes: Handle, 1/4" SlimFix bit holder & 1/4" Bit holding socket adapter, storage box & the following 1/4" bits:


- ⊕ Security **TORX**: T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- ⊖ Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⚙ Tri-Wing: 1, 2, 3, 4
- ⊕ Torq Set: 6, 8, 10
- ⊖ Spanner: 4, 6, 8, 10
- ⦿ Slotted: 6.5, 8.0mm
- ⚙ ⊕ Phillips: 1, 2
- lbs. ⊕ Pozidriv®: 0, 1, 2, 3
- 1.04 ⊖ Square: 1, 2, 3



**71994** Bits Collector with **TORX**, Slotted, Phillips, Pozidriv®, Square & Hex Bits. 38 Pc. Set Includes: Handle, 1/4" bit holder, storage box & the following 1/4" bits:

- ⊕ **TORX**: T7, T8, T9, T10, T15, T20, T25, T27, T30, T40
- ⊖ Square: 1, 2, 3 & Pozidriv®: 1, 2, 3
- ⦿ Slotted: 4.5, 5.5, 6.0mm
- ⊕ Phillips: 0, 1, 2, 3
- ⚙ ⊖ Hex Metric: 2.5, 3.0, 4.0, 5.0, 6.0mm
- lbs. ⊖ Hex Inch: 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4"

## Wiha Security Bits Collector With Extra Fine 72 Tooth Ratchet



**71988** Bits Collector with Security **TORX**, Tri-Wing, Torq Set, Spanner, Security Hex, Slotted, Phillips, Pozidriv® and Square bits. 38 Pc. Set includes: 1/4" Bit Holding Ratchet, 1/4" magnetic bit holder, storage box and 1/4" Insert bits:

- ⊕ Security **TORX**: T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- ⊖ Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⚙ Tri-Wing: 1, 2, 3, 4
- ⊕ Torq Set: 6, 8, 10
- ⊖ Spanner: 4, 6, 8, 10
- ⦿ Slotted: 6.5, 8.0mm
- ⚙ ⊕ Phillips: 1, 2
- lbs. ⊕ Pozidriv®: 0, 1, 2, 3
- 1.02 ⊖ Square: 1, 2, 3



**71095** Bits Collector with Phillips & Hex Inch bits. 51 Piece Set Includes: 1/4" SlimFix Bit Holder, storage box and the following 1/4" bits:

- ⊕ 10 Each Phillips: 1, 2 & 5 Phillips: 3
- lbs. ⊖ 10 Each Hex Inch: 1/8, 3/16" & 5 Hex Inch: 5/32"



**71992** Bits Collector with Security 1/4" Insert bits. 29 Piece Set Includes: 1/4" Bit Holder, 1/4" Bit holding socket adapter, 1/4" Universal Magnetic Bit Holder, storage box and the following 1/4" bits:

- ⊕ Security **TORX**: T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
- ⊖ Security Hex: 1/8, 3/32, 7/64, 9/64, 5/32, 3/16, 7/32, 1/4"
- ⚙ Tri-Wing: 4, 5 & Torq Set: 5, 8
- lbs. ⊕ Pozidriv®: 2 & Square: 1, 2
- .99 Spanner: 6, 8, 10



**Wiha Bit Selectors**

Compact size and easy bit selection make the Bit Selector an ideal maintenance tool



Slide out drawer allows quick bit access and secure storage



**Plastic storage box** is compact, durable and light weight  
**1/4" Magnetic Adapter** fits all standard 1/4" bits

**Molded hex cavity in box end**  
 Magnetic adapter fits into opening so tool case can be used as a handle on quick fastening jobs

**792 Sets Bit-Selector Sets**

These handy sets include 10 hardened bits of chrome-vanadium-molybdenum steel. 1/4" magnetic bit holder can be used in power tools. Plastic storage box is compact, durable and light weight. Molded hex cavity turns box into handle for quick fastening jobs. Quick bit access with slide out drawer. Packaged in clear blister pack.



**79243 Bit-Selector With Slotted, Phillips & TORX® Bits, Includes 1/4" Bit Holder & The Following 10 Bits:** lbs. .32

- ↓ Slotted: 4.5, 5.5, 6.0mm
- Phillips: #0, 1, 2, 3
- TORX®: T10, T15, T20



**79248 Bit-Selector With Slotted, Phillips & Square Bits, Includes 1/4" Bit Holder & The Following 10 Bits:** lbs. .32

- ↓ Slotted: 4.5, 5.5, 6.0mm
- Phillips: #0, 1, 2, 3
- Square: #1, 2, 3



**71090 Bit-Selector With Slotted, Phillips & Hex 1/4" Bits, Includes Universal Magnetic 1/4" Bit Holder & The Following 9 Bits:**

- ↓ Slotted: 4.5, 5.5, 6.5mm lbs.
- Phillips: #1, 2, 3
- Hex Inch: 1/8, 5/32, 3/16"

**Wiha XSelector & XLSelector Bit Sets**

Compact size and easy bit selection make the Wiha XSelector an ideal maintenance tool



Easy bit access with hinged cover



**XLSelector Pocket Sized** 5.3" x 3.1" x .7"  
**XSelector Pocket Sized** 3 1/8" x 2 1/8" x 1/2"

Sets include Clicfix quick release holder

These handy sets include 10 hardened bits of CVM steel. 1/4" Quick Release holder can be used in power tools. Quick bit access through integrated bit-clamp.



**79443 XSelector Bit Set With Slotted, Phillips, and TORX® Bits Set Includes 1/4" Magnetic Holder & the following 10 bits:**

- Slotted: 5.5, 6.5, 8.0mm
- Phillips: #0, 1, 2, 3 lbs.
- TORX®: T10, T15, T20 .27




**79499 XLSelector 1/4" Ratchet & Bit Set**  
 Wiha 1/4" ratchet bit handle, bit holder & 15 Insert bits Includes:

- Slotted: 4.5, 5.5, 6.0mm
- Phillips: #0, 1, 2
- TORX®: T7, T8, T9, T10, T15, T20, T25
- Square: #1, 2
- ↓ lbs. .56




**79491 XLSelector 1/4" Ratchet & Bit Set**  
 Wiha 1/4" ratchet bit handle, bit holder & 15 Insert bits Includes:

- Slotted: 4.5, 6.0mm
- Phillips: #1, 2, 3 lbs.
- Square: #1, 2 .56
- PoziDrive: #1, 2
- Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm



**79495 XLSelector Bit Set With Slotted, Phillips, TORX®, Hex Bits, 31 Pc. Set Includes: 1/4" Magnetic Bit Holder & 30 Insert Bits:**

- Slotted: 4.5, 5.5, 6.0mm
- Phillips: #0, 1, 2, 3
- TORX®: T6, T7, T8, T9, T10, T15, T20, T25
- Metric Hex: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm lbs. .62
- Inch Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"



**79490 XLSelector Security Bit Set, 31 Pc. Set Includes Universal Bit Holder-magnetic and the following 30 bits:**

- Slotted: 6.0mm
- Phillips: #1, 2
- Torq Set: #6, 8, 10
- Square: #1, 2
- Triwing: #2, 3, 4, 5
- PoziDrive: #1, 2
- Spanner: #4, 6, 8, 10
- Security TORX®: T8s, T10s, T15s, T20s, T25s lbs. .64
- Security Hex: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"



**79493 XLSelector Security Bit Set, 31 Pc. Set Includes Universal Bit Holder-magnetic and the following 30 bits:**

- Slotted: 4.5, 5.5, 6.0mm
- Phillips: #1, 2, 3
- Square: #1, 2
- TORX®: T7, T8, T9, T10, T15, T20, T25
- Hex Metric: 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm
- Hex Inch: 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"
- ↓ lbs. .64



**Wiha Insert Bit Blister Pack**



**72593 10 Pack Slotted, Phillips & Square Insert Bit Pack** CVM S2 modified tool steel.

- **Slotted:** 4.5, 5.5, 6.0mm lbs.
- ⊕ **Phillips:** #1, 2, 3 .16
- **Square:** #1, 2, 3

**Wiha Adjustable TorqueControl Tool Sets In Durable Storage Box**



With Certificate of Calibration



**28590 24 Pc. TorqueVario-S Micro-Bit Set** Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder & Torque adjustment tool. Packed in a compact durable storage box.

**Item No. Slotted:** 1.5, 2.0, 3.0, 4.0mm

**28590 Phillips:** #00, #0, #1

**TORX®:** T6, T7, T8, T9, T10, T15

**Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32

lbs. 1.35

28504 - Handle Range 7.5-20 In/lbs.



With Certificate of Calibration



**28593 24 Pc. TorqueVario-S Micro-Bit Set** Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 21 Micro Bits, Micro Bit holder and Torque adjustment tool. Packed in a compact durable storage box.

**Item No. Slotted:** 1.5, 2.0, 3.0, 4.0mm

**28593 Phillips:** #00, #0, #1

**TORX®:** T6, T7, T8, T9, T10, T15

lbs. 1.35

28501 - TorqueVario-S handle Range 15 - 80 Inch/oz (+/- 10%)

**Wiha Power Bit Belt Packs**



**74983 Power Bit Belt Pack With Slotted, Phillips & TORX® Bits** Includes the following 10 bits:

- **Slotted:** 4.5, 5.5, 6.5mm
- ⊕ **Phillips:** #1, 2, 3 lbs.
- ⊗ **TORX®:** T10, T15, T20, T25 .30



**74988 Power Bit Belt Pack With Slotted, Phillips & Square Bits** Includes the following 10 bits:

- **Slot:** 3.0, 4.5, 5.5, 6.5mm
- ⊕ **Phillips:** #1, 2, 3 lbs.
- **Square:** #1, 2, 3 .30



**53 Pc. Set**

With Certificate of Calibration



**28595 53 Pc. TorqueVario-S Bit Set, In Storage Box** Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes ergonomic multi-component adjustable TorqueVario-S handle, 50 Insert bits, 1/4" Bit holder and Torque adjustment tool.

**Item No. 28595**

**Slotted:** 4.5, 5.5, 6.5, 8.0mm

lbs. 2.85

**Phillips:** #0, #1, #2, #3

**TORX®:** T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

**Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16"

**Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0mm

**Pozidriv:** #0, #1, #2, #3

**Torq Set:** #4, #5, #6, #8

**Square:** #1, #2, #3

**Triwing:** #0, #1, #2, #3, #4

28506-Handle Range 10 - 50 In/lbs.

28581 - 1/4" Bit Holder



**59 Pc. Set**

With Certificate of Calibration



**28589 59 Piece TorqueVario-S Bit Set, In Storage Box** Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes 3 ergonomic multi-component adjustable TorqueVario-S handles, 39 Insert bits, 15 Sockets, 1/4" Bit holder, 1/4" Hex to 1/4" Square adapter and Torque adjustment tool.

**Item No. Slotted:** 4.5, 5.5, 6.5mm

**28589 Phillips:** #0, 1, 2

**TORX®:** T5, T6, T7, T8, T9, T10, T15, T20, T25, T30

lbs. 2.73

**Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"

**Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0mm

**Pozidriv:** #1, 2 & **Square:** #1, 2, 3

**Inch Sockets:** 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 3/8"

**Metric Sockets:** 4.0, 4.5, 5.0, 5.5, 6.0, 7.0, 8.0mm

**3 Handles:** 15-80 Inch/oz., 5-10 & 10-50 In/lbs.



## Wiha Bit Holders

For working in confined spaces



**28103 Magnetic 1/4" Bit Holder With Wiha SoftFinish® Stubby Handle** Stainless steel with strong magnet. Wiha-SoftFinish® handle multi-component, cushion grips.

Item					
No.	Inch	mm	Inch	lbs.	pkg.
28103	1/4"	57	2.2	.11	1




Plastic coated flexible metal  
with stainless steel retaining ring  
**38600 Bit Holder 1/4" with Retaining Ring With Flexible Shaft** Wiha-SoftFinish® handle multi-component, cushion grips.

Item					
No.	Inch	mm	Inch	mm	Inch lbs. pkg.
38600	1/4"	150	5.9	268	10.6 .30 1



**48401 1/4" Bit holding Screwdriver, With Wiha Ergo 3K Handle** Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM tool steel, nickel plated.

Item					
No.	Size	mm	Inch	mm	Inch lbs. pkg.
48401	1/4"	125	5.0	244	9.6 .24 1



Hex shaft CVM steel, nickel-plated  
Magnetic, holds bit and screw  
**38800 Bit Holder With Wiha T-handle** Retainer out of stainless steel. Wiha-T-handle high quality plastic, impact resistant.

Item					
No.	Size	mm	Inch	mm	Inch lbs. pkg.
38800	1/4"	150	6.0	80	3.0 .18 1



Adjustable Blade Length  
Magnetic Bit Holder  
**28489 Drive-Loc VI Bit Holder** High alloy CVM steel, through hardened, hard chrome finish. Wiha-SoftFinish® handle multi-component, cushion grips.

Item					
No.	Inch	Extends		lbs.	pkg.
28489	1/4"	1-3/4" to 4-7/8"		.36	1



Retainer out of stainless steel  
**48400 1/4" Bit Holding Screwdriver, With Wiha Protorn Handle** Magnetic, holds bit and screw. Shaft CVM steel, nickel-plated. Handle, molded on, impact resistant.

Item					
No.	Size	mm	Inch	mm	Inch lbs. pkg.
48400	1/4"	125	5.0	243	9.6 .24 10



Magnetic, holds bit and screw  
**38801 Bit Holders With Wiha Soft Grip T-handle** Chrome-V-Moly, hardened, hard chrome finish. Wiha soft grips are molded on with through the handle side torque drive.

Item					
No.	Size	mm	Inch	mm	Inch lbs. pkg.
38801	1/4"	178	7.0	102	4.0 .18 1



Magnetic  
Retainer out of stainless steel  
**384 1/4" Magnetic Bit Holding Drivers, With Wiha SoftFinish® Handle** Ergonomic cushion grip, magnetic, holds bit and screw. Shaft CVM steel, nickel-plated.

Item					
No.	Size	mm	Inch	mm	Inch lbs.
38450	1/4"	125	5.0	240	9.46 .23
38460	1/4"	300	11.8	400	15.69 .37



**66850 1/4" Bit Holding Screwdriver, With Wiha Protorn Precision handle.** Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated.

Item					
No.	Size	mm	Inch	mm	Inch lbs.
66850	1/4"	60	2.36	170	6.7 .07



Non-slip grip, magnetic  
Holds bit and screw  
**52650 1/4" Bit holding Screwdriver, With Wiha MicroFinish Handle** Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil & grease resistant.

Item					
No.	Size	mm	Inch	mm	Inch lbs. pkg.
52650	1/4"	125	5.0	244	9.6 .24 1



## Wiha Bit Holders



Holds 6 bits (bits not included)

**38025 Magnetic Bit Holder, 1/4"**,  
Wiha-Powerhandle, Insulated, impact resistant. Snap-lock rotatable cap. Chambered bit holder equipped with transparent selector for easy selection of bits. 1/4" bit holder, shielded, magnetic, holds bit and screw.

Item	Size	mm	Inch	mm	Inch	lbs.	pkg.
<b>38025</b>	1/4"	120	4.7	230	9.0	.26	1



**711 Universal Magnetic Bit Holder, 1/4" For Insert Bits**

Item	Size	Size	mm	Inch	lbs.
<b>71130</b>	1/4"	1/4"	74	2.9	.06
<b>71131</b>	1/4"	1/4"	59	2.3	.05



**71494 Stainless Steel Bit Holder, 1/4" For Insert Bits**  
Internal C-ring for bit holding & magnet.

Item	Size	Size	mm	Inch	lbs.
<b>71494</b>	1/4"	1/4"	54	2.1"	.05



**71139 Magnetic Bit Holder, 1/4" For Insert Bits**

Item	Size	Size	mm	Inch	lbs.
<b>71139</b>	1/4"	1/4"	100	4.0	.08




Magnetic



Holds 1" (25mm) Bits  
All Stainless with Rubber O-Ring

**714 Screw Cap Bit Holder with O-Ring**

Item	Size	Size	mm	Inch	lbs.
<b>71492</b>	1/4"	1/4"	62	2.4	.10 Non Magnetic
<b>71493</b>	1/4"	1/4"	76	3.0	.10 Magnetic



**714 Protturn 1/4" Quick Release Bit Holder**

Item	Size	mm	Inch	lbs.
<b>71475</b>	2.4"	60	2.4	.06
<b>71476</b>	3.9"	100	3.9	.09
<b>71477</b>	5.9"	150	5.9	.11
<b>71478</b>	7.9"	200	7.8	.14
<b>71479</b>	9.9"	250	9.8	.17

**71474 5 Pc. Protturn 1/4" Quick Release Bit Holder Set With magnets**  
Includes: 60mm, 100mm, 150mm, 200mm, 250mm lbs. .58

**"SlimFix" Impact Rated**



**71496 "SlimFix" Impact Rated Locking 1/4" Bit Holder For 1/4" Insert Bits** Faster, sleeker, more productive "SlimFix" for instant bit changes. Just 10.9mm / 0.42 Diameter. Bit Locks securely in place. CV hardened sleeve.

Item	Size	Size	mm	Inch	lbs.
<b>71496</b>	1/4"	1/4"	66.5	2.62	.06



**714 Bit Holder, Retaining Ring & Magnetic O-Ring**


Item	Size	Size	mm	Inch	lbs.
<b>71431</b>	1/4"	1/4"	60	2.4	.05
<b>71433</b>	1/4"	1/4"	67	2.6	.05
<b>71435</b>	1/4"	1/4"	100	3.9	.07
<b>71437</b>	1/4"	1/4"	150	5.9	.11
<b>71439</b>	1/4"	1/4"	200	7.8	.13
<b>71441</b>	1/4"	1/4"	253	10.0	.16

**71499 5 Pc. Bit Holder Set In Vinyl Pouch**  
Includes: 60mm, 100mm, 150mm, 200mm, 253mm lbs. .60



Micro Bits Made in Germany

**Wiha SYSTEM 4 Micro Bits - 10 Bit Packs**



CVM steel, hardened, on 4 mm hex stock.





Bits High alloy CVM steel, hardened

Tips Exact fit, precision machined

Use bits directly in handle or with 4" bit extension





**756 SYSTEM 4 Hex Metric Micro Bits**

Item				
No.	mm	mm	Inch	lbs.
75616	.7	28	1.1	.06
75617	.9	28	1.1	.06
75618	1.3	28	1.1	.06
75619	1.5	28	1.1	.07
75620	2.0	28	1.1	.07
75621	2.5	28	1.1	.07
75622	3.0	28	1.1	.08
75623	4.0	28	1.1	.08







**756 SYSTEM 4 TORX® Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75660	T1	28	1.1	.06
75661	T2	28	1.1	.06
75662	T3	28	1.1	.06
75663	T4	28	1.1	.06
75664	T5	28	1.1	.06
75665	T6	28	1.1	.06
75666	T7	28	1.1	.06
75667	T8	28	1.1	.07
75668	T9	28	1.1	.07
75669	T10	28	1.1	.07
75670	T15	28	1.1	.08
75671	T20	28	1.1	.08








**756 SYSTEM 4 Slotted Micro Bits**

Item				
No.	mm	mm	Inch	lbs.
75602	0.8	28	1.1	.06
75603	1.2	28	1.1	.06
75604	1.5	28	1.1	.06
75605	1.8	28	1.1	.06
75606	2.0	28	1.1	.07
75607	2.5	28	1.1	.07
75608	3.0	28	1.1	.07
75609	3.5	28	1.1	.07
75610	4.0	28	1.1	.08







**756 SYSTEM 4 Hex Inch Micro Bits**

Item					
No.	Inch	mm	Inch	lbs.	
75628	.028	28	1.1	.06	
75629	.035	28	1.1	.06	
75630	.050	28	1.1	.06	
75631	1/16	28	1.1	.06	
75632	5/64	28	1.1	.06	
75633	3/32	28	1.1	.07	
75634	7/64	28	1.1	.07	
75635	1/8	28	1.1	.07	
75636	9/64	28	1.1	.08	
75637	5/32	28	1.1	.08	







**756 SYSTEM 4 Security TORX® Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75681	T10s	28	1.1	.07
75683	T20s	28	1.1	.08







**756 SYSTEM 4 Phillips Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75611	000	28	1.1	.06
75612	00	28	1.1	.06
75613	0	28	1.1	.06
75614	1	28	1.1	.07
75615	2	28	1.1	.07







**756 SYS 4 Metric Security Hex Micro Bits**

Item				
No.	mm	mm	Inch	lbs.
75624	2.0	28	1.1	.06
75626	3.0	28	1.1	.07
75627	4.0	28	1.1	.08




**756 SYSTEM 4 Inch Nut Setters**

Item No.				
Inch	mm	mm	Inch	lbs.
75644	5/64	30	1.2	.07
75645	3/32	30	1.2	.07
75646	7/64	30	1.2	.07
75647	1/8	30	1.2	.07
75648	9/64	30	1.2	.08
75649	5/32	30	1.2	.08
75650	3/16	30	1.2	.08
75651	7/32	30	1.2	.09








**756 SYSTEM 4 Pentalobe Micro Bits**

Item				
No.	Size	mm	Inch	lbs.
75672	PL1	28	1.1	.06
75673	PL2	28	1.1	.06
75674	PL3	28	1.1	.07
75675	PL4	28	1.1	.07
75676	PL5	28	1.1	.07
75677	PL6	28	1.1	.08







**756 SYS 4 Security Hex Inch Micro Bits**

Item				
No.	Inch	mm	Inch	lbs.
75638	5/64	28	1.1	.06
75639	3/32	28	1.1	.06
75640	7/64	28	1.1	.07
75641	1/8	28	1.1	.07
75642	9/64	28	1.1	.08
75643	5/32	28	1.1	.08



**756 SYSTEM 4 Metric Nut Setters**

Item No.				
Metric	mm	mm	Inch	lbs.
75652	2.0	30	1.2	.07
75653	2.5	30	1.2	.07
75654	3.0	30	1.2	.07
75655	3.5	30	1.2	.07
75656	4.0	30	1.2	.08
75657	4.5	30	1.2	.08
75658	5.0	30	1.2	.08
75659	5.5	30	1.2	.09

## Wiha SYSTEM 4 Micro Bits - On 4mm Hex Stock

### SYSTEM 4 Handles & Micro Bits



**Rotating Cap** for precise turning and control

**Tips**  
Exact fit, precision machined

**Tapered Handle** allows rapid rotation, requires less clearance

**Bits** High alloy CVM steel, hardened

Use bits directly in handle or with 4" bit extension



**750 SYSTEM 4 Slotted Micro Bits**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	mm	mm	Inch	lbs.
75008	0.8	28	1.1	.01
75012	1.2	28	1.1	.01
75015	1.5	28	1.1	.01
75018	1.8	28	1.1	.01
75020	2.0	28	1.1	.01
75025	2.5	28	1.1	.01
75030	3.0	28	1.1	.01
75035	3.5	28	1.1	.01
75040	4.0	28	1.1	.01



**757 SYSTEM 4 TORX® Micro Bits**  
CVM steel, hardened, on 4 mm stock.

Item No.	Size	mm	Inch	lbs.
75701	T1	28	1.1	.01
75702	T2	28	1.1	.01
75703	T3	28	1.1	.01
75704	T4	28	1.1	.01
75705	T5	28	1.1	.01
75706	T6	28	1.1	.01
75707	T7	28	1.1	.01
75708	T8	28	1.1	.01
75709	T9	28	1.1	.01
75710	T10	28	1.1	.01
75715	T15	28	1.1	.01
75720	T20	28	1.1	.01



**75800 SYSTEM 4 Standard Precision Bit**  
Handle Accepts all SYSTEM 4 Series bits.  
110mm/4.3" OAL

Item No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06



**753 SYSTEM 4 Hex Metric Micro Bits**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	mm	mm	Inch	lbs.
75307	.7	28	1.1	.01
75309	.9	28	1.1	.01
75313	1.3	28	1.1	.01
75315	1.5	28	1.1	.01
75320	2.0	28	1.1	.01
75325	2.5	28	1.1	.01
75330	3.0	28	1.1	.01
75340	4.0	28	1.1	.01



**757 SYSTEM 4 Security TORX® Micro Bits**  
CVM steel, hardened, on 4 mm stock.

Item No.	Size	mm	Inch	lbs.
75735	T10s	28	1.1	.01
75742	T20s	28	1.1	.01



**75801 SYSTEM 4 ESD Safe Dissipative Precision Bit Handle** 110mm/4.3" OAL

**Advantages:**

- For working in ESD sensitive applications  
Surface resistant 10<sup>6</sup>-10<sup>9</sup> Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits

Item No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06



**753 SYSTEM 4 Hex Inch Micro Bits**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	Inch	mm	Inch	lbs.
75307	.028	28	1.1	.01
75309	.035	28	1.1	.01
75313	.050	28	1.1	.01
75350	1/16	28	1.1	.01
75352	5/64	28	1.1	.01
75354	3/32	28	1.1	.01
75356	7/64	28	1.1	.01
75358	1/8	28	1.1	.01
75360	9/64	28	1.1	.01
75340	5/32	28	1.1	.01



**753 SYS 4 Metric Security Hex Micro Bits**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	mm	mm	Inch	lbs.
75322	2.0	28	1.1	.01
75332	3.0	28	1.1	.01
75342	4.0	28	1.1	.01



**751 SYSTEM 4 Phillips Micro Bits**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	Size	mm	Inch	lbs.
75105	000	28	1.1	.01
75110	00	28	1.1	.01
75115	0	28	1.1	.01
75120	1	28	1.1	.01
75125	2	28	1.1	.01



**753 SYS 4 Security Hex Inch Micro Bits**

Item No.	Inch	mm	Inch	lbs.
75362	5/64	28	1.1	.01
75364	3/32	28	1.1	.01
75366	7/64	28	1.1	.01
75368	1/8	28	1.1	.01
75370	9/64	28	1.1	.01
75372	5/32	28	1.1	.01



**Wiha SYSTEM 4 Micro Bits**



**757 SYSTEM 4 Pentalobe Micro Bits**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	Size	mm	Inch	lbs.
75743	PL1	28	1.1	.01
75744	PL2	28	1.1	.01
75745	PL3	28	1.1	.01
75746	PL4	28	1.1	.01
75747	PL5	28	1.1	.01
75748	PL6	28	1.1	.01



**758 SYSTEM 4 Inch Nut Setters**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	Inch	mm	mm	Inch	lbs.
75810	5/64	30	1.2	.01	
75811	3/32	30	1.2	.01	
75812	7/64	30	1.2	.01	
75813	1/8	30	1.2	.01	
75814	9/64	30	1.2	.01	
75815	5/32	30	1.2	.01	
75816	3/16	30	1.2	.01	
75817	7/32	30	1.2	.01	



**758 SYSTEM 4 Metric Nut Setters**  
CVM steel, hardened, on 4 mm hex stock.

Item No.	Metric	mm	mm	Inch	lbs.
75820	2.0	30	1.2	.01	
75821	2.5	30	1.2	.01	
75822	3.0	30	1.2	.01	
75823	3.5	30	1.2	.01	
75824	4.0	30	1.2	.01	
75825	4.5	30	1.2	.01	
75826	5.0	30	1.2	.01	
75827	5.5	30	1.2	.01	

**SYSTEM 4 Micro Bit Extension Blades**



**75900 Extension Blade For SYS 4 Micro Bits**  
Shaft CVM steel, hardened, corrosion protected.  
Ball retainer bit extension for 4mm bits.

Item No.	Size	mm	mm	lbs.
75900	4.0	100	4.0	.07



**75901 Magnetic Bit Extension Blade For SYS 4 Micro Bits**  
Shaft CVM steel, hardened, corrosion protected. Magnetic bit holder.

Item No.	Size	mm	mm	lbs.
75901	4.0	100	4.0	.04

**Micro Bit 4mm To 1/4" Socket Adapter**



**75806 Micro Bit 4mm to 1/4" Socket Adapter**  
CVM steel, hardened.

Item No.	mm	Inch	lbs.
75806	28	1.125	.02

**1/4" Drive Micro Bit Tool Adapters**



**75802 Micro Bit To 1/4" Drive Insert Bit Adapter**  
magnets to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75802	4.0	25	4.0	.01



**75803 Long Micro Bit To 1/4" Drive Insert Bit Adapter**  
Uses spring clip non-magnetic to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.
75803	4.0	38	4.0	.02

**Micro Bit 1/4" Drive Power Tool Adapter**




**75902 Micro Bit 1/4" Drive Power Tool Adapter**  
Shaft CVM steel, hardened, corrosion protected. For 4mm bits. 2.3" OAL

Item No.	Size	mm	mm	lbs.
75902	4.0	60	4.0	.07




Wiha SYSTEM 4 Micro Bits & Compact Bit Sets



**75996 SYSTEM 4 Interchangeable Bit Set, 40 Pcs.** Includes Wiha precision handle, bit extension & 38 interchangeable bits.


Item	SYSTEM 4
No.	Combination Bit Set
75996	Set with ESD Safe Precision Handle
<b>Set includes the following bits:</b>	
↓ ↻	<b>Slotted:</b> 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
⊕	<b>Phillips:</b> 000, 00, 0, 1
⊗	<b>TORX®:</b> T3, T4, T5, T6, T7, T8, T9, T10, T15
⬠	<b>Hex Metric:</b> 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
⬠	<b>Hex Inch:</b> .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	<b>100mm Bit Extension</b>
↔	<b>lbs.</b> 1.04



**75994 SYSTEM 4 Slotted/Phillips/Hex Metric/TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box.**

Set includes Wiha precision handle, bit extension & 25 Wiha interchangeable bits.


Item	SYSTEM 4
No.	Combination Bit Set
75994	Set with ESD Safe Precision Handle
<b>Set includes the following bits:</b>	
↓ ↻	<b>Slotted:</b> 1.5, 2.0, 3.0, 4.0mm
⊕	<b>Phillips:</b> 000, 00, 0, 1
⊗	<b>TORX®:</b> T3, T4, T5, T6, T7, T8, T9, T10, T15
⬠	<b>Hex Metric:</b> .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
○	<b>100mm Bit Extension</b>
↔	<b>lbs.</b> .64



**75995 SYS 4 Precision Interchangeable Bit Set, 26 Pcs. In Compact Fold Out Box**

Sets includes Wiha precision handle, bit extension & 24 Wiha interchangeable bits.

Item	SYSTEM 4 Micro Bit Set
No.	Set with ESD Safe Precision Handle
75995	and the following bits:
⊗	<b>TORX®:</b> T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
⬠	<b>Pentalobe:</b> PL1, PL2, PL3, PL4, PL5, PL6
↓ ↻	<b>Slotted:</b> 1.5, 2.0, 2.5, 3.0mm
⊕	<b>Phillips:</b> #000, 00, 0, 1
○	<b>100mm Bit Extension</b>
↔	<b>lbs.</b> .54




**75999 SYSTEM 4 Slotted, Phillips, Hex Inch & Metric Precision Interchangeable Bit Set, 26Pc.** Wiha precision handle, bit extension & 24 interchangeable bits.

Item No.	Combination Bit Set
75999	Set with Standard Precision Handle
<b>Set includes the following bits:</b>	
↓ ↻	<b>Slotted:</b> 1.5, 2.0, 3.0, 4.0mm
⊕	<b>Phillips:</b> 000, 00, 0, 1
⬠	<b>Hex Metric:</b> .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
⬠	<b>Hex Inch:</b> .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	<b>100mm Bit Extension</b>
↔	<b>lbs.</b> .64



**75395 SYS 4 Hex Inch & Metric Precision Interchangeable Bit Set, 18 Pcs. In Compact Fold Out Box.** Wiha precision handle, bit extension and 16 Wiha interchangeable bits.

Item No.	Combination Bit Set
75395	Set with Standard Precision Handle
<b>Includes the following bits:</b>	
⬠	<b>Hex Metric:</b> .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
⬠	<b>Hex Inch:</b> .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	<b>100mm Bit Extension</b>
↔	<b>lbs.</b> .58



**759 sets SYS 4 Slotted / Phillips / Hex In / TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box.** Sets include your choice of Wiha precision handle, bit extension & 25 Wiha interchangeable bits.

Item	Handle Options for SYSTEM 4
No.	Combination Bit Sets
75991	Set with Standard Precision Handle
75992	Set with ESD Safe Precision Handle
<b>Sets include the following bits:</b>	
↓ ↻	<b>Slotted:</b> 1.5, 2.0, 3.0, 4.0mm
⊕	<b>Phillips:</b> 000, 00, 0, 1
⊗	<b>TORX®:</b> T3, T4, T5, T6, T7, T8, T9, T10, T15
⬠	<b>Hex Inch:</b> .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
○	<b>100mm Bit Extension</b>
↔	<b>lbs.</b> .64

## Wiha SYSTEM 4 Micro Bit Sets



**75980 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs.** Includes Wiha ESD Safe Precision Handle, 1/4" to 4mm Adapter, 100mm Bit Extension & 36 Micro Bits.

**Item No. SYSTEM 4 Micro Bit Set**

**75980 Includes The Following Bits:**

- † **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- Phillips:** 000, 00, 0, 1, 2
- TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
- Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- lbs.** .38



**75968 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs.** Includes Wiha ESD Safe Precision Handle, Micro Bit Storage Handle, 1/4" to 4mm Adapter, 100mm Bit Extension & 64 Micro Bits.

**Item No. SYSTEM 4 Micro Bit Set**

**75968 Includes The Following Bits:**

- † **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- Phillips:** 000, 00, 0, 1, 2
- TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
- Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- Nut Driver Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- Nut Driver Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- lbs.** .70

In Zipper Storage Case



**75971 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs.** Includes Wiha ESD Safe Precision Handle, Micro Bit Storage Handle, 1/4" to 4mm Adapter, 100mm Bit Extension & 64 Micro Bits.

**Item No. SYSTEM 4 Micro Bit Set**

**75971 Includes The Following Bits:**

- † **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- Phillips:** 000, 00, 0, 1, 2
- TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
- Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- Nut Driver Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- Nut Driver Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- lbs.** .96



**75965 SYSTEM 4 Master Tech ESD & Ratchet With Micro Bits, 65 Pieces In Storage Box.** Includes Wiha precision ESD Safe handle, micro bit extension, 72 tooth 1/4" ratchet & 62 interchangeable micro bits.

**Item Includes the following micro bits:**

- No. Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- Phillips:** 000, 00, 0, 1
- lbs. TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
- Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- Nut Drivers Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- Nut Drivers Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- Magnetic 1/4" to 4mm Adapter**



**75993 SYSTEM 4 Premium ESD Safe Micro Bit Set, 28 Pcs.** Includes Wiha ESD Safe Precision Handle, 1/4" to 4mm Adapter, 100mm Bit Extension, ESD Safe Tweezers & 21 Micro Bits.

**Item No. SYSTEM 4 Micro Bit Set**

**75993 Micro Bits:**

- † **Slotted:** 0.8, 1.5, 2.0, 2.5, 3.0, 3.5mm
- Phillips:** 000, 00, 0, 1, 2
- TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
- ESD Safe Tweezers:**
- 5SA ESD, 7aSA ESD, 2ASA ESD, AASA ESD, OOSA ESD**
- lbs.** .95



**75977 SYSTEM 4 Master Tech Micro Bit Set, 68 Pcs.** Includes Wiha ESD Safe Precision Handle, ESD Safe Tweezers, 1/4" to 4mm Adapter, 100mm Bit Extension & 64 Micro Bits.

**Item No. SYSTEM 4 Micro Bit Set**

**75977 Includes The Following Bits:**



- Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm
- lbs. Phillips:** 000, 00, 0, 1, 2
- TORX®:** T1, T2, T3, T4, T5, T6, T7, T8, T9, T10, T15, T20
- Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm
- Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- Pentalobe:** PL1, PL2, PL3, PL4, PL5, PL6
- Nut Driver Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm
- Nut Driver Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"
- ESD Fine Round Point Tweezers 3cSA**



**Technician's Micro Bit Sets**

- Micro Precision Bits on 4mm Hex Drive
- Bits of Exclusive CRM-72 Tool Steel
- Handle uses non-magnetic ball retainer
- Use bits in extension only
- Standard extension adds 4" to length
- Non-magnetic bit extension

Surface resistance of handles is 10<sup>6</sup> - 10<sup>9</sup> Ohms



**75093 SYSTEM 4 Slotted, Phillips, TORX® Compact ESD Precision Interchangeable Bit Set, 16 Pcs.** Wiha precision handle, bit extension & 14 interchangeable bits.

**Item No. Combination Bit Set**

**75093** Set with ESD Safe Precision Handle

- **Slotted:** 1.5, 2.0, 2.5, 3.0mm
- ⊕ **Phillips:** 00, 0, 1
- ⚙️ **TORX®:** T6, T7, T8, T9, T10, T15, T20
- lbs. .17
- **100mm Bit Extension**



**75094 SYS 4 Slotted, Phillips, Hex Inch Compact ESD Precision Interchangeable Bit Set, 16 Pcs.** Wiha precision handle, bit extension & 14 interchangeable bits.

**Item No. Combination Bit Set**

**75094** Set with ESD Safe Precision Handle

- **Slotted:** 1.5, 2.0, 2.5, 3.0mm
- ⊕ **Phillips:** 00, 0, 1
- ⚙️ **Hex Inch:** .035, .050, 1/16, 5/64,
- lbs. 3/32, 7/64, 1/8"
- .17 ○ **100mm Bit Extension**



**75095 SYS 4 Slotted, Phillips, Hex Metric Compact ESD Precision Interchangeable Bit Set, 16 Pcs.** Wiha precision handle, bit extension & 14 interchangeable bits.

**Item No. Combination Bit Set**

**75095** Set with ESD Safe Precision Handle

- ⚡ **Slotted:** 1.5, 2.0, 2.5, 3.0mm
- ⊕ **Phillips:** 00, 0, 1
- ⚙️ **Hex Metric:** .9, 1.3, 1.5, 2.0,
- lbs. 2.5, 3.0, 4.0mm
- .17 ○ **100mm Bit Extension**

**75096 SYSTEM 4 Hex Inch & Metric Compact ESD Precision Interchangeable Bit Set, 16 Pcs.** Wiha precision handle, bit extension & 14 interchangeable bits.

**Item No. Combination Bit Set**

**75096** Set with ESD Safe Precision Handle

- **Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- ⚙️ **Hex Metric:** .9, 1.3, 1.5, 2.0,
- lbs. 2.5, 3.0, 4.0mm
- .17 ○ **100mm Bit Extension**



**75097 SYS 4 Slotted, Phillips & 5Point Compact ESD Precision Interchangeable Bit Set, 16 Pcs.** Wiha precision handle, bit extension & 14 interchangeable bits.

**Item No. Combination Bit Set**

**75097** Set with ESD Safe Precision Handle

- **Slotted:** 1.2, 1.5, 2.0, 2.5, 3.0mm
- ⊕ **Phillips:** 000, 00, 0, 1, 2
- ⚙️ **Pentalobe:** PL1, PL2, PL3, PL4
- lbs. .17
- **100mm Bit Extension**

**Micro Bit Handle Storage Sets**



**75981 Micro Bit Handle Storage Slotted & Phillips Bit Set, 7 Pcs.** Wiha precision storage handle & 6 interchangeable bits.

**Item No. Set with Precision Storage Handle**

- 75981** ● **Slotted:** 1.2, 1.5, 2.0mm
- lbs. .12
- ⊕ **Phillips:** 000, 00, 0



**75983 Micro Bit Handle Storage Hex Inch Bit Set, 7 Pcs.** Wiha precision storage handle & 6 interchangeable bits.

**Item No. Set with Precision Storage Handle**

- 75983** ● **Hex Inch:** .050, 1/16, 5/64,
- lbs. .12 3/32, 7/64, 1/8"



**75985 Micro Bit Handle Storage TORX® Bit Set, 7 Pcs.** Wiha precision storage handle & 6 interchangeable bits.

**Item No. Set with Precision Storage Handle**

- 75985** ⚙️ **TORX®:** T3, T4, T5, T6, T7, T8
- ⚡ lbs. .12



**75805 SYS 4 Micro Bit Storage Handle**

Accepts SYS 4 Series bits. 108mm/4.25" OAL

Item No.	○ mm	○ Inch	⚡ lbs.
75805	4.0	.1574	.05

## Wiha Inch & Metric Nut Setters



### 704 Inch Color Coded Hex Inch Nut Setter With Permanent Industrial Magnets

Item No.	Size	mm	lbs.
70480	1/4"	152	.20
70481	5/16"	152	.20
70482	3/8"	152	.21
70483	7/16"	152	.22
70484	1/2"	152	.28
70485	9/16"	152	.30

High visibility color coded for fast selection  
Rugged corrosion resistant black oxide finish

**70486 6 pc. Color Coded Hex Inch Nut Setter Set** Powerful magnet for secure holding of fasteners. 6"/152mm OAL


Item No.	lbs.	Set includes
70486	1.18	1/4" R, 5/16" Y, 3/8" Bl 7/16" Br, 1/2" O, 9/16" Bk

Magnetic 1/4"



### 704 Metric Nut Setters Standard With Permanent Industrial Magnet, 1/4" Hex Metric Nut Setters

Item No.	Size	mm	lbs.
70437	5.0	55	.04
70438	5.5	55	.05
70440	6.0	55	.05
70442	7.0	55	.05
70445	8.0	55	.05
70448	10.0	55	.06
70450	13.0	55	.07




### 704 Nut Setters Standard. 1/4" Hex Inch Permanent industrial magnet.

Item No.	Length	mm	lbs.
70462	2.5"	65	.06
70463	4.0"	102	.10
70464	6.0"	152	.15
70466	12.0"	305	.27



### 704 Nut Setters Standard. 5/16" Hex Inch Permanent industrial magnet.


Item No.	Length	mm	lbs.
70468	2.5"	65	.07
70469	4.0"	102	.12
70470	6.0"	152	.17
70472	12.0"	305	.28



### 704 Nut Setters Standard. 3/8" Hex Inch Permanent industrial magnet.

Item No.	Length	mm	lbs.
70474	2.5"	65	.08
70476	4.0"	102	.14
70477	6.0"	152	.18
70479	12.0"	305	.41

Non Magnetic



### 704 Nut Setters Standard. 1/4" Hex Inch Permanent industrial magnet.

Item No.	Size	mm	lbs.
70424	1/4	55	.05
70427	5/16	55	.05
70430	3/8	55	.06



### 70494 3 pc. Hex Metric Nut Setter Set Permanent industrial magnet. 55mm OAL Hex Metric Nut Setters.

Item No.	lbs.	Set includes
70494	.21	7, 8, 10 x 55mm



### 70490 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 65mm OAL Hex Inch Nut Setters.

Item No.	lbs.	Set includes
70490	.25	1/4, 5/16, 3/8 x 2.5"



### 70491 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 102mm OAL

Item No.	lbs.	Set includes
70491	.39	the following: 1/4, 5/16, 3/8 x 4.0"



### 70492 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 152mm OAL

Item No.	lbs.	Set includes
70492	.54	the following: 1/4, 5/16, 3/8 x 6.0"



### 70493 3 pc. Hex Inch Nut Setter Set Permanent industrial magnet. 305mm OAL

Item No.	lbs.	Set includes
70493	1.03	the following: 1/4, 5/16, 3/8 x 12.0"



Canvas Belt Clip Pouch



### 74990 19 Pc. Quick Change Bit Belt Pack Set, Includes: 1/4" SlimFix bit holder and the following 1/4" bits and Nut Setters:

- Slotted - Power: 4.5, 5.5, 6.5mm x 50mm
- ⊕ Phillips - Power: #1, #2, #3 x 50mm
- Square - Power: #1, #2, #3 x 50mm
- ⊛ Torx® - Insert: T10, T15, T20, T25, T27, T30 x 25mm
- Nut Setters-Power: 1/4, 5/16, 3/8" Magnetic lbs. .93

**Wiha TORX®, TORXPlus® & Security TORX® Bit Sockets**



**761 TORX® Sockets** 1/4" Square Drive

Item	No.	Size	mm	lbs.
	76106	T6	38	.04
	76107	T7	38	.04
	76109	T8	38	.04
	76111	T9	38	.04
	76113	T10	38	.04
	76117	T15	38	.04
	76119	T20	38	.04
	76121	T25	38	.04
	76123	T27	38	.04
	76129	T30	38	.05
	76131	T40	38	.05



**763 TORX® Sockets** 3/8" Square drive, Set screw replaceable bit. 1/4" bits.

Item	No.	Size	mm	lbs.
	76312	T9	42	.09
	76314	T10	42	.09
	76316	T15	42	.09
	76318	T20	42	.09
	76322	T25	42	.09
	76324	T27	42	.09
	76326	T30	42	.09
	76328	T40	42	.09



**763 TORX® Sockets** 3/8" Square drive, Set screw replaceable bit. 5/16" bits. 2" OAL

Item	No.	Size	mm	lbs.
	76346	T40	51	.11
	76348	T45	51	.11
	76352	T50	51	.11
	76354	T55	51	.13

**1/2" Square Drive Sockets**



**764 TORX® Sockets** 1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76403	T30	59	.10	1
	76404	T40	59	.10	1
	76405	T45	59	.10	1
	76406	T50	59	.10	1
	76407	T55	59	.11	1
	76408	T60	59	.11	1



**763 Security TORX® Sockets** 3/8" Square drive, 5/16" bits.

Item	No.	Size	mm
	76339	T40s	51
	76340	T45s	51
	76341	T50s	51
	76342	T55s	51



**763 Security TORX® Sockets** 1/4" Square drive, 1/4" bits.

Item	No.	Size	mm
	76329	T7s	38
	76330	T8s	38
	76331	T9s	38
	76332	T10s	38
	76333	T15s	38
	76334	T20s	38
	76335	T25s	38
	76336	T27s	38
	76337	T30s	38
	76338	T40s	38



**701 Security TORX® Sockets** 3/8" Square drive, 1/4" bits. 2" OAL

Item	No.	Size	mm	lbs.
	70107	T7s	42	.09
	70108	T8s	42	.09
	70109	T9s	42	.09
	70110	T10s	42	.09
	70113	T15s	42	.09
	70115	T20s	42	.09
	70117	T25s	42	.09
	70119	T27s	42	.09
	70121	T30s	42	.09
	70123	T40s	42	.09



**764 Security TORX® Sockets** 1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76411	T40s	59	.11	1
	76412	T45s	59	.11	1
	76413	T50s	59	.11	1
	76414	T55s	59	.12	1



**716 TORXPlus® Sockets** 1/4" Square Drive, Set Screw Replaceable Bit. 1/4" bits

Item	No.	Size	mm	lbs.
	71661	IP6	38	.04
	71662	IP7	38	.04
	71663	IP8	38	.04
	71664	IP9	38	.04
	71665	IP10	38	.04
	71666	IP15	38	.04
	71667	IP20	38	.04
	71668	IP25	38	.04
	71669	IP27	38	.04
	71670	IP30	38	.04
	71671	IP40	38	.04



**716 TORXPlus® Sockets** 3/8" Square Drive, Set Screw Replaceable Bit. 1/4" bits

Item	No.	Size	mm	lbs.
	71673	IP9	42	.09
	71674	IP10	42	.09
	71675	IP15	42	.09
	71676	IP20	42	.09
	71677	IP25	42	.09
	71678	IP27	42	.09
	71680	IP30	42	.09
	71681	IP40	42	.09

**1/2" Square Drive Sockets**



**764 Slotted Bit Sockets** 1/2" Square Drive

Item	No.	mm	mm	lbs.	pkg.
	76417	8	59	.12	1
	76418	10	59	.12	1
	76419	12	59	.12	1



**764 Phillips Bit Sockets** 1/2" Square Drive

Item	No.	Size	mm	lbs.	pkg.
	76422	2	59	.15	1
	76423	3	59	.15	1
	76424	4	59	.15	1

## Hex Inch/Metric Bit Sockets



**713 Hex Sockets** 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
71371	1/16	38	.05	
71370	5/64	38	.05	
71372	3/32	38	.05	
71374	7/64	38	.05	
71376	1/8	38	.05	
71378	9/64	38	.05	
71380	5/32	38	.05	
71382	3/16	38	.05	
71384	7/32	38	.05	
71386	1/4	38	.05	



**713 Hex Sockets** 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM tool steel.

Item				
No.	Inch	mm	lbs.	
71375	1/8	42	.09	
71377	9/64	42	.09	
71379	5/32	42	.09	
71381	3/16	42	.09	
71383	7/32	42	.09	
71385	1/4	42	.09	
71388	5/16	42	.10	
71390	3/8	42	.10	



**713 Hex Metric Sockets** 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71301	1.5	38	.04	
71302	2.0	38	.04	
71305	2.5	38	.04	
71313	3.0	38	.04	
71314	4.0	38	.04	
71317	5.0	38	.05	
71319	6.0	38	.05	
71327	8.0	38	.05	
71340	10.0	38	.05	



**713 Hex Metric Sockets** 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71300	2.0	42	.09	
71316	2.5	42	.09	
71341	3.0	42	.09	
71331	4.0	42	.09	
71323	5.0	42	.09	
71325	6.0	42	.09	
71320	8.0	42	.10	
71322	10.0	42	.11	



**713 Hex Metric Sockets** 3/8" Square drive socket. Replaceable bit. 5/16" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71332	12.0	75	.22	



**761 Security Hex Inch Sockets** 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
76164	5/64	42	.09	
76165	3/32	42	.09	
76166	7/64	42	.09	
76167	1/8	42	.09	
76168	9/64	42	.09	
76169	5/32	42	.09	
76170	3/16	42	.09	
76171	7/32	42	.09	
76172	1/4	42	.09	



**761 Security Hex Metric Sockets** 3/8" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
76132	2.0	42	.09	
76133	2.5	42	.09	
76134	3.0	42	.09	
76135	4.0	42	.09	
76136	5.0	42	.09	
76137	6.0	42	.09	
76138	8.0	42	.09	

## Wiha Ball End Hex Inch & Metric Bit Sockets



**717 Ball End Hex Inch Sockets** 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	Inch	mm	lbs.	
71761	3/32	38	.05	
71762	7/64	38	.05	
71763	1/8	38	.05	
71764	9/64	38	.05	
71765	5/32	38	.05	
71766	3/16	38	.05	
71767	7/32	38	.05	
71768	1/4	38	.05	



**717 Ball End Hex Metric Sockets** 1/4" Square drive socket. Replaceable bit. 1/4" bits CVM steel.

Item				
No.	mm	mm	lbs.	
71771	1.5	51	.11	
71772	2.0	51	.11	
71773	2.5	51	.11	
71774	3.0	51	.11	
71775	4.0	51	.11	
71776	5.0	51	.12	
71777	6.0	51	.12	

## Socket Adapters



**721 Hex To Square** 1/4" socket bit adapter.

Item				
No.	Size	mm	Drive	lbs.
72110	1/4"	25	1/4"	.03
72115	1/4"	30	3/8"	.05



**724 Tool Shaft** 1/4" drive socket power adapter.





Item				
No.	Drive	mm	Drive	lbs.
72401	1/4"	100	1/4"	.09
72405	1/4"	50	1/4"	.03
72410	1/4"	100	3/8"	.17
72415	1/4"	50	3/8"	.06



**Wiha Bit Holding Socket Replacements**







**72014 1/4" Drive Bit Holding Socket With Retaining Ring** For 1/4" drive bits.

Item				
No.	Bit	mm	Drive	lbs.
72014	1/4"	25	1/4"	.04







**72038 3/8" Drive Bit Holding Socket With Retaining Ring** For 1/4" drive bits.

Item				
No.	Bit	mm	Drive	lbs.
72038	1/4"	25	3/8"	.08






**72040 3/8" Drive Bit Holding Socket With Retaining Ring** For 5/16" drive bits.


Item				
No.	Bit	mm	Drive	lbs.
72040	5/16"	25	3/8"	.08

**Wiha Long Blade Sockets & Sets**






**771 Hex Inch Sockets**  
1/4" Drive 6" Long Bit Socket

Item			
No.	Inch	Inch	lbs.
77128	3/32	6	.12
77130	7/64	6	.12
77132	1/8	6	.12
77134	9/64	6	.12
77136	5/32	6	.12
77138	3/16	6	.12
77139	7/32	6	.12
77141	1/4	6	.12

**77191 8 Pc. Hex Inch Socket Blade Set**  
Inch: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"  wt. .97






**771 Hex Inch Sockets**  
3/8" Drive 6" Long Bit Socket

Item			
No.	Inch	Inch	lbs.
77165	3/32	6	.12
77167	7/64	6	.12
77169	1/8	6	.12
77171	9/64	6	.12
77173	5/32	6	.12
77175	3/16	6	.12
77177	7/32	6	.12
77179	1/4	6	.12







**771 Hex Metric Sockets**  
3/8" Drive 6" Long Bit Socket

Item			
No.	Inch	Inch	lbs.
77180	2.5	6	.12
77182	3.0	6	.12
77184	4.0	6	.12
77186	5.0	6	.12
77188	6.0	6	.12

**Impact Bit Holding Sockets**






**720 Impact Bit Holding Socket With Retaining Ring** For 5/16" drive bits.


Item				
No.	Bit	mm	Drive	lbs.
72004	5/16"	25	1/4"	.04
72005	5/16"	30	3/8"	.04
72006	5/16"	35	1/2"	.04

**Wiha Long Blade Sockets & Sets**






**771 Hex Metric Sockets**  
1/4" Drive 6" Long Bit Socket


Item			
No.	mm	Inch	lbs.
77140	2.5	6	.12
77142	3.0	6	.12
77144	4.0	6	.12
77146	5.0	6	.12
77148	6.0	6	.12

**77192 5 Pc. Hex Metric Socket Blade Set**  
Metric: 2.5, 3.0, 4.0, 5.0, 6.0mm  lbs. .51







**771 TORX® Sockets**  
1/4" Drive 6" Long Bit Socket


Item			
No.	Size	Inch	lbs.
77151	T8	6	.12
77153	T9	6	.12
77152	T10	6	.12
77154	T15	6	.12
77156	T20	6	.12
77158	T25	6	.12
77160	T27	6	.12
77162	T30	6	.12
77164	T40	6	.12

**77193 7 Pc. TORX® Socket Blade Set**  
TORX®: T10, T15, T20, T25, T27, T30, T40  wt. .69






**720 Impact Bit Holding Socket With Retaining Ring** For 1/4" drive insert bits.


Item				
No.	Bit	mm	Drive	lbs.
72001	1/4"	25	1/4"	.05
72002	1/4"	30	3/8"	.10
72003	1/4"	35	1/2"	.21


**72090 3 Piece Bit Holding Socket Set**  
for use with 1/4" insert bits  
Drive:  lbs.  
1/4", 3/8", 1/2" .40




**771 TORX® Sockets**  
3/8" Drive 6" Long Bit Socket

Item			
No.	Size	Inch	lbs.
77101	T8	6	.12
77103	T9	6	.12
77105	T10	6	.12
77107	T15	6	.12
77109	T20	6	.12
77111	T25	6	.12
77113	T27	6	.12
77115	T30	6	.12
77117	T40	6	.12

**77195 9 Pc. TORX® Socket Blade Set**  
TORX®: T8, T9, T10, T15, T20, T25, T27, T30, T40  wt. 1.08



**77198 22 Pc. Hex & TORX® Long Blade Socket Set, 1/4" Drive**  
Inch Hex: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4"  
Metric Hex: 2.5, 3.0, 4.0, 5.0, 6.0mm  
TORX®: T8, T9, T10, T15, T20, T25, T27, T30, T40  lbs. 2.82

## Wiha Socket Sets On Molded Rails




**76194 6 pc. TORX® Socket Set**  
1/4" Square Drive Replaceable Bit Socket.  
Bits CVM tool steel.

Item No.	lbs.	Set includes the following:
76194	.20	T10, T15, T20, T25, T27, T30



**76395 8 pc. TORX® Socket Set**  
3/8" Square Drive Replaceable Bit Socket.  
Bits CVM tool steel. OAL 1.5"

Item No.	lbs.	Set includes the following:
76395	.75	T9, T10, T15, T20, T25, T27, T30, T40



**70195 10 pc. Security TORX® Socket Set**  
1/4" Square drive replaceable bit socket.  
1/4" Bits CVM tool steel.

Item No.	lbs.	Set includes the following:
70195	.48	T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s




**76191 10 pc. TORX® Socket Set**  
1/4" Square Drive Replaceable Bit Socket.  
Bits CVM tool steel. OAL 1.5"

Item No.	lbs.	Set includes the following:
76191	.49	T7, T8, T9, T10, T15, T20, T25, T27, T30, T40




**76396 8 pc. TORX® Socket Set**  
3/8" Square Drive Replaceable Bit Socket.  
1/4" & 5/16" Bits CVM tool steel. OAL 1.65"

Item No.	lbs.	Set includes the following:
76396	.84	1/4": T20, T25, T27, T30, T40, 5/16": T45, T50, T55




**76397 9 pc. Security TORX® Socket Set**  
1/4" & 3/8" Sq. Drive Replaceable Bit Socket.  
1/4" & 5/16" Bits CVM tool steel.

Item No.	lbs.	Set includes the following:
76397	.85	1/4": T10s, T15s, T20s, T25s, T27s, T30s 3/8": T40s (1/4" bit) 3/8": T45s, T50s (5/16" bit)



**76490 6 pc. TORX® Socket Set**  
1/2" Square Drive Replaceable Bit Socket.  
Bits CVM tool steel.

Item No.	lbs.	Set includes the following:
76490	1.06	T30, T40, T45, T50, T55, T60



**71698 8 pc. TORXPlus® Socket Set On Rail, In Vinyl Pouch**  
1/4" & 3/8" Square Drive Replaceable Bit Socket. Bits CVM tool steel.

Item No.	lbs.	Set includes the following:
71698	.60	1/4": IP9, IP10, IP15, IP20 3/8": IP25, IP27, IP30, IP40




**76399 12 pc. Security TORX® Socket Set**  
1/4" & 3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.


Item No.	lbs.	Set includes the following:
76399	.80	1/4": T7s, T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s 5/16": T45s, T50s, T55s


**Wiha Socket Sets On Molded Rails**




**71391 10 Piece Hex Inch Socket Set**  
 1/4" Square drive replaceable bit socket.  
 Bits CVM tool steel. OAL 1.5"  
**Item**   
**No.** lbs. **Set includes the following:**  
**71391** .48 1/16, 5/64, 3/32, 7/64, 1/8  
 9/64, 5/32, 3/16, 7/32, 1/4"




**71392 8 Piece Hex Inch Socket Set**  
 3/8" Square Drive Replaceable Bit Socket.  
 1/4" Bits CVM tool steel. OAL 1.65"  
**Item No.**   
**71392** lbs. **Set includes the following:**  
 .78 1/8, 9/64, 5/32, 3/16,  
 7/32, 1/4, 5/16, 3/8"




**71798 8 Pc. Ball End Hex Inch Socket Set**  
 1/4" Square Drive Replaceable Bit Socket.  
 1/4" Bits CVM tool steel.  
**Item No.**   
**71798** lbs. **Set includes the following:**  
 .80 3/32, 7/64, 1/8, 9/64, 5/32,  
 3/16, 7/32, 1/4"





**71393 5 Piece Hex Inch Socket Set**  
 3/8" Square Drive Replaceable Bit Socket.  
 1/4" Bits CVM tool steel.  
**Item No.**   
**71393** lbs. **Set includes the following:**  
 .54 Hex Inch: 1/8, 3/16, 1/4,  
 5/16, 3/8"





**71398 7 Pc. Ball End Hex Inch Socket Set**  
 1/4" Square Drive Replaceable Bit Socket.  
 1/4" Bits CVM tool steel.  
**Item No.**   
**71398** lbs. **Set Includes:** 3/32, 1/8,  
 .48 9/64, 5/32, 3/16, 7/32, 1/4"





**71394 5 Piece Hex Metric Socket Set**  
 3/8" Square Drive Replaceable Bit Socket.  
 1/4" Bits CVM tool steel.  
**Item No.**   
**71394** lbs. **Set includes the following:**  
 .56 Hex Metric: 4.0, 5.0, 6.0,  
 8.0, 10.0mm





**71797 7 Pc. Ball End Hex Metric Socket Set**  
 1/4" Square Drive Replaceable Bit Socket.  
 1/4" Bits CVM tool steel.  
**Item No.**   
**71797** lbs. **Set includes the following:**  
 .72 Hex Metric: 1.5, 2.0, 2.5, 3.0,  
 4.0, 5.0, 6.0mm




**71996 9 Piece Hex Metric Socket Set**  
 1/4" & 3/8" Square Drive Replaceable Bit  
 Socket. 1/4" Bits CVM tool steel. OAL 1.65"  
**Item No.**   
**71996** lbs. **Set includes the following:**  
 .66 1/4": 1.5, 2.0, 2.5, 3.0, 4.0mm  
 3/8": 5.0, 6.0, 8.0, 10.0mm






**71999 9 Pc. Security Hex Inch Socket Set**  
 3/8" Square Drive Replaceable Bit Socket.  
 1/4" Bits CVM tool steel.  
**Item No.**   
**71999** lbs. **Set includes the following:**  
 .86 Inch: 5/64, 3/32, 7/64, 1/8,  
 9/64, 5/32, 3/16, 7/32, 1/4"




**71989 7 Pc. Security Hex Metric Socket Set**  
 3/8" Square Drive Replaceable Bit  
 Socket. 1/4" Bits CVM tool steel.  
**Item No.**   
**71989** lbs. **Set includes the following:**  
 .72 Metric: 2.0, 2.5, 3.0, 4.0,  
 5.0, 6.0, 8.0mm

**Wiha Universal Socket Rail System**




**91095 Universal Rail For 1/4, 3/8 and 1/2" Sockets** Select any combination of socket drive sizes. Socket snaps firmly into place for a secure hold. Clips required.  
**Item**     
**No.** lbs. pkg. lbs.  
**91095** .057 1 .06




**91110 Replacement 1/4" Clips For The Universal Socket Rail** Package of 10 pieces.  
**Item No.**  lbs.  
**91110** .03



**91112 Replacement 3/8" Clips For The Universal Socket Rail** Package of 10 pieces.  
**Item No.**  lbs.  
**91112** .03



**91114 Replacement 1/2" Clips For The Universal Socket Rail** Package of 10 pieces.  
**Item No.**  lbs.  
**91114** .05

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
28103	40	70153	12	70540	12	71166	17	71360	19	71509	8
28180	42	70154	12	70545	12	71182	29	71361	19	71510	8
28489	40	70155	12	70550	12	71183	29	71362	19	71513	10
28589	39	70156	12	70556	12	71195	10	71363	19	71515	8
28590	39	70157	12	70557	12	71198	17	71364	19	71516	29
28593	39	70158	12	70558	12	71199	16	71365	19	71517	29
28595	39	70159	12	70559	12	71200	26	71366	19	71518	29
35512	28	70160	12	70560	12	71201	26	71367	19	71520	8
35514	28	70163	12	70561	12	71202	26	71368	19	71521	29
35516	28	70168	12	70562	12	71203	26	71369	19	71522	29
38003	10	70175	21	70563	12	71211	29	71370	52	71523	8
38006	38	70176	21	70564	12	71212	29	71371	52	71524	8
38009	13	70190	13	70565	12	71213	29	71372	52	71525	8
38010	13	70195	54	70566	12	71221	29	71373	19	71527	8
38014	22	70401	18	70567	12	71223	29	71374	52	71530	8
38025	41	70405	18	70568	12	71243	26	71375	52	71536	11
38032	32	70410	26	71001	24	71250	26	71376	52	71537	11
38033	38	70411	10	71002	24	71251	26	71377	52	71538	11
38035	32	70414	10	71003	24	71252	26	71378	52	71540	8
38041	32	70416	10	71004	24	71253	26	71379	52	71541	11
38042	13	70417	10	71010	29	71254	26	71380	52	71542	11
38043	32	70424	50	71011	29	71300	52	71381	52	71543	11
38044	10	70427	50	71012	29	71301	52	71382	52	71544	11
38045	10	70430	50	71013	29	71302	52	71383	52	71545	11
38046	13	70437	50	71020	29	71303	19	71384	52	71546	11
38047	13	70438	50	71021	29	71304	21	71385	52	71547	11
38048	32	70440	50	71022	29	71305	52	71386	52	71548	8
38049	22	70442	50	71023	29	71306	19	71387	19	71549	8
38050	32	70445	50	71030	24	71307	21	71388	52	71550	8
38051	32	70448	50	71031	24	71308	19	71390	52	71551	8
38056	23	70450	50	71032	24	71309	19	71391	55	71552	8
38057	22	70462	50	71034	24	71310	21	71392	55	71553	8
38058	22	70463	50	71035	24	71311	21	71393	55	71554	8
38060	42	70464	50	71036	24	71312	19	71394	55	71555	8
38450	40	70466	50	71051	25	71313	52	71396	19	71556	8
38460	40	70468	50	71052	25	71314	52	71397	19	71557	8
38490	38	70469	50	71053	25	71315	19	71398	55	71558	8
38600	40	70470	50	71054	25	71316	52	71404	18	71559	8
38701	42	70472	50	71055	25	71317	52	71424	18	71560	8
38790	42	70474	50	71056	16	71318	19	71431	41	71561	8
38800	40	70476	50	71090	37	71319	52	71433	41	71563	30
38801	40	70477	50	71094	29	71320	52	71435	41	71564	30
48400	40	70479	50	71095	36	71321	19	71437	41	71565	30
48401	40	70480	50	71100	16	71322	52	71439	41	71566	30
52650	40	70481	50	71101	16	71323	52	71441	41	71567	30
66850	40	70482	50	71102	16	71324	19	71452	18	71568	30
70107	51	70483	50	71103	16	71325	52	71453	18	71570	8
70108	51	70484	50	71106	17	71326	19	71455	18	71571	8
70109	51	70485	50	71107	17	71327	52	71456	18	71576	29
70110	51	70486	50	71111	29	71328	19	71464	18	71578	29
70113	51	70490	50	71112	29	71329	19	71465	18	71582	29
70115	51	70491	50	71113	29	71330	19	71466	18	71585	30
70117	51	70492	50	71122	30	71331	52	71474	41	71587	30
70119	51	70493	50	71123	30	71332	52	71475	41	71603	14
70121	51	70494	50	71125	16	71333	19	71476	41	71604	14
70123	51	70507	12	71126	17	71336	19	71477	41	71605	14
70127	12	70508	12	71130	41	71339	19	71478	41	71606	14
70128	12	70509	12	71131	41	71340	52	71479	41	71607	14
70129	12	70510	12	71132	16	71341	52	71480	28,42	71608	14
70135	12	70515	12	71133	18	71342	19	71491	42	71609	14
70139	12	70520	12	71135	18	71343	21	71492	41	71610	14
70142	12	70525	12	71139	41	71345	19	71493	41	71615	14
70143	28	70527	12	71142	30	71346	21	71494	41	71620	14
70144	28	70530	12	71143	30	71348	19	71496	41	71625	14
70145	28	70533	12	71149	16	71349	21	71499	41	71627	14
70146	28	70534	12	71150	16	71351	19	71500	10	71630	14
70147	28	70535	12	71151	16	71352	21	71502	10	71631	14
70148	12	70536	12	71152	16	71353	19	71505	8	71632	14
70150	12	70537	12	71153	16	71354	21	71506	8	71633	14
70151	12	70538	12	71154	16	71356	19	71507	8	71634	14
70152	12	70539	12	71155	16	71359	19	71508	8	71635	14



Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
71636	14	71750	21	71959	27	72519	16	73314	11	74069	25
71637	14	71760	21	71960	21	72521	16	73315	11	74100	17
71638	14	71761	52	71963	28	72522	16	73316	11	74101	30
71639	14	71762	52	71964	28	72523	16	73317	11	74102	17
71640	14	71763	52	71965	28	72525	8	73318	11	74103	17
71641	14	71764	52	71966	28	72527	8	73319	11	74104	17
71642	14	71765	52	71970	21	72528	8	73320	11	74105	30
71643	14	71766	52	71971	21	72529	8	73901	26	74106	17
71644	14	71767	52	71972	21	72530	8	73902	26	74107	17
71645	14	71768	52	71973	21	72531	8	73903	26	74108	30
71648	15	71771	52	71974	21	72534	24	73905	25	74109	17
71650	15	71772	52	71975	21	72535	24	73906	25	74111	17
71652	15	71773	52	71976	21	72536	24	73907	25	74112	17
71654	15	71774	52	71977	21	72537	24	73908	25	74113	17
71656	15	71775	52	71978	21	72538	24	73909	25	74115	17
71657	15	71776	52	71979	21	72539	24	73910	25	74116	17
71658	15	71777	52	71980	21	72540	8	73912	17	74118	17
71660	15	71797	55	71981	21	72541	8	73913	17	74121	17
71661	51	71798	55	71982	21	72542	12	73914	17	74123	17
71662	51	71801	24	71983	21	72545	8	73915	17	74124	17
71663	51	71802	24	71984	21	72546	8	73916	17	74126	17
71664	51	71803	24	71985	21	72547	12	73919	20	74127	17
71665	51	71851	24	71988	36	72550	8	73920	20	74130	17
71666	51	71852	24	71989	55	72551	8	73921	20	74131	17
71667	51	71853	24	71990	36	72552	12	73922	20	74133	17
71668	51	71854	24	71991	36	72555	8	73923	20	74136	17
71669	51	71900	27	71992	36	72556	8	73924	20	74141	29
71670	51	71901	27	71994	36	72557	12	73925	20	74142	29
71671	51	71902	27	71995	22	72558	12	73926	20	74143	29
71673	51	71903	27	71996	55	72559	12	73928	20	74150	17
71674	51	71904	27	71998	22	72560	12	73929	20	74157	17
71675	51	71905	27	71999	55	72561	12	73930	20	74158	17
71676	51	71906	27	72001	53	72562	12	73931	20	74161	29
71677	51	71907	27	72002	53	72563	12	73932	20	74163	29
71678	51	71908	27	72003	53	72564	12	73933	20	74164	17
71680	51	71909	27	72004	53	72567	12	73934	20	74165	17
71681	51	71910	27	72005	53	72568	12	73936	9	74166	17
71690	14	71911	27	72006	53	72569	8	73937	9	74167	17
71692	14	71912	27	72014	53	72570	8	73938	9	74168	17
71698	54	71913	27	72031	25	72572	8	73939	9	74201	26
71701	20	71914	28	72038	53	72573	8	73940	9	74203	26
71702	20	71916	28	72039	25	72574	8	73941	9	74205	26
71703	20	71918	28	72040	53	72575	8	73942	9	74212	26
71704	20	71920	28	72047	25	72576	8	73943	9	74214	26
71705	20	71921	27	72049	25	72577	8	73944	9	74221	26
71706	20	71922	27	72050	25	72578	8	73945	9	74231	26
71707	20	71923	27	72051	25	72579	8	73946	9	74232	26
71708	20	71924	27	72090	53	72580	8	74003	25	74233	26
71711	20	71930	21	72102	17	72581	8	74006	25	74236	26
71712	20	71932	21	72103	17	72582	19	74009	25	74237	26
71713	20	71934	21	72104	17	72583	19	74010	25	74238	26
71714	20	71936	21	72110	52	72584	19	74012	25	74241	29
71715	20	71938	21	72115	52	72585	19	74015	25	74242	29
71716	20	71939	21	72388	19	72586	19	74018	25	74243	29
71717	20	71940	21	72401	25	72587	19	74021	25	74261	26
71718	20	71941	21	72405	52	72590	10	74023	25	74262	26
71719	20	71942	21	72410	52	72593	39	74033	25	74263	26
71720	20	71943	21	72415	52	72595	10	74034	25	74301	21
71721	20	71944	21	72502	19	72596	22	74035	25	74303	18,25
71722	20	71945	21	72503	19	73301	19	74036	25	74304	18
71723	20	71946	21	72504	19	73302	19	74039	25	74305	21
71724	20	71949	27	72506	19	73303	19	74041	25	74306	18,25
71725	20	71950	27	72507	19	73304	19	74050	25	74307	21
71726	21	71951	27	72508	19	73305	19	74061	25	74308	18
71728	21	71952	27	72509	19	73306	19	74062	25	74309	18,25
71730	21	71953	27	72511	19	73307	19	74063	25	74310	18
71732	21	71954	27	72512	19	73308	19	74064	25	74311	20
71734	21	71955	21	72513	19	73309	19	74065	25	74312	20
71736	21	71956	21	72514	12	73310	11	74066	25	74313	20
71738	21	71957	27	72515	12	73311	11	74067	25	74314	20
71740	21	71958	27	72516	12	73312	11	74068	25	74315	20

58 Tools that work for you

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
74316	20	74512	9	74587	9	74962	27	75614	43	75709	44
74317	20	74513	9	74588	9	74963	27	75615	43	75710	44
74318	20	74514	9	74589	9	74964	27	75616	43	75715	44
74319	21	74515	9	74590	9	74965	27	75617	43	75720	44
74325	20	74516	9	74591	9	74966	27	75618	43	75735	44
74330	20	74517	9	74601	14	74967	27	75619	43	75742	44
74332	20	74518	9	74602	14	74968	27	75620	43	75743	45
74333	20	74519	9	74603	14	74981	11	75621	43	75744	45
74334	20	74520	15	74604	14	74982	14	75622	43	75745	45
74335	20	74521	9	74608	14	74983	39	75623	43	75746	45
74336	20	74522	15	74611	14	74985	10	75624	43	75747	45
74337	20	74523	9	74612	14	74986	22	75626	43	75748	45
74340	20	74524	15	74613	14	74987	13	75627	43	75800	44
74342	20	74525	9	74614	14	74988	39	75628	43	75801	44
74343	20	74526	15	74616	14	74990	50	75629	43	75802	45
74344	20	74527	9	74617	14	74992	38	75630	43	75803	45
74345	20	74528	15	74620	14	74996	38	75631	43	75805	49
74346	20	74529	9	74624	14	74999	23	75632	43	75806	45
74348	20	74530	9	74628	14	75008	44	75633	43	75810	45
74349	20	74531	9	74632	14	75012	44	75634	43	75811	45
74350	20	74532	15	74636	14	75015	44	75635	43	75812	45
74351	20	74533	9	74659	14	75018	44	75636	43	75813	45
74352	20	74534	15	74660	14	75020	44	75637	43	75814	45
74353	20	74535	9	74661	14	75025	44	75638	43	75815	45
74354	20	74536	9	74662	14	75030	44	75639	43	75816	45
74355	20	74537	15	74663	14	75035	44	75640	43	75817	45
74356	20	74538	9	74664	14	75040	44	75641	43	75820	45
74357	20	74539	15	74665	14	75093	49	75642	43	75821	45
74360	20	74540	9	74666	14	75094	49	75643	43	75822	45
74361	20	74541	15	74667	14	75095	49	75644	43	75823	45
74362	20	74542	9	74668	14	75096	49	75645	43	75824	45
74363	20	74543	15	74669	14	75097	49	75646	43	75825	45
74364	20	74544	9	74670	14	75105	44	75647	43	75826	45
74365	20	74545	15	74711	11	75110	44	75648	43	75827	45
74366	20	74546	9	74714	11	75115	44	75649	43	75900	45
74369	21	74547	15	74717	11	75120	44	75650	43	75901	45
74371	21	74548	9	74721	11	75125	44	75651	43	75902	45
74373	21	74549	15	74724	11	75307	44	75652	43	75965	48
74375	21	74550	15	74728	11	75309	44	75653	43	75968	48
74379	21	74551	9	74732	11	75313	44	75654	43	75971	48
74380	20	74552	15	74736	11	75315	44	75655	43	75977	48
74381	20	74553	9	74739	11	75320	44	75656	43	75980	48
74382	20	74554	15	74742	11	75322	44	75657	43	75981	49
74383	20	74555	15	74760	11	75325	44	75658	43	75982	46
74384	20	74556	9	74761	11	75330	44	75659	43	75983	49
74385	20	74557	15	74762	11	75332	44	75660	43	75984	46
74386	20	74558	9	74763	11	75340	44	75661	43	75985	49
74387	20	74559	9	74764	11	75342	44	75662	43	75986	46
74388	20	74561	9	74765	11	75350	44	75663	43	75987	46
74413	9	74562	15	74766	11	75352	44	75664	43	75988	46
74415	9	74563	9	74767	11	75354	44	75665	43	75991	47
74417	9	74564	15	74768	11	75356	44	75666	43	75992	47
74419	9	74565	9	74769	11	75358	44	75667	43	75993	48
74431	9	74566	12	74811	24	75360	44	75668	43	75994	47
74433	9	74567	9	74812	24	75362	44	75669	43	75995	47
74435	9	74568	12	74813	24	75364	44	75670	43	75996	47
74461	9	74569	9	74814	24	75366	44	75671	43	75999	47
74462	9	74570	12	74816	24	75368	44	75672	43	76000	13,18,23,31
74463	9	74571	9	74819	24	75370	44	75673	43	76001	23
74464	9	74572	12	74860	24	75372	44	75674	43	76002	23
74465	9	74573	9	74861	24	75395	47	75675	43	76003	23
74468	9	74574	12	74862	24	75602	43	75676	43	76004	23
74469	9	74575	9	74890	24	75603	43	75677	43	76005	23
74470	9	74576	12	74895	24	75604	43	75681	43	76006	23
74501	9	74577	9	74901	27	75605	43	75683	43	76007	23
74502	9	74579	9	74903	27	75606	43	75701	44	76008	13
74503	9	74580	9	74904	27	75607	43	75702	44	76009	13
74504	9	74581	9	74911	27	75608	43	75703	44	76010	13
74505	15	74582	9	74912	27	75609	43	75704	44	76011	26
74506	9	74583	9	74913	27	75610	43	75705	44	76012	26
74508	9	74584	9	74914	27	75611	43	75706	44	76013	26
74510	9	74585	9	74915	27	75612	43	75707	44	76014	23
74511	9	74586	9	74961	27	75613	43	75708	44	76015	13

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
76016	23	76164	52	76525	5	76653	7	77109	53	77780	33
76017	23	76165	52	76526	5	76654	7	77111	53	77781	33
76018	23	76166	52	76530	5	76655	7	77113	53	77782	33
76019	23	76167	52	76531	5	76656	7	77115	53	77783	35
76021	23	76168	52	76532	5	76801	4	77117	53	77786	35
76020	13	76169	52	76533	5	76802	4	77128	53	77789	35
76022	28	76170	52	76534	5	76803	4	77130	53	77790	33
76023	28	76171	52	76535	5	76806	4	77132	53	77791	33
76024	28	76172	52	76538	4	76807	4	77134	53	77792	33
76025	13	76191	54	76539	4	76808	4	77136	53	77793	35
76027	13	76194	54	76540	4	76810	4	77138	53	77795	35
76030	13	76312	51	76543	6	76811	4	77139	53	78002	28
76031	27	76314	51	76544	6	76812	4	77140	53	78005	28
76032	27	76316	51	76545	6	76813	4	77141	53	78008	28
76033	27	76318	51	76548	6	76814	4	77142	53	78011	28
76034	27	76322	51	76549	6	76816	4	77144	53	78015	28
76035	25	76324	51	76550	6	76817	4	77146	53	78018	28
76036	25	76326	51	76553	6	76823	5	77148	53	78615	28
76037	25	76328	51	76554	6	76824	5	77151	53	78617	28
76038	25	76329	51	76555	6	76825	5	77152	53	78619	28
76039	25	76330	51	76556	6	76826	5	77153	53	78621	28
76040	13	76331	51	76557	6	76830	5	77154	53	78622	28
76041	18	76332	51	76558	6	76831	5	77156	53	78624	28
76042	18	76333	51	76559	6	76832	5	77158	53	79242	10
76043	18	76334	51	76563	6	76833	5	77160	53	79243	37
76044	18	76335	51	76564	6	76834	5	77162	53	79245	10
76045	23	76336	51	76565	6	76835	5	77164	53	79246	22
76046	23	76337	51	76566	6	76838	4	77165	53	79247	13
76047	23	76338	51	76570	6	76839	4	77167	53	79248	37
76048	23	76339	51	76571	6	76840	4	77169	53	79256	22
76049	23	76340	51	76572	6	76843	6	77171	53	79266	22
76050	23	76341	51	76573	6	76844	6	77173	53	79276	23
76051	23	76342	51	76574	6	76845	6	77175	53	79283	11
76052	23	76346	51	76575	6	76848	6	77177	53	79443	37
76053	23	76348	51	76578	6	76849	6	77179	53	79445	10
76054	23	76352	51	76579	6	76850	6	77180	53	79446	22
76056	23	76354	51	76580	6	76853	6	77182	53	79447	13
76057	23	76395	54	76581	7	76854	6	77184	53	79450	15
76058	23	76396	54	76582	7	76855	6	77186	53	79490	37
76079	31	76397	54	76583	7	76856	6	77188	53	79491	37
76084	31	76399	54	76584	7	76857	6	77191	53	79493	37
76085	31	76403	51	76585	7	76858	6	77192	53	79495	37
76086	31	76404	51	76586	7	76859	6	77193	53	79499	37
76087	31	76405	51	76587	7	76863	6	77195	53	91095	55
76088	27	76406	51	76588	7	76864	6	77198	53	91110	55
76089	28	76407	51	76589	7	76865	6	77701	8	91112	55
76090	23	76408	51	76590	7	76866	6	77702	8	91114	55
76091	26	76411	51	76591	7	76870	6	77703	8	97780	34
76092	13	76412	51	76592	7	76871	6	77704	8	97781	34
76093	25	76413	51	76593	7	76872	6	77705	8	97782	34
76094	18	76414	51	76594	7	76873	6	77707	16	97790	34
76095	23	76417	51	76595	7	76874	6	77708	16	97791	34
76096	23	76418	51	76596	7	76875	6	77710	26	97792	34
76098	31	76419	51	76597	7	76876	5	77712	24		
76099	31	76422	51	76598	7	76877	5	77713	24		
76106	51	76423	51	76601	7	76878	6	77715	24		
76107	51	76424	51	76602	7	76879	6	77716	24		
76109	51	76490	54	76603	7	76880	6	77717	24		
76111	51	76501	4	76605	7	76881	5	77719	19		
76113	51	76502	4	76610	7	76890	5	77720	19		
76117	51	76503	4	76611	7	76891	5	77721	19		
76119	51	76506	4	76612	7	76892	7	77723	19		
76121	51	76507	4	76613	7	76893	5	77724	19		
76123	51	76508	4	76614	7	76894	7	77725	19		
76129	51	76510	4	76615	7	76895	5	77726	19		
76131	51	76511	4	76616	7	76896	7	77740	33		
76132	52	76512	4	76641	7	76897	5	77741	33		
76133	52	76513	4	76642	7	76898	4,35				
76134	52	76514	4	76643	7	76899	5				
76135	52	76516	4	76645	7	77101	53				
76136	52	76517	4	76650	7	77103	53				
76137	52	76523	5	76651	7	77105	53				
76138	52	76524	5	76652	7	77107	53				

**Prop65 WARNING:** This product can expose you to chemicals including Diisononyl Phthalate, Vinyl Chloride, Ethylene Glycol, Nickel or Hexavalent Chromium Six, which is known to the State of California to cause cancer or reproductive harm. For more information, go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).



# PROFESSIONAL QUALITY BITS



(800) 494-6104  
fax: (800) 494-7456  
cservice@wihatools.com  
www.wihatools.com


Catalog Item No. 99951.wo  
version - 1/1/19

**Subject to change  
without notice**

©2019 Willi Hahn Corporation

®Torx is a registered trademark of  
Acument Intellectual Properties LLC.

	<b>Wiha Quality Tools</b> 1348 Dundas Circle Monticello, MN 55362 tel: 763.295.6591 fax: 763.295.6598	<b>Wiha Tools Canada Ltd.</b> www.wihatools.ca Brampton, ONT L6T 4X4 tel: 866.494.0096 or 763.295.6591 fax: 763.295.6598	
	To:		



99977.wo - Pliers/Crimpers Catalog



99914.wo - TORX Catalog



99001.wo - TorqueControl Catalog



99904.wo - Shop Tools Catalog



99919.wo - Insulated Catalog



99902.wo - Screwdrivers Catalog



99934.wo - Hex Tools Catalog



99906.wo - Tech Tools Catalog



99945.wo - ESD Catalog



91330.wo - Tooling Catalog