

## OHT1850X | 18V Cordless Extended Reach Hedge Trimmer, 50cm Blade



- Extended reach hedge trimmer makes easy work of trimming hard-to-reach hedges and shrubs.
- 50cm blade with 16mm blade gap to cut through branches.
- 4-position articulating head for pruning all sizes of hedges and shrubs.
- Rotating rear handle for optimum reach in all cutting applications.
- Central trigger for easy use in extended reach position.
- HedgeSweep™ debris sweeper for easy removal of clippings.

	OHT1850X
Battery pack capacity (Ah)	-
Blade length [cm]	50
Blade speed (rpm)	1200
Blade type	Diamond ground
Charger included?	No
Max. cutting capacity (mm)	16
No. of batteries supplied	0
Power	18V
Sound Power [dB Lwa]	85.6
Sound power level [dB(A)]	86
Sound power level guaranteed [dB(A)]	91
Sound power level uncertainty [dB(A)]	3
Sound pressure level (dB(A))	77
Sound pressure level uncertainty [dB(A)]	3
Supplied in	Recyclable Carton
Vibration Level Auxiliary Handle [m/s <sup>2</sup> ]	2.5
Vibration level front handle: idling [m/s <sup>2</sup> ]	1.303
Vibration level front handle: uncertainty [m/s <sup>2</sup> ]	1.5
Vibration Level Main Handle [m/s <sup>2</sup> ]	2.5
Vibration level rear handle: idling [m/s <sup>2</sup> ]	1.157
Vibration level rear handle: uncertainty [m/s <sup>2</sup> ]	1.5
Vibration uncertainty [m/s <sup>2</sup> ]	1.5