

## USB VGA Console Extender over CAT5 UTP (500 ft)

Product ID: SV565UTPUGB



The SV565UTPUGB USB VGA KVM Console Extender over CAT5 UTP (500 ft) lets you control a server, computer or multiple computers (connected through KVM Switch) over a standard Cat5 or Cat6 UTP network cable connection, at distances of up to 500 ft (150 m) away. PC connection cables are included with this product for a ready out of the box solution.

You can use your existing keyboard, mouse, and monitor to access both the server room and your office computer, saving space and avoiding the need for a dedicated remote console by allowing you to switch between workstation view and KVM view at the remote location.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Monitor computer-controlled equipment in a factory or warehouse
- Use one or more servers in a server room from a remote location
- Control remote machines and security monitoring systems

### Features

- USB computers are supported at the host and remote locations (USB keyboard and mouse required for remote console)
- Cables Included for a ready out of the box setup
- Can be used with a single computer or connected to an existing KVM switch
- Easy installation using industry-standard UTP network cable
- Intuitive hotkey commands
- Supports most combo keyboard and mouse sets (including Wireless)
- Supports auto-switching between host and remote users or dedicated control

<b>Hardware</b>	Warranty	2 Years
	Audio	No
	KVM Ports	2
	Number of Monitors Supported	1
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	No
<b>Performance</b>	IP Control	No
	Max Transfer Distance	150 m (492 ft)
	MTBF	126000 hours
	Supported Resolutions	1280x1024 @ 300ft(100m) 1024x768 @ 500ft(150m)
<b>Connector(s)</b>	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female 2 - USB Type-A (4 pin) USB 2.0 Female
	Host Connectors	1 - VGA (15 pin, High Density D-Sub) Female
	Other Interface(s)	1 - RJ-45 Female
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Special Notes / Requirements</b>	<b>Note</b>	Product weights, measurements and connectors indicate a single unit only (either Host or Remote)
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.2 A
	Input Voltage	100 - 240 AC
	Output Current	0.6 A
	Output Voltage	9 DC
	Plug Type	M
	Power Consumption (In Watts)	5.4
	Power Source	AC Adapter Included
<b>Environmental</b>	Humidity	0~80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel

	Product Height	2 cm [0.8 in]
	Product Length	75 mm [3 in]
	Product Width	15.5 cm [6.1 in]
	Weight of Product	299 g [10.6 oz]
<b>Packaging Information</b>	Package Height	90 mm [3.5 in]
	Package Length	30 cm [11.8 in]
	Package Width	25 cm [9.8 in]
	Shipping (Package) Weight	1.7 kg [3.8 lb]
<b>What's in the Box</b>	Included in Package	1 - Host Unit
		1 - Remote Unit
		2 - 6 ft 2-in-1 USB VGA KVM cables
		2 - Packs Rubber Feet
		1 - Power Adapter
		1 - Manual

Product appearance and specifications are subject to change without notice.