



Main

Range of product	OsiSense XU
Sensor name	XUY
Sensor design	Fiber design
Sheath type	Standard
[Sn] nominal sensing distance	80 mm XUYAFV
End fitting type	Straight with nickel plated brass, M4 x 0.7

Complementary

Electronic sensor type	Photo-electric sensor
Optic fiber material	50 µ glass
Sheath material	PVC + thermo polyolefine
Detection system	Diffuse
Optic fiber length	1 m
Minimum bending radius	10 mm
Head mounting	M4 x 0.7
Net weight	0.04 kg

Environment

Ambient air temperature for operation	-25...60 °C
---------------------------------------	-------------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

Contractual warranty

Warranty	18 months
----------	-----------