

# SP15NUK

Product no.: SP15NUK



## Benefits

- › Three high-temperature, long-life LEDs for superior soldering accuracy
- › Co-molded, soft-grip ribbed handle design for maximum comfort
- › Triangular area for maximum of tip control and round handle for ease of tip rotation
- › High-performance stainless steel heater
- › Applications: micro components, electronic kits, low voltage wiring, wire connection 18AWG (0.04" diameter)


For this purpose, we recommend:



Solder fume extractors



Pre-heating plates



Cleaning



Soldering tips



Technical Data

Active Tip heating element technology	---
Power Response heating element technology	---
Silver Line heating element technology	---
Voltage	230 V ~ 50 Hz
Power	15 W
Tip range	---
Supply unit	---
WX-compatible	---
Temperature range °C	400
Temperature range °F	752
Heating time	---
Safety rest	---
Safety rest (optional)	---
Barrel	---
Integrated direct extraction	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE