



- Preheating plate
- 80 W, 24 V
- Heating surface 80 x 50 mm
- Temperature range 50 °C - 200 °C
- For all Weller stations with min. 80 W
- Size housing 150 x 120 x 65 mm

### WHP 80 Preheating plate

Product no.: T0052702899N

Dimensions L x W x H (mm)	175 x 125 x 45 mm
Dimensions L x W x H (inches)	6.89 x 4.92 x 1.77 Inch
Weight (approx.) in kg	---
Voltage	24 V
Power	80 W
Channels	---
Temperature range (depends on tool) °C	66 - 204
Temperature range (depends on tool) °F	150 - 400
Temperature accuracy °C	---
Temperature accuracy °F	---
Temperature accuracy for hot air °C	---
Temperature accuracy for hot air °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	---
Display	---
Additional vacuum pump	---
Max. hot air flow rate l/min (depends on tool)	---
Capacity l/min	---
Max. vacuum	---
Interface	---