


# WXHAP 200 Set

Product no.: T0052712099N



## Benefits

- › 200 W, 24 V
- › Temperature range 50°C to 550°C
- › Blue LED light
- › Internal Parameter storage (zero tolerance)
- › Hot air flow ionic free

For this purpose, we recommend:



Solder fume extractors



Pre-heating plates



Cleaning



Soldering tips



Technical Data

|   |                      |
|---|----------------------|
| Active Tip heating element technology     | ---                  |
| Power Response heating element technology | ---                  |
| Silver Line heating element technology    | ---                  |
| Voltage                                   | 24 V                 |
| Power                                     | 200 W                |
| Tip range                                 | F, R, D, Q           |
| Supply unit                               | WXA 2, WXR 3         |
| WX-compatible                             | on                   |
| Temperature range °C                      | 100 - 550            |
| Temperature range °F                      | 200 - 999            |
| Heating time                              | ---                  |
| Safety rest                               | WDH 30 (T0051515299) |
| Safety rest (optional)                    | WDH 30 (T0051515299) |
| Barrel                                    | ---                  |
| Integrated direct extraction              | ---                  |

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE