

WP 80 Set

Product no.: T0052918199N



Benefits

- › Soldering Iron 80 W, 24 V with Tip-to-Grip position
- › For medium components with high energy demand
- › For universal soldering jobs with WT stations and WR rework stations
- › Extensive range of LT soldering tips
- › Silver-Line heating technology
- › Fast heating up

For this purpose, we recommend:



Solder fume extractors



Pre-heating plates



Cleaning



Soldering tips



Technical Data

Active Tip heating element technology	---
Power Response heating element technology	---
Silver Line heating element technology	on
Voltage	24 V
Power	80 W
Tip range	LT
Supply unit	PU 81, PUD 81, PUD 81i, PU WAD 101, PUD 121, PU WAD 101IG, PUD 151, WD 1, WD 1M, WR 2, WR 3M, WR 3ME
WX-compatible	---
Temperature range °C	50 - 450
Temperature range °F	150 - 850
Heating time	10
Safety rest	WDH 10 (T0051512199)
Safety rest (optional)	WDH 10 (T0051512199), WDH 10T (T0051516199)
Barrel	T0058744845
Integrated direct extraction	Attachment T0052918699 / T0052918599

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE