

# WS 81 SOLDERING STATION 230V UK

Soldering station, 1 channel, 80 W / 230 V, analog - UK version  
Product no.: T0053250399N



## Benefits


- › Power unit, 1 channel with soldering iron WSP 80
- › Silver-Line Technology




For this purpose, we recommend:



Solder fume extractors



Soldering irons



Cleaning




Pre-heating plates



**Technical Data**

Dimensions L x W x H (mm)	170 x 118 x 102
Dimensions L x W x H (inches)	6,69 x 4,65 x 4,02
Weight (approx.) in kg	1.89
Voltage	230 V
Power	95 W
Channels	1
Temperature range (depends on tool) °C	150 - 450
Temperature range (depends on tool) °F	302 - 842
Temperature accuracy °C	± 9
Temperature accuracy °F	± 16
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	Via 3,5 mm pawl socket on back of device (normal state hard grounded)
Display	---
Air consumption l/min	---
Operating pressure in bar/psi	---
Capacity l/min	---
Vacuum	---

Owning the bench



PROFESSIONAL



FILTRATION



EREM



XCELITE