



- Preheating plate
- 1200 W, 230 V
- Board size upto 190 x 245 mm
- Temperature range 50 °C - 400 °C
- Digital display for set and actual temperature
- Digitally controlled
- 6 Infrared high temperature ceramic elements for fast and efficient heat up
- 2 Easy Fix board holder

### WHP 3000 Infrared preheating plate

Product no.: T0053364699N

Dimensions L x W x H (mm)	254 x 395 x 70
Dimensions L x W x H (inches)	10 x 15.55 x 2.76
Weight (approx.) in kg	---
Voltage	230 V, 50/60 Hz
Power	1200 W
Channels	---
Temperature range (depends on tool) °C	---
Temperature range (depends on tool) °F	---
Temperature accuracy °C	---
Temperature accuracy °F	---
Temperature accuracy for hot air °C	---
Temperature accuracy for hot air °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	---
Display	---
Additional vacuum pump	---
Max. hot air flow rate l/min (depends on tool)	---
Capacity l/min	---
Max. vacuum	---
Interface	1 x RS232, 1 x thermocouple type K