



Main

Range of product	OsiSense XG
Accessory / separate part destination	XGCS XGSD XGSK
Product or component type	RS232/RS485 interface
Accessory / separate part type	RS232C/RS485 line adaptor

Complementary

Communication port converter	RS232C/RS485 no modem signals
Connection element	RS232/RS485 interface
Current consumption	20 mA
[I _e] rated operational current DC	20 mA
Mounting support	35 mm symmetrical DIN rail
Product mounting	35 mm symmetrical DIN rail
Product weight	0.1 kg 0.105 kg
[U _s] rated supply voltage	18...30 V DC 24 V DC
Supply voltage limits	20...30 V
Transmission rate	<= 19200 bit/s 19200 bauds
Electrical connection	Screw connectors

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1149 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

 [Product Environmental Profile](#)

Product end of life instructions

Available

 [End of Life Information](#)

Contractual warranty

Warranty period

18 months
