



### Main

Range of product	Harmony
Product or component type	Digital display body
[Us] rated supply voltage	24 V DC
Connections - terminals	Screw connectors : 0.5 x 2.5 mm <sup>2</sup>

### Complementary

Mounting support	Panel
Device mounting	Fixing hole: Ø 22.3 mm
Electronic decoding	BCD + latch
Supply voltage limits	13...30 V
Current consumption	<= 36 mA at 30 V <= 40 mA at 24 V
Protection type	Reverse polarity protection
Logic input	Positive
Voltage state 0 guaranteed	-30...5 V
Voltage state 1 guaranteed	13...30 V
Current state 0 guaranteed	<= 1.4 mA
Current state 1 guaranteed	4...9.5 mA

### Environment

Product certifications	CSA UL
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	10 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	180 gn for 11 ms conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to NF C 20-030 Class II conforming to IEC 60536
IP degree of protection	IP65 conforming to IEC 60529 IP65 conforming to NF C 20-010

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---