



### Main

Range of product	EcoStruxure operator terminal Expert
Product or component type	License
Language	French German Chinese Spanish English Italian Portuguese
Format	Paper
Previous software version	V3.0

### Complementary

Range compatibility	Magelis STO7 Magelis ST6
Software designation	EcoStruxure Operator Terminal Expert
Type of license	Single (1 seat)
Software version	V3.1
System requirements	> 1 GB HDD storage device Windows 7 Professional 32/64 bit, > 4 GB primary memory > 1 GB HDD storage device Windows 8.1, > 4 GB primary memory > 1 GB HDD storage device Windows 10, > 4 GB primary memory > 1 GB HDD storage device Windows Embedded standard 7 32/64 bit, > 4 GB primary memory
Communication port protocol	Modbus TCP slave Q series CPU direct Simatic S7 Ethernet Modbus SIO master Uni-Telway Q/QnA Series Ethernet CS/CJ series Ethernet Modbus TCP master FX series computer link CS/CJ series HOST link ROC Plus SIO SoMachine network FX series Ethernet Zelio Logic Modbus SIO slave Q series QnU CPU Ethernet IQ-R/F series Ethernet FX series CPU direct

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

CS/CJ/NJ series Ethernet/IP  
ROC Plus Ethernet  
Modbus SIO ASCII master  
Simatic S7 MPI direct  
DH485  
PacDrive  
DF1  
Ethernet/IP  
Q/QnA series serial

---

Provided equipment	User's documentation in electronic format EcoStruxure operator terminal Expert
Software function	26 type of fonts 32768 variables 32768 alarms

---

## Environment

---

Image import standard	PNG
-----------------------	-----

---