



### Main

Range of product	Harmony
Product or component type	Digital display head
Mounting diameter	22 mm
Cap/Operator or lens colour	Red
[Us] rated supply voltage	24 V DC

### Complementary

Display type	7 segments LED + decimal point
Supply voltage limits	13...30 V
Product weight	0.02 kg

### Environment

Product certifications	CSA UL
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	10 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	180 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to NF C 20-030
IP degree of protection	IP65 conforming to IEC 60529 IP65 conforming to NF C 20-010

### Contractual warranty

Warranty period	18 months
-----------------	-----------