


Cat6 Gigabit Bulk Solid PVC Cable - Blue, 1000-ft.

MODEL NUMBER: **N222-01K-BL**



Description

With Tripp Lite's new category 6 bulk solid PVC cable you can stay ahead of the game with use of this high-speed cabling to distribute data voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA, Cat6, TIA/EIA 568-b-2.1 draft 9 standards. Constructed with high-quality copper wire, near-end crosstalk levels are kept to a minimum. This 1000', Reel-in-a-Box, solid PVC cable makes industrial runs a snap. Cat6 patch cables are available in a variety of colors and sizes.

Features

- Designed for premise (in-wall) cabling applications
- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire
- Length: 1000-ft. Color: Blue Reel-in-a-Box
- 23 AWG, 4-pair solid cable with PVC (CMR) jacket
- Deliver stable performance up to 550MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)

Specifications

OVERVIEW	
UPC Code	037332123077

Highlights

- Meets category 6 cabling standards
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- 4pr Solid - CMR PVC Jacket

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications

Package Includes

- 1000Ft Cat6 Gigabit Bulk Solid Blue PVC Cable



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.8
Cable Length (in.)	12000
Cable Length (cm)	30480
PHYSICAL	
Wire Gauge (AWG)	23
Shipping Dimensions (hwd / in.)	13.78 x 14.17 x 13.78
Shipping Dimensions (hwd / cm)	35.00 x 35.99 x 35.00
Shipping Weight (lbs.)	28.00
Shipping Weight (kg)	12.70
Color	Blue
Cable Jacket Rating	CMR
Wire Type	Solid
Snagless Connector	No
Cable Shielding	UTP
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
FEATURES & SPECIFICATIONS	
Technology	Cat6
CERTIFICATIONS	
Approvals	UL verified, meets EIA/TIA CAT6 TIA/EIA- 568-B-2.1, DRAFT 9 standards
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>