


## XHM-5000

Item number 66.9425-\*

Highly flexible, with in-line Ø 4 mm MULTILAM plug with rigid insulating sleeve on both ends.

Technical data	
Diameter of plug system	4 mm
Rated Values	1000 V, CAT IV, 10 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Lead cross section	0.5 mm <sup>2</sup>
Lead lengths <input type="text"/>	150 cm
Lead insulation	TPE
Colours *	<span style="background-color: black; color: white; padding: 2px;">21</span> <span style="background-color: red; color: white; padding: 2px;">22</span> <span style="background-color: blue; color: white; padding: 2px;">23</span>
Test accessory acc. to	IEC EN 61010-031
Approvals	CE
Remarks	Rated voltage 5'000 V: Output voltage of test instruments, e.g. insulation testers