



Specifications

Electrical

Number of Contacts : 4 pin - 4 pin
Contact Resistance : $\leq 20\text{m}\Omega$
Insulation Resistance : $>1\text{G}\Omega$


Mechanical

Lifetime : >1000 cycles

Material

Shell : PA6+30% GF (GF: glass fibre)
Contacts : Bronze, Ag plated

Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
4 Pin Female-to-Female Speaker Audio Adapter	27-10156