

Female XLR 3-Pin Connector Waterproof IP67



Specifications

Electrical

Number of Contacts	: 3
Contact Resistance	: $\leq 5\text{m}\Omega$
Insulation Resistance	: $> 1\text{G}\Omega$


Mechanical

Lifetime	: > 1000 cycles
Insertion/withdrawal force	: $\leq 30\text{N}$
Cable OD. Range	: 6mm - 6.5mm

Material

Shell	: Zinc Die-cast
Contacts	: Bronze Ag plated
Protection Rating	: IP67

Diagram



Dimensions : Millimetres

Part Number Table

Description	Part Number
Female XLR 3-Pin Connector Waterproof IP67	27-10286