

# BT Elements 1K

## Block up to 80% of Nuisance Calls



Enjoy the freedom of your office, warehouse or any large outdoor environment with the outstanding range of up to 1000 metres. The new rugged design combined with reassuring weatherproof technology means you can make calls indoor or out, confident in its durability. The phone comes complete with a stand-alone base unit that can be plugged into any telephone socket or power supply, freeing up the charger pod to be plugged in anywhere you want.

Block nuisance calls - The BT Elements 1K blocks numbers in two separate ways to help you avoid nuisance calls:

### Block by Number

The BT Elements 1K can block 10 individual numbers, meaning that you really can avoid speaking to the people you don't want to.

### Block by call type

Choose the type of calls you want to block. For example, international, withheld, no caller ID or payphone numbers can all be blocked.

### Do Not Disturb

For those times when you just want some peace and quiet, switch on Do Not Disturb so that your phone won't ring or light up. If you want key friends and family to still get through, they can do, by tagging them as VIP's in your address book.

### Main Features

- Block up to 80% of Nuisance Calls
- IP67 rating
- Up to 1km range
- 200 Name & Number directory
- Auto copy contacts between handsets
- Location free base
- Record up to 30 minutes of messages
- Easy guided set up
- Outgoing call controls (PIN protect calls to premium / mobile numbers)
- Backlit keypad for easy dialling even in poor light
- Do not disturb mode
- Up to 10 hours of talking and 250 hours on standby
- See who's left you messages
- Easy access to BT calling features (3 way calling, call divert)

(N.B you must subscribe to a Caller Display service from your network provider for nuisance calls blocking, text messaging and visual voicemail features. Charges may apply)

# BT Elements 1K

## Product Specification

GAP compatible	yes	Hands free	Yes	Text message memory	40
Max. number of handsets	5	Headset socket	No		
Max. number of bases	4	Auto answer	Yes	Call waiting indicator	Yes
Conference call	Yes	Secrecy	Yes	PBX access code	Yes
Call transfer	Yes	Handset naming	Yes	Repeater compatible	No
Internal calls	Yes	Keypad lock	Yes	Wall Mount	Yes
Music on hold	No	Power on/off	Yes		
Indoor range* (Metres)	50	Inductive coupler	No	Talk time (hours)	10
Outdoor range* (Metres)	1000	Earpiece volume control	Yes	Standby (hours)	250
Display type	Mono	Hands free volume control	Yes	Battery type	Li-Ion
Display-number of lines #	6	Call timer	Yes	Battery size	
Backlit	Yes	Clock	Yes	Battery capacity (mAh)	550
Contrast control	Yes	Alarm	Yes		
Wallpapers		Calendar	No	Base PSU item code	066720
Screen saver		Appointments	No	Charger PSU item code	066720
Handset polyphonic ringtones	10	Illuminated keypad	Yes		
Handset standard ringtones	5	Keypad confirmation tone	Yes	<b>Answer Machine</b>	
Handset ringer on/off	Yes	Low battery indicator	Yes	Recording time (mins)	Up to 30
Handset ringer volume control	Yes	Low battery alert	Yes	Playback	Handset
Visual ring indicator	Yes	Out of range indicator	Yes	Outgoing messages	1
Associated ring tone	Yes	Out of range alert	Yes	Recordable outgoing messages	Yes
Base ringtones	0	Handset settings PIN protected	Yes	Answer delay	Yes
Base ringer on/off	No	Base settings Pin protected	Yes	Time saver	Yes
		Find key on base	Yes	Remote access	Yes
SIM card	No			Message advice	Indicator
Caller groups	No			Call screening	Yes
Quick dial memories	9			Memo	Yes
BT Call Block button	No			Timed TAM	Yes

Notes: \* In ideal conditions # including icons and soft keys as appropriate

# BT Elements 1K

## Product Specification

<b>Weights (g) and dimensions (cm)</b> Base: 161 Handset: 172 Charger: 82  Base: 12.6(H) x 12.8(W) x 6.5(D) Handset: 19.6(H) x 5.5(W) x 3.1(D) Charger: 4.5(H) x 10.8(W) x 7.9(D)	<b>Item code</b> Single : 079482 Twin : 079483 Trio : n/a Quad : n/a
<b>Gift box – dimensions (cm) / empty (g) / complete (g)</b> Single: 18(H) x 23(W) x 10(D) / 133 / 872 Twin: 18(H) x 23(W) x 14.3(D) / 182 / 1344 Trio: n/a Quad: n/a	<b>CSS code</b> Single : B46068 Twin : B46666 Trio : n/a Quad : n/a
<b>Over pack – dimensions (cm) / complete (kg)</b> Single: 26(H) x 49.1(W) x 38(D) / 9.34 Twin: 26(H) x 45.2(W) x 38(D) / 8.71 Trio: n/a Quad: n/a	<b>Gift box barcode</b> Single : 5016351616949 Twin : 5016351616956 Trio : n/a Quad : n/a
<b>No. of gift boxes per over pack</b> Single : 10 Twin : 6 Trio : n/a Quad : n/a	<b>Over pack barcode</b> Single : 05016351823149 Twin : 05016351823156 Trio : n/a Quad : n/a
<b>Pallet Ti's x Hi's</b> Single : 6 x 3 Twin : 6 x 3 Trio : n/a Quad : n/a	

Technical support:

Available from the BT Helpdesk on 0800 145 6789 or via the email link on the product page at [www.bt.com/producthelp](http://www.bt.com/producthelp)

Status: Launched

Country of manufacture: China

