



◆ SPECIFICATION

Model NO.	IPTA30HHE200	IPTA30HHL200	IPTA30HP200
Camera			
Image Sensor	1/2.7" Full HD CMOS Sensor	1/2.8" SONY Starvis Back-illuminated CMOS Sensor	1/2.8" SONY Starvis Back-illuminated CMOS Sensor
Resolution	2MP 1080P	2MP 1080P	2MP 1080P
Effective Pixels	1920(H)*1080(V)	1945(H)*1097(V)	1945(H)*1097(V)
Compression	H.264/H.264+/H.265/H.265+/JPEG/AVI /MJPEG		
TV System	PAL/NTSC		
Electronic Shutter Time	Auto: PAL 1/25-1/10000Sec; NTSC 1/25-1/10000Sec		
Minimun Illumination	0.001Lux	0.005Lux	0.002Lux
S/N Ratio	≥52dB		
Scanning System	Progressive		
Video Output	Network		
Reset Button	Optional		
Lens			
Focus Length	Board Lens 3.6mm		
Focus Control	Fixed		
Lens Type	Fixed		
Pixels	2M		
Night Vision			
Infrared LED	42μ x 2PCS		
Infrared Distance	25M		
IR Status	Auto Control		
IR Power On	Auto Control		
Network			
Ethernet	RJ-45 (10/100Base-T)		
Protocol	TCP/IP,ICMP,HTTP,HTTPS,FTP,DHCP,DNS,DDNS,RTP,RTSP,RTCP,NTP,SMTP		
ONVIF	Support ONVIF 2.4		

P2P	YES, Support QR Code		
POE	Optional, Support IEEE 802.3af		
Video Delay	0.3S (Within the Lan)		
Main Stream 1	2304*1296@20fps	2304*1296@20fps	2048*1536@15fps
Main Stream 2	1920*1080@30fps	1920*1080@30fps	1920*1080@30fps
Main Stream 3	1280*720@30fps	1280*720@30fps	1280*720@30fps
Sub Stream 1	720*480@20fps 720*480@30fps	720*480@20fps 720*480@30fps	720*480@15fps 720*480@30fps
Sub Stream 2	/	/	/
Sub Stream 3	/	/	/
Tri Stream	352*288@20fps 352*288@30fps	352*288@20fps 352*288@30fps	352*288@15fps 352*288@30fps
IE Brower	IE8-11, Google Chrome (lower than Ver44), Firefox (lower than Ver53), Mac Safari(lower than version 12)		
Smart Phone	iPhone, iPad, Android, Android Pad		
Camera Features			
Day/Night	Color/ B&W (IR-CUT)		
Intelligence function	/	/	/
Image Config	Saturation/Brightness/Contrast /Sharpness, Mirror, 3D NR , White Balance, FLK(Flicker Control)	Saturation/Brightness/Contrast /Sharpness, Mirror, 3D NR , White Balance, FLK(Flicker Control)	Saturation/Brightness/Contrast /Sharpness, Mirror, 3D NR , White Balance, FLK(Flicker Control), Video Tampering
Full Starlight	/	/	/
Corridor Pattern	Support	Support	Support
Defog Mode	Support	Support	Support
ROI	Support	Support	Support
BLC	Support	Support	Support
HDR	/	/	/
WDR	Support	Support	Support
Motion Detection	Support	Support	Support
Privacy Masking	3 Rectangular Zone	3 Rectangular Zone	3 Rectangular Zone
Recording Mode	NVR/NAS/CMS/Web	NVR/NAS/CMS/Web	NVR/NAS/CMS/Web
Language	Chinese Simplified, Chinese Traditional, English, Bulgarian, Polish, Farsi, German, Russian, French, Korean, Portuguese, Japanese, Turkish, Spanish, Hebrew, Italian,Nederlands		
Interface			
Audio	Optional	Optional	Optional
Alarm	/	/	/
SD Card Slot	Optional, Support Max 128GB	Optional, Support Max 128GB	Optional, Support Max 128GB
RS485	/	/	/

General

Housing	IP66
Anti-cut Bracket	YES
IR Cut Filter	YES
Operation Temperature	-20°C ~ +60°C RH95% Max
Storage Temperature	-20°C ~ +60°C RH95% Max
Power Source	DC12V±10%,700mA
Dimension	170(W) x 75(H) x 77(D)mm
Weight	770g

Cantonk (guangzhou) Corporation Limited

Add. :F5, 2# Building, No. 728, Kaichuang AVE., Economic & Technological Development Zone, Luogang District, 510530 Guangzhou, China

Tel. No.: +86 20 66217288 Fax No.: +86 20 66217166 Homepage: <http://www.cantonk.com> Email: info@cantonk.com