

R18IW7-0 | 18V Cordless Brushless Impact Wrench



- Compact brushless impact wrench delivers 270Nm of torque.
- Ideal for automotive applications such as changing oil, spark plugs or even maintaining brakes and suspension systems.
- Impact mechanism allows for high amounts of torque with little reactionary feedback through the handle.
- 4 torque settings for added control including AutoStop, a setting optimised for tightening and loosening wheel nuts on cars.
- Tri-Beam LED lights illuminate the work area and eliminate shadows on bits and fasteners.
- 1/2" Square drive with locking pin for easy socket fitment.

	R18IW7-0
Charger included?	No
Impact rate (ipm)	0-3900
Max. torque (Nm)	270
No load speed (rpm)	0-3000
No load speed gear 1 (rpm)	1800
No load speed gear 2 (rpm)	2200
No load speed gear 3 (rpm)	3000
No. of batteries supplied	0
Power	18V
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level uncertainty [dB(A)]	3.0
Standard equipment	1/4" hex adaptor
Supplied in	Recyclable Carton
Torque settings	150/200/270/120
Voltage (V)	18
Weight [without battery] [Kg]	1.0
Weight with battery pack (kg)	1.3