

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0008700058**  
**Status:** **Active**  
**Overview:** SPOX BMI Connector System  
**Description:** SPOX Crimp Terminal 5103, 22-28 AWG, Reel, Phosphor Bronze (CuSn), Chain Type

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-5103-003 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5103-004 (PDF)</a>
<a href="#">Product Specification PS-5045-001 (PDF)</a>	<a href="#">Packaging Specification SPK-5103-001-001 (PDF)</a>
<a href="#">Product Specification PS-5045-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-5102-004-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	5103
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	SPOX BMI Connector System
Packaging Alternative	08700059 (Loose)
Product Name	SPOX
UPC	800753534797

**Physical**

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	60.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size AWG	22, 24, 26, 28
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	250V

**Solder Process Data**


Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

Engineering Number	5103PBT
--------------------	---------

**Reference - Drawing Numbers**

Crimp Specification	CS-5103, CS-5103A
Packaging Specification	SPK-5103-001-001
Product Specification	PS-5045-001, PS-5045-002, PS-5102-004-001, PS-5103-003, PS-5103-004
Sales Drawing	SD-5103-002



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free  
Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5103 Series](#)

**Use With**

[5102 Crimp Housing](#), [5207 Mini SPOX Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below.*

*Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
-------------	-----------

Manual Extraction Tool	<a href="#">638131500</a>
------------------------	---------------------------

Hand Crimp Tool for 2.50mm Pitch SPOX Crimp Terminal, 22-28 AWG	<a href="#">638281900</a>
-----------------------------------------------------------------	---------------------------

FineAdjust Applicator for Wire-to-Board and Wire-to-Wire Terminal, 22-28 AWG Wire	<a href="#">639004600</a>
-----------------------------------------------------------------------------------	---------------------------

This document was generated on 05/07/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**