

MAX300S orange

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer
Latches: nylon
Pins: nylon + 30% fiberglass
O-ring: polymer

COLOURS: black, orange
EXTERNAL DIMENSIONS: 336 x 300 x H148 mm (13.23 x 11.81 x H5.83 inch)
INTERNAL DIMENSIONS: 300 x 225 x H132 mm (11.81 x 8.86 x H5.20 inch)
LID-BOTTOM DEPTH: 33 + 99 mm (1.30 + 3.90 inch)
WEIGHT WITH FOAM: 1.76 kg – 3.88 lbs.
CAPACITY: 15kg – 33 lbs.
CARTON DIMENSIONS: 605 x 345 x 320 mm – 23.82 x 13.58 x 12.60 inch
PCS PER CARTON: 4
WEIGHT OF THE FULL CARTON WITH FOAMS: 8.04 kg – 17.72 lbs.
MOULDING: injection molded
RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)
FEATURES: IP67, DEF STAN 81-41, STANAG 4280
CUSTOMIZATION: personalized nameplate/resin label
ACCESSORIES: cubed foams, pouch

