

## MAX002S

- Waterproof and dustproof IP67 certified
- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system

Body: polypropylene copolymer

Latches: nylon

O-ring: polymer

COLOURS: black

EXTERNAL DIMENSIONS: 230 x 175 x H53mm (9.05 x 6.88 x h2.08 inch)

INTERNAL DIMENSIONS: 212 x 140 x H47mm (8.34 x 5.51 x H1.85 inch)

LID-BOTTOM DEPTH: 14+33mm (0.55+1.33 inch)

WEIGHT WITH FOAM: 0.28 kg – 0.62 lbs.

CARTON DIMENSIONS: 370 x 245 x 375mm – 14.57 x 9.65 x 14.76 inch

PCS PER CARTON: 12

WEIGHT OF THE FULL CARTON WITH FOAMS: 3.89kg – 8.58 lbs.

MOULDING: injection molded

RANGE TEMPERATURE: -10 / 80°C (14 / 176°F)

CUSTOMIZATION: personalized nameplate/resin label

FEATURES: IP67

