

MAX004S

- Waterproof and dustproof IP67 certified
- Watertight seal around lid
- Automatic pressure release valve
- Stackable interlocking system

Body: polypropylene copolymer

Latches: nylon

O-ring: polymer

COLOURS: black

EXTERNAL DIMENSIONS: 350 x 230 x H86mm (13.77 x 9.05 x H3.38 inch)

INTERNAL DIMENSIONS: 316 x 195 x H80mm (12.44 x 7.67 x H3.14 inch)

LID-BOTTOM DEPTH: 16+40mm (0.63+2.55 inch)

WEIGHT WITH FOAM: 0.62 kg – 1.37 lbs.

WEIGHT OF THE FULL CARTON WITH FOAMS: 2.87 kg – 6.33 lbs.

PCS PER CARTON: 4

MOULDING: injection molded

RANGE TEMPERATURE: -10 / 80°C (14 / 176°F)

CUSTOMIZATION: personalized nameplate/resin label

FEATURES: IP67

