

## Han-INOX 3A-HBM-DL-C



Part number	19 44 003 0305
Specification	Han-INOX 3A-HBM-DL-C
HARTING eCatalogue	<a href="https://b2b.harting.com/19440030305">https://b2b.harting.com/19440030305</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Bulkhead mounted housings
Description of hood/housing	Straight With metal cover

### Version

Locking type	Single locking lever
Size	3 A
Field of application	Hoods/housings for harsh environments
Details	for mounted male insert

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR



Pushing Performance

## Material properties

Material (locking)	Stainless steel
--------------------	-----------------

## Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

## Commercial data

Packaging size	1
Net weight	65 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors