



SpeedSplice™



Field-Serviceable, Splicing Solution

Amphenol Sine Systems' **SpeedSplice™** product is our field-serviceable solution where permanent splices are needed. Made of silicone rubber with an IP67 rating, our **SpeedSplice™** houses an environmentally-sealed, mated pair of contacts, ensuring your repairs will withstand harsh environmental conditions. For use with A Series Common Contact Size 16 & 12 Machined/Stamped & Formed. Available in individual piece or as a kit.






Applications: Heavy Equipment, Agricultural, Automotive, Military, Alternate Energy, and other demanding interconnect applications.

Key Features

- Available in Size 12, 10-14AWG; Size 16, 14-20AWG
- 13-25A Range @ 250V
- Operating Temperature -55°C to +125°C



SpeedSplice™ Part Numbers

Image	Part Number	Description	AWG	Amperage	Voltage	IP Rating
	ATSS-16-00	SpeedSplice™, Contact Size 16, Single Terminal Connection	14-20	13A	250V	IP67
	ATSS-16-KIT01	SpeedSplice™, Contact Size 16, Single Terminal Connection, Kit	16-20	13A	250V	IP67
	ATSS-16-KIT02	SpeedSplice™, Contact Size 16, Single Terminal Connection, Kit	14	13A	250V	IP67
	ATSS-12-00	SpeedSplice™, Contact Size 12, Single Terminal Connection	10-14	25A	250V	IP67
	ATSS-12-KIT01	SpeedSplice™, Contact Size 12, Single Terminal Connection, Kit	12-14	25A	250V	IP67



A Series™ Family



Standard products. Custom solutions
Customer Service +1 800 394 7732

For more information, contact: Customer Service, +1 800 394 7732, csr@amphenol-sine.com

© 2019 Amphenol Sine Systems Corporation, 44274 Morley Drive, Clinton Township MI 48036 USA. www.amphenol-sine.com. Customer Service +1 800 394 7732
Every effort has been made to ensure that the information contained in this document is accurate at the time of publication. Specifications or information stated in this document are subject to change without notice. 06/2019