

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2074580006](#)
Status: **Active**
Overview: [L1NK Connector System](#)
Description: L1NK 396 Receptacle Housing, Single Row, 6 Circuits, UL 94V-0, Black

Documents:

| | |
|---|---|
| 3D Model | Product Specification 2074580000-TS-000 (PDF) |
| Drawing (PDF) | Packaging Specification 2074580000-PK-000 (PDF) |
| Product Specification 2074580000-PS-000 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

UL E29179

General

| | |
|--------------------|---------------------------------------|
| Product Family | Crimp Housings |
| Series | 207458 |
| Application | Power, Wire-to-Board |
| Datasheet Order No | 987651-9951 |
| Overview | L1NK Connector System |
| Product Name | L1NK 396 |
| UPC | 191130115600 |

Physical

| | |
|-------------------------------|----------------|
| Circuits (maximum) | 6 |
| Color - Resin | Black |
| Flammability | 94V-0 |
| Gender | Receptacle |
| Glow-Wire Capable | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 2.090/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.96mm |
| Pitch - Termination Interface | 3.96mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|--------------------------------------|
| Packaging Specification | 2074580000-PK-000 |
| Product Specification | 2074580000-PS-000, 2074580000-TS-000 |
| Sales Drawing | 2074580000-SD-000 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[207458](#) Series

Mates With

L1NK 396 Headers [207478](#) , [207479](#)

Use With

MarKK Crimp Terminal [455703000](#) , L1NK
TPA Retainer [207459](#)