

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0747521108](#)
Status: **Active**
Overview: SFP+ Passive Cable Assembly
Description: SFP+-to-SFP+ Lite Passive Cable Assembly, 10Gbps, 30 AWG Cable, with Latch, 1.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR64395
 UL E72548

General

Product Family Cable Assemblies
 Series [74752](#)
 Assembly Configuration Dual Ended Connectors
 Comments Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths., Meets customer requirements for speeds up to 10 Gbps. Passive cables may require host pre-emphasis and equalization to reach at the longer lengths.
 Connector to Connector SFP+-to-SFP+
 Overview [SFP+ Passive Cable Assembly](#)
 Product Name SFP Plus, SFP+
 UPC 889056311670

Physical

Cable Length 1.0m
 Circuits (Loaded) TWO DIFFERENTIAL PAIR
 Gender Male-Male
 Lock to Mating Part Yes
 Net Weight 1.000/g
 Packaging Type Bag
 Single Ended No
 Wire Size AWG 30
 Wire/Cable Type Twinax

Electrical

Impedance 100Ω
 Shield Type Full Shield
 Shielded Yes

Material Info

Reference - Drawing Numbers

Sales Drawing 747520008-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[74752 Series](#)