



TOUGH ALUMINIUM STRUCTURE




TRIPOD AVAILABLE (ALSO SHOWING THE SLR-4750 /1300 MODELS)



2500 LUMEN

SLR-2500 - INDUSTRIAL SITE LIGHT



2500
LUMEN
OUTPUT

2½-9
HOURS
RUNTIME


60
METRE
BEAM RANGE

IP65
DUST + WATER
RESISTANCE

- Super bright 2500 Lumen white COB LED
- Dual power - rechargeable & mains
- Super tough aluminium structure
- 180° adjustable handle
- IK07 shock resistant
- IP65 dust + water resistant
- Mains multi-country charger included
- 3.5 hours charge time



180° ADJUSTABLE HANDLE/STAND



TOUGH ALUMINIUM STRUCTURE

BATTERY 11.1v 4400mAh Li-ion Rechargeable Battery

WEIGHT 1115g

DIMENSIONS 70 x 224 x 198mm