

# Novopro Partybar 100 DMX

48w RGBW, remote controlled lighting rig with bags



Includes:  
IR remote control  
5 meter long IEC mains  
Stand & floor brackets  
2 x gig bags  
Colour box



- A portable and affordable, all-in-one stage lighting system
- Set up and ready to rock the party in minutes!
- T-bar controller with four par cans on a stand plus full remote control
- Creates superb multicolour wash effects
- Pre-programmed light shows that dance to the beat of the music
- Ideal for parties, bands & DJs or performers on-the-go
- Perfect for school plays or wedding parties
- Each individual par can light can be positioned as required
- 4 x 12 pcs 1 watt red, green, blue & white ultra bright LEDs
- Front and rear IR sensors for the remote control
- Operating modes: Auto, Sound-to-Light, 8 channel DMX512, Remote Control
- Linkable Master/Slave operation
- The lighting stand extends from 1.30m to 2.4m and uses a 35mm top pole mount
- Floor mount using the included brackets
- Expandable - 4 x mounting points for additional lights on the top of the bar
- Includes an extra long, 5m IEC mains power lead
- Linkable IEC output
- Power: AC220-240V 50/60Hz / 60W
- Unit dimensions (WxDxH): 750 x 190 x 92mm (not inc stand)
- Stand dimensions (WxDxH): 90 x 90 x 130mm (closed)
- Unit Weight: 6.25Kg

The Kit includes the following:

- 1 x T-bar controller
- 1 x T-bar controller gig bag
- 4 x Individually adjustable par cans
- 1 x Height adjustable lighting stand
- 1 x Light stand gig bag
- 2 x Floor mounting brackets
- 1 x 5m IEC mains power lead
- 1 x IR remote control
- 1 x Instruction manual

Supplied in a full colour, POS display box

EAN barcode: 5060473245501

## novopro

Designed & engineered in the UK by working performers