


COBAGRiP® Stair Nosing

Designed to help prevent slips on stairs



- Suitable for use on existing or new-build steps.
- Manufactured with chamfered back edge for additional safety.
- Bright colour for visibility meeting DDA requirements.



COBAGRiP Stair Nosing



COBAGRiP Stair Tread



Technical Specification

Material:	Silicone Carbide
Resistant to Chemicals:	5mm
Environmental Resistance:	Designed to help prevent slips on stairs
Cleaning Method:	COBAGRiP should be almost maintenance free in most outside environments. Natural elements will have the effect of cleaning COBAGRiP. Brushing and flushing with a mild detergent solution may be desirable now and again to restore appearance
Product Performance:	Slip tested to R13 in accordance with BS 7976-2:2002 <ul style="list-style-type: none"> • PTV 79 in dry conditions • PTV 73 in wet conditions
Operating Temperature:	-10°C to 80°C
Flame Retardancy:	Fire tested to EN 9239-1:2010
Country of Origin:	China

Stair Nosings	Yellow	Weight
3m x 55mm x 55mm	GRP070001N	1.80 kg
2m x 55mm x 55mm	GRP070002N	1.20 kg
1.5m x 55mm x 55mm	GRP070003N	0.90 kg
1m x 55mm x 55mm	GRP070004N	0.60 kg

Stair Treads	Black/Yellow	Black/White	Weight
3m x 345mm x 55mm	GRP010701S	GRP010131S	6.60 kg
2m x 345mm x 55mm	GRP010702S	GRP010132S	4.40 kg
1.5m x 345mm x 55mm	GRP010703S	GRP010133S	3.30 kg
1m x 345mm x 55mm	GRP010704S	GRP010134S	2.20 kg

COBAGRiP® Stair Tread

Silicone carbide surface helps to prevent slip accidents on stairs

- Designed to fully cover the stair area.
- 55mm x 55mm contrasting coloured nosing meeting DDA requirements.
- Can be used in conjunction with COBAGRiP Sheet.

Mapei Mapeflex PU45

- Single component, thixotropic, rapid-hardening polyurethane sealant and adhesive with a high modulus of elasticity

Size	Grey	Weight
600ml	PU45	0.50 kg

