

ZK2.5-CH-4P-RL



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNK Series

General Information

| | |
|-------------------------------|--|
| Extended Product Type: | ZK2.5-CH-4P-RL |
| Product ID: | 1SNK705711R0000 |
| EAN: | 3472597057113 |
| Catalog Description: | ZK2.5-CH-4P-RL PI-Spring clamp Terminal Block - Component holder - Grey |
| Long Description: | - Protect your circuit with one 1N4007 diode, - Clear identification of the diode orientation with marking identification on the top of the terminal block |

Ordering

| | |
|--------------------------------|----------|
| Color: | Grey |
| Minimum Order Quantity: | 50 piece |
| Customs Tariff Number: | 85369010 |

Popular Downloads

| | |
|----------------------------------|-----------------|
| Instructions and Manuals: | 1SNK160027C0206 |
|----------------------------------|-----------------|

Dimensions

| | |
|------------------------------------|---------|
| Product Net Width: | 5.2 mm |
| Product Net Height: | 86.1 mm |
| Product Net Depth / Length: | 42.2 mm |
| Product Net Weight: | 10.91 g |

Technical

| | |
|--|---|
| Rated Cross-Section: | 2.5 mm ² |
| Spacing: | 5.2 mm |
| Connection Type: | PI Spring |
| Function: | Component holder |
| Number of Levels: | 1 |
| Connecting Capacity Main Circuit: | Spring Clamp / Flexible 1x 0.22 ... 2.5 mm ² Spring Clamp / Rigid 1x 0.2 ... 4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / Without Insulated Ferrule 1x 0.22 ... 2.5 mm ² Spring Clamp / With Twin Ferrule 2x 0.22 ... 0.5 mm ² |
| Gauge Type: | A2 / 2.3 mm Dia. |
| Rated Current (I_n): | Main Circuit 1 A |
| Rated Voltage (U_r): | 630 V |

| | |
|---|--|
| Rated Impulse Withstand Voltage (U_{imp}): | 6000 V |
| Pollution Degree: | 3 |
| Power Loss: | 0 W |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Insulation Material: | Polyamide |
| Mounting on DIN Rail: | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |

Technical UL/CSA

| | |
|---|--|
| Maximum Operating Voltage UL/CSA: | Main Circuit 300 V |
| Connecting Capacity Main Circuit UL/CSA: | Spring Clamp / Rigid 1x 26 ... 12 AWG Spring Clamp / With Insulated Ferrule 1x 26 ... 14 AWG Spring Clamp / Without Insulated Ferrule 1x 26 ... 14 AWG |
| Connecting Capacity UL/CSA: | Stranded 12 AWG |
| Flammability According to UL94: | V0 |

Environmental

| | |
|--|--|
| Ambient Air Temperature: | Operation -55 ... +110 °C Storage -55 ... +110 °C |
| Resistance to Vibrations acc. to IEC 60068-2-6: | Compliant |
| RoHS Status: | Following EU Directive 2011/65/EU |

Certificates and Declarations (Document Number)

| | |
|--|-----------------|
| BV Certificate: | 1SND162013A0203 |
| CSA Certificate: | 1SND162014A0206 |
| cUL Certificate: | 1SND162012A0204 |
| Declaration of Conformity - CE: | 1SND225108U1000 |
| EAC Certificate: | 1SND161009A1100 |
| Environmental Information: | 1SND220094E1001 |
| Instructions and Manuals: | 1SNK160027C0206 |
| RoHS Information: | 1SND230556F0201 |

Classifications

| | |
|------------------------------------|--|
| Object Classification Code: | X |
| ETIM 4: | EC000902 - (Knife) disconnect terminal block |
| ETIM 5: | EC000902 - (Knife) disconnect terminal block |
| ETIM 6: | EC000902 - (Knife) disconnect terminal block |

Container Information

Package Level 1 Units: 50 piece

Package Level 1 Width: 101 mm

Package Level 1 Depth / Length: 265 mm

Package Level 1 Height: 47 mm

Package Level 1 Gross Weight: 0.596 kg

Package Level 1 EAN: 3472597057113

Package Level 2 Units: 500 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 400 mm

Package Level 2 Height: 200 mm

Package Level 3 Units: 24000 piece

Product Packing Type: Box

