

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2032630034](#)
Status: **Active**
Overview: Coeur CST High-Current Interconnect System
Description: Coeur CST High-Current Male Press-Fit Pin, 3.40mm Diameter, 26.00mm Length

Documents:

[Drawing \(PDF\)](#) [Application Specification 2043130018-AS-000 \(PDF\)](#)
[Product Specification 2043130018-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	PCB Headers
Series	203263
Application	Power
CURRENT-MAX-NUMERIC	75.0
Datasheet Order No	987651-8619
Overview	Coeur CST High-Current Interconnect System
Product Name	Coeur CST
UPC	191130073702

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	3.40mm
Durability (mating cycles max)	200
Glow-Wire Capable	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Net Weight	2.527/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Press-Fit

Electrical

Current - Maximum per Contact	75.0A
Voltage - Maximum	600V

Material Info

Reference - Drawing Numbers

Application Specification	2043130018-AS-000
Product Specification	2043130018-PS-000
Sales Drawing	2032630034-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[203263](#) Series

Mates With

Coeur CST 3.40mm Socket [204365](#) ,
[204318](#) , [204313](#)