

## METEOR SERIES 3 – Triple CCT LED Batten Light A Standard

Direct replacement for traditional single and twin batten lights.

Slim, opal diffuser in square or rounded shape.

Available in 4ft, 5ft and 6ft lengths.

Single or triple CCT versions, flicker free.

**Flicker Free**



### Features

- Size = conventional batten width
- Housing = steel housing with aluminium gear tray, matt white finish
- Diffuser = opal polycarbonate
- PCB = fibre
- Fitting = surface or suspended mount
- Driver = high quality Lifud, flicker free
- Colour Temp = single or switchable


### Options

- CCT switch = single or triple CCT
- Output = standard or high output
- Length = 4ft, 5ft or 6ft

### Specifications

- LED type = SMD2835
- CRI = >80
- CCT = 3000K, 4000K, 6000K single or switchable
- Power Factor = >0.95
- Colour Index = Ra>80
- Input Voltage = AC220-240V 50/60Hz
- Operating Voltage = DC36-42V
- Operating Temp = -15 degC to +50 degC
- Storage Temp = -25 degC to +55 degC
- IP Rating = IP20
- Life Span = 50,000 hours
- Warranty = 5 years

Product Size	CCT		LM/W		
	Single	Rated Power	3000K/4000K/6000K		
4ft/1227x62x72mm	T	30W	80	110	90
4ft/1227x62x72mm	T	45W	80	110	90
5ft/1527x62x72mm	T	35W	80	110	90
5ft/1527x62x72mm	T	55W	80	110	90
6ft/1791x62x72mm	T	45W	80	110	90
6ft/1791x62x72mm	T	65W	80	110	90
4ft/1227x62x72mm	S	30W	100	110	110
4ft/1227x62x72mm	S	45W	100	110	110
5ft/1527x62x72mm	S	35W	100	110	110
5ft/1527x62x72mm	S	55W	100	110	110
6ft/1791x62x72mm	S	45W	100	110	110
6ft/1791x62x72mm	S	65W	100	110	110



30W / 45W = 1227    35W / 55W = 1527    45W / 65W = 1791



## METEOR SERIES 3 – Triple CCT LED Batten Light A Standard

### Order Code

### **MET3A R ST 4 XK 45 S**

01    02 03 04 05 06 07

- 01. Product series
- 02. Shape (R = Round, S = Square)
- 03. Type (ST = Standard)
- 04. Length (4 = 4ft, 5 = 5ft, 6 = 6ft)
- 05. CCT (3K = 3000K only, 4K = 4000K only, 6K = 6000K only, XK = switchable between 3K/4K/6K)
- 06. Rated Power in W (30, 35, 45, 55 or 65)
- 07. Output lumens (S = Standard, H = High)



square or round  
polycarbonate diffuser



3 x pinch points for easy  
removal of diffuser



UK standard BESA box  
cut outs



Lifud Driver



Internal CCT Switch



Screwless Terminal Block