

# Technical Data

Part Number: XN4P

Product Group: CCTV

Product Type: NVR



## Xvision 4 Camera HD-IP 8MP (4K) H265+ NVR with built in 4 Port PoE Switch

Model: XN4P	
IP Cameras Supported	X2C, X4C, X5C, Onvif
IP Camera Channels	4 Channel
Compression	H264/H265+
Maximum Recording Resolution	8MP (4K)
Recording Bandwidth	50Mbps
Live/Playback	8MP – 2 Channel 5MP – 3 Channel 4MP/2MP - 4 Channel
Video Output	1 x HDMI (4K), 1 x VGA
Display Split	1/4
Recording Mode	Continuous/Manual/Motion
Ethernet	RJ45 10/1000M

## Technical Data

Internal Hard Drive	1 SATA HDD, up to 6TB
ESata	No
PoE Ports	Yes - 4 Port
Alarm Input/Outputs	No
RS485	No
USB Interface	2 x USB For Mouse, Backup, Upgrade
Controls	IR Remote, USB Mouse, Touch Panel
Dropbox Support	Yes - Motion Activated Events
Email Alerts	Yes
Power Supply	DC 48V
Dimensions (WxHxD)	300x53x227mm