

# Technical Data

Part Number: X4C2000VV-G

Product Group: CCTV

Product Type: IP Dome Camera



## **Xvision 2MP H265+ Vandal Dome IP Camera, 2.7-13.5mm, 60m IR, Starlight**

<b>Model: X4C2000VV-G</b>	
Style	Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Megapixel CMOS Sensor
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, DNR, Starlight, Backlight Compensation

## Technical Data

Resolution	1080P
Lens Type	Varifocal
Lens Size	2.7-13.5mm
Viewing Angle	33-114°
Night Vision	60m IR
Minimum Illumination	0.05 Lux
Video Compression	H265+
Video Streams	Dual Stream
Video Resolution & Frame Rates	1920x1080 - 25fps 1280x960 - 25fps 1280x720 - 25fps
Video Bitrate	256Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Power Consumption	<7W
Audio Input	Yes
Power Input	12V DC Socket (2.1mm)
On Board Recording	No
Alarm Input	No
Video Analytics	No
Operating Temperature	-30 ~ 55°
Dimensions (WHD)	Ø135.4x127.7mm
Weight (kg)	0.72
Warranty	3 Year Warranty